






SPECIFICATIONS

Voltage rating : 250V AC/DC

Current rating : 7A AC/DC

Withstanding voltage : 1500V AC/minute

Contact resistance : 20mΩ max

Temperature range : -40°C to +105°C

Insulation resistance : 1000MΩ min

MATERIAL

Insulator : Nylon66 (UL94V-2)

Insulator color : Transparnt White

Contact : Brass

Plating : Tin Plated

Poles	Dimensions(mm)		
	A	B	C
2	----	5.60	9.40
4	4.20	9.80	13.60
6	8.40	14.00	17.80
8	12.60	18.20	22.00
10	16.80	22.40	26.20
12	21.00	26.60	30.40
14	25.20	30.80	34.60
16	29.40	35.00	38.80
18	33.60	39.20	43.00
20	37.80	43.40	47.20
22	42.00	47.60	51.40
24	46.20	51.80	55.60

TOLERANCE (mm)		APPROVALS		DATE		TITLE 4.2 Power Wafer Straight Dip w/Pegs		AMPHENOL Amphenol European Design Center			
X.	±0.3	DRAWN Stephane		05/Jan/2007				Scale N.A.		Sheet 1 of 1	
XX	±0.2	CHECKED Rob		05/Jan/2007							
X.XX	±0.15	APPROVED Rob		05/Jan/2007							
UNLESS OTHERWISE SPECIFIED				UNIT : mm		SIZE : A4		DRAWING N° MF42-SP-XX		REV. A	