

**Broadband Solutions**

CX3799812 | 2000135 RIB EMPTY DUCT COEX

**ConQuest® Empty Conduit, 2 in, SDR 13.5, ribbed, orange**

## Dimensions

|                            |                       |
|----------------------------|-----------------------|
| Nominal Size               | 2 in                  |
| Wall Thickness Designation | SDR 13.5              |
| Inner Diameter, nominal    | 50.876 mm   2.003 in  |
| Length                     | 762.00 m   2500.00 ft |
| Outer Diameter, nominal    | 60.325 mm   2.375 in  |
| Wall Thickness, minimum    | 4.470 mm   0.176 in   |
| Weight                     | 532.0 lb/kft          |

## General Specifications

|              |              |
|--------------|--------------|
| Color        | Orange       |
| Conduit Type | Non-toneable |
| Wall Type    | Ribbed       |
| Brand        | ConQuest®    |
| Warranty     | One year     |

## Material Specifications

|                                       |                                     |
|---------------------------------------|-------------------------------------|
| Density Test Method                   | ASTM D792A                          |
| Density, maximum                      | 0.955 g/cm <sup>3</sup>             |
| Density, minimum                      | 0.941 g/cm <sup>3</sup>             |
| Design Standard                       | ASTM D3350-05                       |
| Environmental Stress Crack Resistance | Failure rate of 10% within 96 hours |
| Environmental Stress Test Method      | ASTM D1693, ESCR Condition B        |
| Flexural Modulus, minimum             | 552 N/mm <sup>2</sup>   80000 psi   |
| Flexural Property Test Method         | ASTM D790                           |
| Hydrostatic Design Basis              | Not pressure rated                  |
| Hydrostatic Design Test Method        | ASTM D2837                          |
| Material Type                         | High density polyethylene (HDPE)    |
| Melt Flow Rate Test Method            | ASTM D1238                          |
| Melt Flow Rate, maximum               | 0.39 g/10 min                       |
| Tensile Property Test Method          | ASTM D638                           |
| Tensile Strength at yield, minimum    | 21 N/mm <sup>2</sup>   3000 psi     |

## Mechanical Specifications

|                                  |                    |
|----------------------------------|--------------------|
| Minimum Bend Radius, unsupported | 660.4 mm   26.0 in |
|----------------------------------|--------------------|

CX3799812 | 2000135 RIB EMPTY DUCT COEX

Pulling Tension, maximum 1170.3 kg | 2580.0 lb

## Regulatory Compliance/Certifications

| Agency        | Classification                                                                 |
|---------------|--------------------------------------------------------------------------------|
| ISO 9001:2008 | Designed, manufactured and/or distributed under this quality management system |

## \* Footnotes

Environmental Stress Crack Resistance ESCR—Environmental Stress Crack Resistance