



1

2

3

4

A		B		C	
HG-2	3.2 [.126]	4.8 [.190]	1.6 [.063]	8.0 [.315]	6.4 [.252]
HG-2.5	4.0 [.148]	6.4 [.252]	1.6 [.063]	9.5 [.374]	6.3 [.248]
HG-3	4.8 [.188]	7.7 [.305]	0.8 [.032]	10.9 [.430]	4.8 [.188]
HG-3.5	5.5 [.217]	8.0 [.315]	1.6 [.063]	10.9 [.430]	5.5 [.217]
HG-4	6.4 [.252]	9.5 [.374]	2.4 [.095]	14.2 [.559]	7.0 [.276]
HG-5	8.0 [.313]	10.9 [.430]	1.6 [.063]	14.3 [.562]	4.8 [.188]
HG-6	9.5 [.374]	12.5 [.492]	1.6 [.063]	17.0 [.669]	7.0 [.276]
HG-8	12.6 [.495]	16.8 [.660]	1.6 [.063]	21.5 [.846]	6.4 [.250]
HG-9	14.2 [.558]	17.1 [.675]	1.6 [.063]	22.2 [.875]	4.8 [.188]
HG-10	15.5 [.610]	18.8 [.742]	1.6 [.063]	22.2 [.875]	5.6 [.219]
HG-11	17.1 [.672]	18.7 [.735]	1.6 [.063]	23.7[.933]	4.8 [.188]
HG-12	18.6 [.734]	24.8 [.976]	1.6 [.063]	31.3 [1.234]	8.0 [.313]
HG-14	21.8 [.860]	25.1 [.990]	1.6 [.063]	30.2 [1.188]	8.0 [.313]
HG-16	24.6 [.970]	31.5 [1.240]	1.6 [.063]	38.1 [1.500]	8.0 [.313]
HG-17	8.0 [.315]	11.0 [.433]	2.0 [.079]	16.0 [.630]	7.0 [.276]
HG-18	12.7 [.500]	19.0 [.748]	2.4 [.095]	24.0 [.945]	7.1 [.280]
PART NUMBER	"ID"	"H"	"P"	"OD"	"T"



SECTION A-A

NOTES

- 1a) METRIC PRIMARY UNITS:mm
- 1b) IMPERIAL SECONDARY UNITS: [inches]
- 2) ALL RMS-262 PARTS (UL94-V2) ARE AVAILABLE IN RMS-263 (UL94-V0) BY SPECIAL ORDER

INFORMATION CONTAINED IN THIS DOCUMENT IS CONFIDENTIAL TO RICHCO INTERNATIONAL Co. Ltd. AND MAY NOT BE DISCLOSED OR REPRODUCED IN WHOLE OR PART WITHOUT THEIR WRITTEN CONSENT.



GENERAL TOLERANCE:
FOR REFERENCE ONLY ±0.50 [0.02]
UNLESS OTHERWISE STATED
ANGULAR ±1°



MATERIAL:		RMS-262 TPE (see notes)		COLOUR:		BLACK	
DESCRIPTION:		HG-X		PART No:		SEE TABLE	
DRG No:		760-0001		NPR No:		N/A	
DRN		DATE		CHKD		DATE	
OW		06/04/05		NBr		08/04/05	
SCALE		SHEET No.		SHEET No.		SHEET No.	
NTS		1 OF 1		1 OF 1		1 OF 1	