

3.5x2.8mm SURFACE MOUNT LED LAMP


XZMY45W



SUN LED

Email : sales@us.sunled.com

Web Site : www.sunled.com



Notes:


1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01)$ unless otherwise noted.

Absolute maximum ratings (T _A =25°C)		MY (InGaAlP)	Unit
Reverse voltage	V _R	5	V
Forward current	I _F	30	mA
Forward current (peak) 1/10Duty cycle 0.1ms pulse width	i _{FS}	150	mA
Power dissipation	P _T	125	mW
Operating temperature	T _A	-40 ~ +85	°C
Storage temperature	T _{stg}		





Operating Characteristics (T _A =25°C)		MY (InGaAlP)	Unit
Forward voltage (typ.) (I _F =20mA)	V _F	2.0	V
Forward voltage (max.) (I _F =20mA)	V _F	2.5	V
Reverse current (V _R =5V)	I _R	10	uA
Wavelength at peak emission (I _F =20mA)	λ _{peak}	590	nm
Wavelength at Dominate emission (I _F =20mA)	λ _D	588	nm
Spectral Line half-width (I _F =20mA)	Δλ	28	nm
Capacitance (V _F =0V, f=1MHz)	C	25	pF

Part Number	Emitting Color	Emitting Material	Lens-color	Luminous Intensity (I _F =20mA) mcd min. typ.		Wavelength nm λ _P	Viewing Angle 2θ1/2
XZMY45W	Yellow	InGaAlP	Water Clear	36	115	590	120°

XZMY45W




◆MY




XZMY45W

❖SMT Reflow Soldering Instructions



❖Recommended Soldering Pattern (Units : mm;Tolerance:±0.1)



❖Tape Specification (Units : mm)

