ALUMINUM ELECTROLYTIC CAPACITORS

nichicon

VR Miniature Sized series

Anti-Solvent Feature (Through 100V only)

- One rank smaller case sizes than VX series.
- Compliant to the RoHS directive (2011/65/EU).





■Specifications

Item	Performance Characteristics
Category Temperature Range	−40 to +85˚C (6.3V to 400V), −25 to +85˚C (450V)
Rated Voltage Range	6.3 to 450V
Rated Capacitance Range	0.1 to 33000μF
Capacitance Tolerance	±20% at 120Hz, 20˚C
Leakage Current	Rated voltage (V) | 6.3 to 100V: After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.03CV or 4 (μA), whichever is greater. After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01CV or 3 (μA), whichever is greater. | 160 to 450V: After 1 minute's application of rated voltage at 20°C, CV ≦ 1000 : I = 0.1CV+40μA or less. After 1 minute's application of rated voltage at 20°C, CV > 1000 : I = 0.04CV+100 (μA) or less
Tangent of loss angle (tan δ)	For capacitance of more than 1000μF, add 0.02 for every increase of 1000μF. Measurement frequency : 120Hz at 20˚C

Rated voltage (V)	6.3	10	16	25	35	50	63	100	160 to 315	350 to 450
tan δ (MAX.)	0.28	0.24	0.20	0.16	0.14	0.12	0.10	0.08	0.20	0.25

Stability at Low Temperature — Measurement frequency : 120Hz

Rated voltage (V)		6.3	10	16	25	35	50	63	100	160 to 200	250 to 350	400	450
Impedance ratio	Z−25˚C / Z+20˚C	5	4	3	2	2	2	2	2	3	4	6	15
ZT / Z20 (MAX.)	Z−40˚C / Z+20˚C	12	10	8	5	4	3	3	3	4	8	10	—

Endurance — The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C.

Capacitance change	Within ±20% of the initial capacitance value
tan δ	200% or less than the initial specified value
Leakage current	Less than or equal to the initial specified value

Shelf Life — After storing the capacitors under no load at 85˚C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.

Marking — Printed with white color letter on black sleeve.

■Radial Lead Type



(mm)

φD	4	5	6.3	8	10	12.5	16	18	20	22	25
P	1.5	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10.0	10.0	12.5
φd	0.45	0.5	0.5	0.6	0.6	0.6	0.8	0.8	1.0	1.0	1.0
β	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	1.0	1.0

α	(L<20) 1.5
	(L≧20) 2.0

• Please refer to page 20 about the end seal configuration.

Type numbering system (Example : 10V 330μF)

1	2	3	4	5	6	7	8	9	10	11	12
U	V	R	1	A	3	3	1	M	E	D	

- 12: Size code
- 10, 11: Configuration※
- 9: Capacitance tolerance (±20%)
- 6, 7, 8: Rated capacitance (330μF)
- 4, 5: Rated voltage (10V)
- 1, 2, 3: Series name
- Type

※ Configuration

φ D	Pb-free leadwire Pb-free PET sleeve
4	DD6
5	DD
6.3	ED
8 · 10	PD
12.5 to 18	HD
20 to 25	RD

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.

●Dimension table in next page.

VR series

■Dimensions

Cap.(μF) \ V / Code	6.3		10		16		25		35		50		63		100	
	0J		1A		1C		1E		1V		1H		1J		2A	
0.1	0R1										• 5 × 11	1.3			5 × 11	2.1
0.22	R22										• 5 × 11	2.9			5 × 11	4.7
0.33	R33										• 5 × 11	4.3			5 × 11	7
0.47	R47										• 5 × 11	6.2			5 × 11	10
1	010										• 5 × 11	17			5 × 11	21
2.2	2R2										• 5 × 11	28			5 × 11	30
3.3	3R3										• 5 × 11	35			5 × 11	40
4.7	4R7						• 5 × 11	35	• 5 × 11	40	• 5 × 11	40			5 × 11	45
10	100				• 5 × 11	50	• 5 × 11	55	• 5 × 11	60	• 5 × 11	60	5 × 11	65	6.3 × 11	75
22	220	• 5 × 11	65	• 5 × 11	65	• 5 × 11	75	• 5 × 11	80	• 5 × 11	90	5 × 11	95	5 × 11	100	6.3 × 11	130
33	330	• 5 × 11	80	• 5 × 11	85	• 5 × 11	90	• 5 × 11	95	5 × 11	105	5 × 11	125	6.3 × 11	140	8 × 11.5	180
47	470	• 5 × 11	95	• 5 × 11	100	• 5 × 11	110	• 5 × 11	115	5 × 11	130	6.3 × 11	155	6.3 × 11	170	10 × 12.5	230
100	101	• 5 × 11	135	• 5 × 11	145	5 × 11	160	6.3 × 11	190	6.3 × 11	210	8 × 11.5	260	10 × 12.5	300	10 × 20	370
220	221	5 × 11	200	6.3 × 11	240	6.3 × 11	260	8 × 11.5	330	10 × 12.5	385	10 × 12.5	430	10 × 16	490	12.5 × 25	620
330	331	6.3 × 11	270	6.3 × 11	290	8 × 11.5	370	10 × 12.5	440	10 × 12.5	490	10 × 16	590	10 × 20	710	12.5 × 25	760
470	471	6.3 × 11	320	6.3 × 11	350	8 × 11.5	440	10 × 12.5	550	10 × 16	650	12.5 × 20	760	12.5 × 20	900	16 × 25	1000
1000	102	8 × 11.5	540	10 × 12.5	650	10 × 16	790	10 × 20	960	12.5 × 20	1150	12.5 × 25	1350	16 × 25	1300	18 × 40	1380
2200	222	10 × 20	1000	10 × 20	1100	12.5 × 20	1300	12.5 × 25	1550	16 × 25	1800	16 × 35.5	2100	18 × 35.5	2300	22 × 50	2400
																▲25 × 40	2400
3300	332	10 × 20	1190	12.5 × 20	1450	12.5 × 25	1700	16 × 25	1980	16 × 35.5	2280	18 × 35.5	2500	20 × 40	2700	25 × 50	2900
												▲22 × 30	2450	▲25 × 30	2600		
4700	472	12.5 × 20	1550	12.5 × 25	1800	16 × 25	2100	16 × 31.5	2450	18 × 35.5	2700	20 × 40	2900	22 × 50	3400		
										▲20 × 31		▲25 × 30	2900	▲25 × 40	3200		
6800	682	12.5 × 25	1920	16 × 25	2250	16 × 35.5	2650	18 × 35.5	2900	20 × 40	3000	22 × 50	3500	25 × 50	3900		
								▲20 × 31	2700	▲25 × 30	2900	▲25 × 40	3300				
10000	103	16 × 25	2350	16 × 35.5	2700	18 × 35.5	2950	20 × 40	3000	22 × 50	3700	25 × 50	4000				
						▲20 × 31	3000	▲25 × 30	2900	▲25 × 40	3600						
15000	153	16 × 35.5	2850	18 × 35.5	3100	20 × 40	3400	22 × 50	3800	25 × 50	4300						
						▲25 × 30	3300	▲25 × 40	3600								
22000	223	18 × 40	3350	20 × 40	3700	22 × 50	4200	25 × 50	4500								
		▲22 × 30	3200	▲25 × 30	3300	▲25 × 40	4000										
33000	333	22 × 50	3900	22 × 50	4500	25 × 50	4800									Case size φD × L (mm)	Rated ripple
		▲25 × 40	3800	▲25 × 40	4800												

Cap.(μF) \ V / Code	160		200		250		315		350		400		450	
	2C		2D		2E		2F		2V		2G		2W	
0.47	R47	6.3 × 11	15	6.3 × 11	15	6.3 × 11	15							
1	010	6.3 × 11	22	6.3 × 11	22	6.3 × 11	22	6.3 × 11	22	6.3 × 11	22	8 × 11.5	25	8 × 11.5	23
2.2	2R2	6.3 × 11	33	6.3 × 11	33	6.3 × 11	33	8 × 11.5	33	8 × 11.5	38	10 × 12.5	45	10 × 12.5	35
3.3	3R3	6.3 × 11	40	6.3 × 11	40	8 × 11.5	46	10 × 12.5	55	10 × 12.5	55	10 × 12.5	55	10 × 16	45
4.7	4R7	6.3 × 11	50	8 × 11.5	55	8 × 11.5	55	10 × 12.5	65	10 × 12.5	65	10 × 16	70	10 × 20	55
10	100	8 × 11.5	80	10 × 12.5	95	10 × 16	105	10 × 20	115	10 × 20	115	12.5 × 20	130	12.5 × 20	90
22	220	10 × 16	155	10 × 20	170	12.5 × 20	190	12.5 × 20	190	12.5 × 25	200	16 × 25	240	16 × 25	165
33	330	10 × 20	205	12.5 × 20	230	12.5 × 20	230	16 × 25	275	16 × 25	275	16 × 31.5	300	16 × 35.5	230
47	470	12.5 × 20	270	12.5 × 20	270	12.5 × 25	300	16 × 25	340	16 × 35.5	380	16 × 35.5	370	18 × 40	300
														▲22 × 30	290
100	101	12.5 × 25	430	16 × 31.5	530	16 × 31.5	520	18 × 35.5	560	18 × 40	590	20 × 40	550	22 × 40	350
										▲22 × 30	570	▲25 × 30	530		
220	221	16 × 35.5	800	18 × 35.5	810	20 × 40	740	22 × 50	850	22 × 50	850	25 × 50	750		
						▲22 × 30	820	▲25 × 30	770	▲25 × 40	890				
330	331	18 × 40	940	20 × 40	1130	22 × 50	1170	25 × 50	1250						
		▲22 × 30	900	▲25 × 30	1090	▲25 × 30	970								
470	471	22 × 40	1410	22 × 50	1490	25 × 50	1600							Case size φD × L (mm)	Rated ripple
		▲25 × 30	1290	▲25 × 40	1550										
1000	102	25 × 50	1900												

Size 4×11 is available for capacitors marked "•"
In this case, 6 will be put at 12th digit of type numbering system "▲"

Rated ripple current (mArms) at 85˚C 120Hz

● Frequency coefficient of rated ripple current

V	Cap.(μF) \ Frequency	50Hz	120Hz	300Hz	1 kHz	10kHz or more
6.3 to 100	0.1 to 47	0.75	1.00	1.35	1.57	2.00
	100 to 470	0.80	1.00	1.23	1.34	1.50
	1000 to 33000	0.85	1.00	1.10	1.13	1.15
160 to 450	0.47 to 220	0.80	1.00	1.25	1.40	1.60
	330 to 1000	0.90	1.00	1.10	1.13	1.15

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

UVR0J102MPA UVR0J102MPA1TA UVR0J102MPA1TD UVR0J472MHA UVR0J682MHA UVR0J101MDA UVR0J101MDA1TA UVR0J222MPA UVR0J223MHA UVR0J221MDA UVR0J103MHA UVR0J153MHA UVR0J331MEA UVR0J332MPA UVR1A101MDA UVR1A101MDA1TA UVR1A101MDA1TD UVR1A221MEA UVR1A221MEA1TD UVR1A222MPA UVR1A470MDA UVR1A470MDA1TA UVR1A470MDA1TD UVR1C102MPA1TD UVR1C103MHA UVR1C152MPA1TD UVR1C153MRA UVR1C330MDA UVR1C330MDA1TD UVR0J471MEA UVR1A332MHA UVR1C101MDA UVR1C101MDA1TA UVR1C101MDA1TD UVR1C102MPA UVR1C102MPA1AA UVR1A102MPA UVR1A102MPA1TD UVR1A103MHA UVR1A153MHA UVR1A331MEA UVR1A682MHA UVR1C100MDA UVR1C100MDA1TD UVR1C221MEA UVR1C221MEA1TD UVR1A471MEA UVR1A472MHA UVR1C220MDA UVR1C331MPA UVR1C332MHA UVR1C332MHA1TO UVR1C681MPA UVR1C682MHA UVR1E100MDA UVR1E100MDA1TA UVR1E100MDA1TD UVR1E221MPA UVR1E221MPA1TA UVR1E471MPA UVR1E471MPA1TD UVR1E472MHA UVR1E4R7MDA UVR1H100MDA UVR1H100MDA1TA UVR1H100MDA1TD UVR1C222MHA UVR1C222MHA1TO UVR1C471MPA UVR1C471MPA1TA UVR1C471MPA1TD UVR1C472MHA UVR1E220MDA UVR1E220MDA1TD UVR1E332MHA UVR1E332MHA1AA UVR1E470MDA UVR1E470MDA1TA UVR1E470MDA1TD UVR1C470MDA UVR1C470MDA1TD UVR1E102MPA1TD UVR1E103MRA UVR1E103MRA6 UVR1E330MDA1TA UVR1E330MDA1TD UVR1E331MPA UVR1E331MPA1TD UVR1H010MDA UVR1H010MDA1TA UVR1H010MDA1TD UVR1E101MEA UVR1E101MEA1TA UVR1E101MEA1TD UVR1E102MPA UVR1E102MPA1AA UVR1E222MHA UVR1E222MHA1TO UVR1E330MDA UVR1E4R7MDA1TD