


Inductive Proximity Sensor with Chemical-resistant Fluororesin Case

- Housing and mounting are made of Fluororesin resistant to chemicals.
- Maximum sensing distance: 10 mm.




Be sure to read *Safety Precautions* on page 5.

Note: The cable is made of vinyl chloride and requires separate protection.

Ordering Information

Sensors [Refer to *Dimensions* on page 6.]

Appearance	Sensing distance	Output configuration	Operation mode	Model
Shielded 	M12	2 mm	NO	DC 2-wire
				DC 3-wire, NPN
	M18	5 mm		DC 2-wire
				DC 3-wire, NPN
				AC 2-wire
	M30	10 mm		DC 2-wire
				DC 3-wire, NPN
				AC 2-wire
				E2FQ-X2D1 2M
				E2FQ-X2E1 2M
				E2FQ-X5D1 2M
				E2FQ-X5E1 2M
				E2FQ-X5Y1 2M
				E2FQ-X10D1 2M
				E2FQ-X10E1 2M
				E2FQ-X10Y1 2M

Ratings and Specifications

Model		E2FQ-X2E1 E2FQ-X2D1	E2FQ-X5E1 E2FQ-X5D1, E2FQ-X5Y1	E2FQ-X10E1 E2FQ-X10D1, E2FQ-X10Y1
Item				
Sensing distance		2 mm ±10%	5 mm ±10%	10 mm ±10%
Set distance		0 to 1.6 mm	0 to 4 mm	0 to 8 mm
Differential travel		E1/Y1 Models: 10% max. of sensing distance, D1 Models: 20% max. of sensing distance		
Detectable object		Ferrous metal (The sensing distance decreases with non-ferrous metal. Refer to <i>Engineering Data</i> on page 3.)		
Standard sensing object		Iron, 12 × 12 × 1 mm	Iron, 18 × 18 × 1 mm	Iron, 30 × 30 × 1 mm
Response frequency *		E1 Models: 1.5 kHz D1 Models: 800 Hz	E1 Models: 600 Hz D1 Models: 500 Hz	E1 Models: 400 Hz D1 Models: 300 Hz
			Y1 Models: 25 Hz	
Power supply voltage (operating voltage range)		E1 Models: 12 to 24 VDC (10 to 30 VDC), ripple (p-p): 10% max. Y1 Models: 24 to 240 VAC (20 to 264 VAC), 50/60 Hz D1 Models: 12 to 24 VDC (10 to 36 VDC), ripple (p-p): 20% max.		
Current consumption		E1 Models: 17 mA max.		
Leakage current		D1 Models: 0.8 mA max., Y1 Models: 1.7 mA max. (at 200 VAC)		
Control output	Load current	E1 Models: 200 mA max., D1 Models: 5 to 100 mA, Y1 Models: 5 to 300 mA		
	Residual voltage	E1 Models: 2 V max. (Load current: 200 mA, Cable length: 2 m) Y1 Models: Refer to <i>Engineering Data</i> on page 3. D1 Models: 4 V max. (Load current: 100 mA, Cable length: 2 m)		
Indicators		E/D Models: Detection indicator (red), Y Models: Operation indicator (red)		
Operation mode (with sensing object approaching)		E1/D1/Y1 Models: NO (Refer to the timing charts under <i>I/O Circuit Diagrams</i> on page 5 for details.)		
Protection circuits		E1 Models: Load short-circuit protection, Reverse polarity protection, Surge suppressor, D1/Y1 Models: Surge suppressor		
Ambient temperature range		Operating/Storage: −25 to 70°C (with no icing or condensation)		
Ambient humidity range		Operating/Storage: 35% to 95% (with no condensation)		
Temperature influence		±10% max. of sensing distance at 23°C in the temperature range of −25 to 70°C		
Voltage influence		E1 Models: ±2.5% max. of sensing distance at rated voltage in the rated voltage ±15% range D1 Models: ±2.5% max. of sensing distance at rated voltage in the rated voltage ±20% range Y1 Models: ±1% max. of sensing distance at rated voltage in the rated voltage ±10% range		
Insulation resistance		50 MΩ min. (at 500 VDC) between current-carrying parts and case		
Dielectric strength		E1/D1 Models: 1,000 VAC, 50/60 Hz for 1 min between current-carrying parts and case Y Models: 4,000 VAC, 50/60 Hz for 1 min between current-carrying parts and case		
Vibration resistance		Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions		
Shock resistance		Destruction: 500 m/s ² 10 times each in X, Y, and Z directions	Destruction: 1,000 m/s ² 10 times each in X, Y, and Z directions	
Degree of protection		IEC 60529 IP67, in-house standards: oil-resistant		
Connection method		Pre-wired Models (Cable length: 2 m)		
Weight (packed state)		Approx. 70 g	Approx. 130 g	Approx. 170 g
Materials	Case	Fluororesin		
	Sensing surface			
	Clamping nuts			
	Toothed washer	Zinc-plated iron		
	Cable	Vinyl chloride		
Accessories		Instruction manual		


* The response frequency is an average value.

Measurement conditions are as follows: standard sensing object, a distance of twice the standard sensing object, and a set distance of half the sensing distance.

Engineering Data (Typical)


Sensing Area

E2FQ-X□




Influence of Sensing Object Size and Material


E2FQ-X2□



E2FQ-X5□




E2FQ-X10□




Residual Output Voltage


E2FQ-X□




E2FQ-X□Y1 at 24 VAC



E2FQ-X□Y1 at 100 VAC




E2FQ-X□Y1 at 200 VAC




Leakage Current

E2FQ-X□D



E2FQ-X□Y



I/O Circuit Diagrams

Operation mode	Output configuration	Model	Timing chart	Output circuit
NO	NPN	E2FQ-X2E1 E2FQ-X5E1 E2FQ-X10E1	Sensing object Present Not present Load (between brown and black leads) Operate Reset Output voltage (between black and blue leads) H L Detection indicator (red) ON OFF	<p>*1. 200 mA max. (load current). *2. When a transistor is connected.</p>
	DC 2-wire	E2FQ-X2D1 E2FQ-X5D1 E2FQ-X10D1	Sensing object Present Not present Load Operate Reset Detection indicator (red) ON OFF	<p>Note: The load can be connected to either the +V or 0 V side.</p>
	AC 2-wire	E2FQ-X5Y1 E2FQ-X10Y1	Sensing object Present Not present Load Operate Reset Operation indicator (red) ON OFF	

Safety Precautions

Refer to *Warranty and Limitations of Liability*.

⚠ WARNING

This product is not designed or rated for ensuring safety of persons either directly or indirectly. Do not use it for such purposes.




Precautions for Correct Use

Do not use this product under ambient conditions that exceed the ratings.

● Design

Influence of Surrounding Metal

When mounting the Sensor within a metal panel, ensure that the clearances given in the following table are maintained. Failure to maintain these distances may cause deterioration in the performance of the Sensor.



Influence of Surrounding Metal

(Unit: mm)


Model	Item	l	d	D	m	n
E2FQ-X2□	0	12	0	0	8	18
E2FQ-X5□		18			20	27
E2FQ-X10□		30			40	45

Mutual Interference

When installing two or more Sensors face-to-face or side-by-side, ensure that the minimum distances given in the following table are maintained.

Mutual Interference (Unit: mm)

Model	Item	A	B
E2FQ-X2□		30	20
E2FQ-X5□		50	35
E2FQ-X10□		100	70



Mounting

Do not tighten the nut with excessive force. A washer must be used with the nut.



Note: The following torque assume washers are being used.

Model	Torque
E2FQ-X2□	0.98 N·m
E2FQ-X5□	2 N·m
E2FQ-X10□	

Miscellaneous


Chemical Resistance

Refer to *Chemical Resistance* for details.

Dimensions


Tolerance class IT16 applies to dimensions in this data sheet unless otherwise specified.

E2FQ-X2E1




* 6-dia. vinyl-insulated round cable with 3 conductors (Flame resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m
The cable can be extended up to 200 m (separate metal conduit).

E2FQ-X2D1




* 6-dia. vinyl-insulated round cable with 2 conductors (Flame resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m
The cable can be extended up to 200 m (separate metal conduit).

E2FQ-X5E1



* 6-dia. vinyl-insulated round cable with 3 conductors (Flame resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m
The cable can be extended up to 200 m (separate metal conduit).


E2FQ-X5D1
E2FQ-X5Y1



*1. 6-dia. vinyl-insulated round cable with 2 conductors (Flame-resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m
The cable can be extended up to 200 m (separate metal conduit).


*2. D Models: Detection indicator, Y Models: Operation indicator

E2FQ-X10E1



* 6-dia. vinyl-insulated round cable with 3 conductors (Flame resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m
The cable can be extended up to 200 m (separate metal conduit).


E2FQ-X10D1
E2FQ-X10Y1



*1. 6-dia. vinyl-insulated round cable with 2 conductors (Flame-resistant, Conductor cross section: 0.5 mm², Insulator diameter: 1.9 mm), Standard length: 2 m
The cable can be extended up to 200 m (separate metal conduit).

*2. D Models: Detection indicator, Y Models: Operation indicator

Mounting Hole Dimensions



Model	F (mm)
E2FQ-X2□	12.5 ^{+0.5} ₀ dia.
E2FQ-X5□	18.5 ^{+0.5} ₀ dia.
E2FQ-X10□	30.5 ^{+0.5} ₀ dia.

Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments.

Warranty and Limitations of Liability

WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall the responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

Application Considerations

SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the products.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety equipment, and installations subject to separate industry or government regulations.
- Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCTS ARE PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

Disclaimers

CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the products may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased products.

DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

ERRORS AND OMISSIONS

The information in this document has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.

2008.11

In the interest of product improvement, specifications are subject to change without notice.

OMRON Corporation
Industrial Automation Company

<http://www.ia.omron.com/>

(c)Copyright OMRON Corporation 2008 All Right Reserved.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

[E2FQ-X10D1](#) [E2FQ-X10D1-5M](#) [E2FQ-X10E1](#) [E2FQ-X10E1-5M](#) [E2FQ-X10Y1](#) [E2FQ-X10Y1-5M](#) [E2FQ-X2D1](#)
[E2FQ-X2D1-5M](#) [E2FQ-X2E1](#) [E2FQ-X2E1-2 5M](#) [E2FQ-X2E1-5M](#) [E2FQ-X5D1](#) [E2FQ-X5D1-5M](#) [E2FQ-X5E1](#) [E2FQ-X5E1-5M](#) [E2FQ-X5Y1](#) [E2FQ-X5Y1-5M](#)