


FODB100

FODB101

FODB102

DESCRIPTION

The FODB100, FODB101 and FODB102 single channel MICROCOUPLERS™ are all Pb-free, low profile miniature surface mount optocouplers in a Ball Grid Array (BGA) package. Each consists of an aluminum gallium arsenide (AlGaAs) infrared emitting diode driving a silicon phototransistor.




FEATURES

- Low profile package (1.20mm maximum mounted height)
- Land pattern allows for optimum board space savings
- High Current Transfer Ratio (CTR) at low IF
- Minimum isolation distance of 0.45mm
- High steady state isolation voltage of 2500V_{rms}
- Data rates up to 120Kbit/s (NRZ)
- Minimum creepage distance of 2mm
- Wide operating temperature range of -40°C to +125°C
- Available in tape and reel quantities of 3000 units
- Applicable to Pb-free Infrared Ray reflow (260°C max)
- UL, C-UL approved; VDE pending


APPLICATIONS

- Primarily suited for DC-DC converters
- For ground loop isolation, signal to noise isolation
- Communications – chargers, adapters
- Consumer – appliances, set top boxes
- Industrial – power supplies, motor control

SCHEMATIC



PACKAGE DIMENSIONS



FODB100

FODB101

FODB102

ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise specified)			
Parameter	Symbol	Value	Units
TOTAL PACKAGE			
Storage Temperature	T _{STG}	-55 to +150	°C
Operating Temperature	T _{OPR}	-40 to +125	°C
Junction Temperature	T _j	130	°C
EMITTER			
Continuous Forward Current	I _{F (avg)}	30	mA
Reverse Input Voltage	V _R	6	V
Power Dissipation Derate linearly (above 25°C)	P _D	40	mW
		0.39	mW/°C
DETECTOR			
Continuous Collector Current		50	mA
Power Dissipation Derate linearly (above 25°C)	P _D	150	mW
		1.42	mW/°C
Collector-Emitter Voltage	V _{CEO}	75	V
Emitter-Collector Voltage	V _{ECO}	7	V

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$)						
INDIVIDUAL COMPONENT CHARACTERISTICS						
Parameter	Test Conditions	Symbol	Min	Typ**	Max	Unit
EMITTER						
Forward Voltage	($I_F = 2 \text{ mA}$)	V_F	1.0		1.5	V
Reverse Current	($V_R = 6 \text{ V}$)	I_R			10	μA
DETECTOR						
Breakdown Voltage Collector to Emitter	($I_C = 100 \mu\text{A}$, $I_F = 0$)	BV_{CEO}	75			V
Emitter to Collector	($I_E = 100 \mu\text{A}$, $I_F = 0$)	BV_{ECO}	7			
Collector Dark Current	($V_{\text{CE}} = 75 \text{ V}$, $I_F = 0$)	I_{CEO}			100	nA
Capacitance	($V_{\text{CE}} = 0 \text{ V}$, $f = 1 \text{ MHz}$)	C_{CE}		8		pF

FODB100

FODB101

FODB102

TRANSFER CHARACTERISTICS ($T_A = 25^\circ\text{C}$)						
Characteristic	Test Conditions	Symbol	Min	Typ**	Max	Unit
Current Transfer Ratio ¹	($I_F = 1\text{ mA}$, $V_{CE} = 5\text{ V}$)	CTR	100			%
Saturated Current Transfer Ratio (Collector to Emitter)	($I_F = 1.6\text{ mA}$, $V_{CE} = 0.4\text{ V}$)	$CTR_{CE(SAT)}$	100			%
	($I_F = 1.0\text{ mA}$, $V_{CE} = 0.4\text{ V}$)		75			
Saturation Voltage	($I_F = 3.0\text{ mA}$, $I_C = 1.8\text{ mA}$) ($I_F = 1.6\text{ mA}$, $I_C = 1.6\text{ mA}$)	$V_{CE(SAT)}$			0.4	V
Rise Time (Non-Saturated)	($I_C = 2\text{ mA}$, $V_{CE} = 5\text{ V}$) ($R_L = 1\text{ K}\Omega$)	t_r		1		μs
Fall Time (Non-Saturated)	($I_C = 2\text{ mA}$, $V_{CE} = 5\text{ V}$) ($R_L = 1\text{ K}\Omega$)	t_f		5		
Propagation Delay High to Low	$I_F = 1.6\text{ mA}$, $V_{CC} = 5.0\text{ V}$ $R_L = 750\Omega$	T_{PHL}		3		μs
	$I_F = 1.6\text{ mA}$, $V_{CC} = 5.0\text{ V}$ $R_L = 4.7\text{ K}\Omega$			12		
Propagation Delay Low to High	$I_F = 1.6\text{ mA}$, $V_{CC} = 5.0\text{ V}$ $R_L = 750\Omega$	T_{PLH}		5		μs
	$I_F = 1.6\text{ mA}$, $V_{CC} = 5.0\text{ V}$ $R_L = 4.7\text{ K}\Omega$			19		

ISOLATION CHARACTERISTICS						
Characteristic	Test Conditions	Symbol	Min	Typ**	Max	Unit
Steady State Isolation Voltage ²	($R_H \leq 50\%$, $T_A = 25^\circ\text{C}$, $t = 1\text{ sec}$)	V_{ISO}	2500			V(rms)
Resistance (input to output) ²	($V_{I-O} = 500\text{ VDC}$)	R_{ISO}	10^{12}			Ω
Capacitance (input to output) ²	$f = 1\text{ MHz}$	C_{ISO}		0.3	0.5	pF

Notes:

1. CTR bin (FODB100 only)

FODB101: 100% – 200%

FODB102: 150% – 300%

2. Pin 1 and Pin 2 are shorted as input and Pin 3 and Pin 4 are shorted as output.

FODB100

FODB101

FODB102

TYPICAL PERFORMANCE CURVES

Fig. 1 Normalized CTR vs. Temperature (VCE = 2V)




Fig. 2 Normalized CTR vs. Temperature (VCE = 5V)




Fig. 3 Current Transfer Ratio vs. Collector to Emitter Voltage




Fig. 4 Current Transfer Ratio vs. Collector Saturation Voltage






Fig. 5 Baud Rate vs. Load Resistor






TAPE AND REEL SPECIFICATIONS

Embossed Carrier Tape Configuration




Dimensions are in millimeter														
Pkg type	A_0	B_0	W	D_0	D_1	E_1	E_2	F	P_1	P_0	K_0	T	W_c	T_c
Optocoupler (12mm)	3.80 ± 0.10	3.80 ± 0.10	12.0 $+0.3/-0.1$	1.50 $+0.25/-0.00$	1.50 $+0.25/-0.00$	1.75 ± 0.10	10.25 min	5.50 ± 0.05	8.0 ± 0.1	4.0 ± 0.1	1.40 ± 0.10	0.279 ± 0.02	9.2 ± 0.3	0.06 ± 0.02

Notes: A_0 , B_0 , and K_0 dimensions are determined with respect to the EIA/Jedec RS-481 rotational and lateral movement requirements (see sketches A, B, and C).



Optocoupler Reel Configuration




Dimension are in inches and millimeters									
Tape Size	Reel Option	Dim A	Dim B	Dim C	Dim D	Dim N	Dim W1	Dim W2	Dim W3 (LSL-USL)
12mm	13" Dia	13.00 330	0.059 1.5	512 $+0.020/-0.008$ 13 $+0.5/-0.2$	0.795 20.2	7.00 178	0.488 $+0.078/-0.000$ 12.4 $+2/-0$	0.724 18.4	0.469 - 0.606 11.9 - 15.4

FODB100

FODB101

FODB102


MARKING INFORMATION



Definitions	
1	Fairchild logo
2	Device number (FODB100)
3	One digit year code e.g. "4" for 2004
4	6-week date code character
5	Die Run Code
6	Assembly package code
7	VDE 0884 approved (Optional)

Note: The device number prefix of "FOD" will be omitted in the part number


RECOMMENDED FOOTPRINT DRAWING FOR PCB LAYOUT



Note:

1. All dimensions in millimeters (mm)
2. It is recommended to use 6 mils of stencil thickness on PCB

RECOMMENDED INFRARED REFLOW SOLDERING PROFILE



Reflow Profile for Pb Free

	Convection Reflow
Average ramp-up rate (183°C to peak)	3°C/sec max
Preheat Temperature 125(±25)°C to 200°C	60-180°C
Temperature maintained above 220°C	60-150 sec
Time within 5°C of actual peak temperature	20-40 sec
Peak temperature range	260 ±5°C
Ramp down rate	6°C/sec max
Time 25°C to peak temperature	8min max

Note: Surface Mount Adhesives (SMA) isn't recommended to be used on the dome area (white dome).

FODB100

FODB101

FODB102

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.