







SECTION A-A



mat'l. code				surface	tolerance	projection	product family	
				ISO 1302	ISO 406 ISO 1101		HEADERS	
ltr	ecn no	dr	date	tolerances unless otherwise specified			title	
B	V13090	JWB	10/3/91	angles	.XX±.01/.3		VERTICAL STACKING 2 ROW HEADER	
C	v30274	JWB	2/1/93	linear	.XXX±.005/.13	INCH/MM	.680/17.27 W/O MOUNTING HOLES	
D	V50568	LSS	8/17/95	0°±2°	.xxxx±.0020/.051	scale 1:1	dwg no	
E	M05-0089	ERE	5/20/05	dr	J.W. BAIR	9/18/91	sheet 1 of 2	
F	M07-0116	AGS	2/24/07	enr	S. AURAND	9/18/91	68575	
				chr	E. IORFIDO	2/1/93	A3	
				appd	E. IORFIDO	2/1/93	type Product Customer Drawing	
sheet index	revision sheet	F	F	1	2			

PRODUCT NO. NOTE 6	SIZE	DIM B	DIM C	OVERALL LENGTH DIM L
68575-001	2X5	.400/10.16	.53/13.5	.61/15.5
-002	2X6	.500/12.70	.63/16.0	.71/18.0
-003	2X7	.600/15.24	.73/18.5	.81/20.6
-004	2X8	.700/17.78	.83/21.1	.91/23.1
-005	2X9	.800/20.32	.93/23.6	1.01/25.7
-006	2X10	.900/22.86	1.03/26.2	1.11/28.2
-007	2X11	1.000/25.40	1.13/28.7	1.21/30.7
-008	2X12	1.100/27.94	1.23/31.2	1.31/33.3
-009	2X13	1.200/30.48	1.33/33.8	1.41/35.8
-010	2X14	1.300/33.02	1.43/36.3	1.51/38.4
-011	2X15	1.400/35.56	1.53/38.9	1.61/40.9
-012	2X16	1.500/38.10	1.63/41.4	1.71/43.4
-013	2X17	1.600/40.64	1.73/43.9	1.81/46.0
-014	2X18	1.700/43.18	1.83/46.5	1.91/48.5
-015	2X19	1.800/45.72	1.93/49.0	2.01/51.1
-016	2X20	1.900/48.26	2.03/51.6	2.11/53.6
-017	2X21	2.000/50.80	2.13/54.1	2.21/56.1
-018	2X22	2.100/53.34	2.23/56.6	2.31/58.7
-019	2X23	2.200/55.88	2.33/59.2	2.41/61.2
-020	2X24	2.300/58.42	2.43/61.7	2.51/63.8
-021	2X25	2.400/60.96	2.53/64.3	2.61/66.3
-022	2X26	2.500/63.50	2.63/66.8	2.71/68.8
-023	2X27	2.600/66.04	2.73/69.3	2.81/71.4
-024	2X28	2.700/68.58	2.83/71.9	2.91/73.9
-025	2X29	2.800/71.12	2.93/74.4	3.01/76.5
-026	2X30	2.900/73.66	3.03/77.0	3.11/79.0
-027	2X31	3.000/76.20	3.13/79.5	3.21/81.5
-028	2X32	3.100/78.74	3.23/82.0	3.31/84.1
-029	2X33	3.200/81.28	3.33/84.6	3.41/86.6
-030	2X34	3.300/83.82	3.43/87.1	3.51/89.2
-031	2X35	3.400/86.36	3.53/89.7	3.61/91.7
68575-032	2X36	3.500/88.90	3.63/92.2	3.71/94.2



RECOMMENDED PC BOARD LAYOUT

NOTES:

1. MOLDING MATERIAL: 20% MIN GLASS FILLED NYLON PER UL-94V-0, COLOR-BLACK.
2. TERMINAL MATERIAL: 3/4 HARD PHOS BRONZE ALLOY UNS C51000
3. TERMINAL PLATING 15u"/0.38u Au OVER 50u"/1.27u Ni
4. PIN RETENTION TO BE 3 LBS/1.4 KG MIN PER PIN IN EITHER DIRECTION.
- ⑤ COMPANY LOGO TO BE MOLDED IN APPROX LOCATION SHOWN.
- ⑥ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
7. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
- ⑧ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑨ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code					surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS					
ltr	ecn	no	dr	date	tolerances unless otherwise specified					INCH/MM		title				
F					angles	linear	.XX±.01/.3 .XXX±.005/.13 .XXXX±.0020/.051					VERTICAL STACKING 2 ROW HEADER				
					0°±2'					scale 1:1		.680/17.27 W/O MOUNTING HOLES				
					dr	J.W. BAIR	9/18/91				dwg no		sheet2 of 2		size	
					enrg	S. AURAND	9/18/91				68575		A3			
					chr	E. IORFIDO	2/1/93									
					appd	E. IORFIDO	2/1/93									
sheet index		revision sheet														

form: A3