



REV.	DATE	ECR NO.	DESCRIPTION
NC	01/31/12	XXXXXX	INITIAL RELEASE






TOP VIEW

RECOMMENDED PCB LAYOUT



BOTTOM VIEW



- FREQUENCY RANGE: DC-18 GHZ
- VSWR: NOT APPLICABLE
- DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS, MIN.
- DURABILITY: 500 CYCLES MIN.
- TEMPERATURE RANGE: -65°C TO +165°C
- CONTACT PIN MUST WITHSTAND 6 LBS MIN. AXIAL IN BOTH DIRECTIONS AND 4 IN-OZ MIN. RADIAL FORCE.
- BOARD THICKNESS=0.81 MM [.032"]

3	CONTACT PIN	BER. COPPER	GOLD	1
2	INSULATOR	PTFE	NATURAL	1
1	BODY	BRASS	GOLD	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20mm
8 - 30mm ± 0.40mm
30 - 120mm ± 0.50mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007"
.315 - 1.180 = ± 0.015"
1.180 - 4.724 = ± 0.020"

DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN M.ZHANG	01/31/12
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE C:/CONNEX/132432.DWG	

Amphenol Connex

PART DESCRIPTION

SMA END LAUNCH RECEPT. JACK
FLUSH FLANGE (.032" BOARD THICKNESS)

PART NO.

132432

DWG. NO. 132432.DWG

REV. NC

SIZE A

SCALE NA