






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		F	REVISED PER ECR-12-013486	08JAN13	KH	KR


SUGGESTED MATING TAB




- MATL: ½H BRASS OR NICKEL PL STEEL.
 - NO BURRS PERMISSIBLE AT HOLE.
 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225°F
 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



SECTION B-B




VIEW A-A



SECTION C-C

- CONTINUOUS STRIP ON REELS.
- WIRE SIZE IS [#18-#14] AWG.
- THE 1.40 [.055] / 1.27 [.050] DIMENSION MUST BE MAINTAINED BY THE APPLICATOR CUT-OFF TO ENSURE THE PROPER LOCKING FUNCTION OF THE RECEPTACLE.
- INSULATION RANGE IS 2.29-3.94 [.090-.155] DIA.

63442-1
PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN	JR RUTH	10/29/98	 TE Connectivity			
			CHK	MS FEHER	10/29/98				
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	D DECKER	10/29/98	NAME RECEPTACLE, POSI-LOCK, 6.35 [.250] SERIES		
		0 PLC ± -		PRODUCT SPEC					
		1 PLC ± -		—					
		2 PLC ± 0.25 [.010]		—					
		3 PLC ± -		APPLICATION SPEC		SIZE A2			
		4 PLC ± -		—					CAGE CODE 00779
		ANGLES ± -		—		DRAWING NO C-63442			
MATERIAL BRASS		FINISH TIN		WEIGHT —					RESTRICTED TO —
				CUSTOMER DRAWING		SCALE 4:1			
									SHEET 1 of 1
						REV F			