



## LM7800 Series 3-Terminal Positive Voltage Regulators


### General Description

The LM7800 series of monolithic 3-terminal positive voltage regulators employ internal current-limiting, thermal shut-down and safe-area compensation, making them essentially indestructible. If adequate heat sinking is provided, they can deliver over 1.0A output current. They are intended as fixed voltage regulators in a wide range of applications including local (on-card) regulation for elimination of noise and distribution problems associated with single-point regulation. In addition to use as fixed voltage regulators, these devices can be used with external components to obtain adjustable output voltages and currents.

### Features

- Output current in excess of 1.0A
- No external components
- Internal thermal overload protection
- Internal short circuit current-limiting
- Output transistor safe-area compensation
- Available in JEDEC TO-220 and TO-3 packages
- Output voltages of 6V, 8V, 18V and 24V (See Note)
- Available in extended temperature range


### Connection Diagrams



TL/H/10052-1

Top View

Order Number LM7806K, LM7808K, LM7818K,  
LM7824K, LM7806CK, LM7808CK,  
LM7818CK or LM7824CK  
See NS Package Number K02A



Lead 3 connected to tab.

TL/H/10052-2

Top View

Order Number LM7806CT, LM7808CT  
LM7818CT or LM7824CT  
See NS Package Number T03B

**Note:** See General Purpose Linear Databook for specifications on similar devices with 5V, 12V, or 15V outputs. These parts can be found under LM140/LM340, LM140A/LM340A (for tighter output tolerance) and LM78XX datasheets.

## Absolute Maximum Ratings

If Military/Aerospace specified devices are required, please contact the National Semiconductor Sales Office/Distributors for availability and specifications.

### Storage Temperature Range

|                |                 |
|----------------|-----------------|
| TO-3 Metal Can | −65°C to +175°C |
| TO-220 Package | −65°C to +150°C |

### Operating Junction Temperature Range

|                      |                 |
|----------------------|-----------------|
| Extended (LM7800)    | −55°C to +150°C |
| Commercial (LM7800C) | 0°C to +150°C   |

### Lead Temperature

|                                     |       |
|-------------------------------------|-------|
| TO-3 Metal Can (Soldering, 60 sec.) | 300°C |
| TO-220 Package (Soldering, 10 sec.) | 265°C |

### Power Dissipation

Internally Limited

### Input Voltage

|             |     |
|-------------|-----|
| 6.0V to 18V | 35V |
| 24V         | 40V |

### ESD Susceptibility

(to be determined)

## LM7806C

### Electrical Characteristics

0°C ≤ T<sub>A</sub> ≤ +125°C, V<sub>I</sub> = 11V, I<sub>O</sub> = 500 mA, C<sub>I</sub> = 0.33 μF, C<sub>O</sub> = 0.1 μF, unless otherwise specified

| Symbol                           | Parameter                                         | Conditions (Note 1)                                                  | Min                            | Typ | Max  | Units |
|----------------------------------|---------------------------------------------------|----------------------------------------------------------------------|--------------------------------|-----|------|-------|
| V <sub>O</sub>                   | Output Voltage                                    | T <sub>J</sub> = 25°C                                                | 5.75                           | 6.0 | 6.25 | V     |
| V <sub>R LINE</sub>              | Line Regulation                                   | T <sub>J</sub> = 25°C                                                |                                | 5.0 | 120  | mV    |
|                                  |                                                   | 8.0V ≤ V <sub>I</sub> ≤ 25V                                          |                                | 1.5 | 60   |       |
| V <sub>R LOAD</sub>              | Load Regulation                                   | T <sub>J</sub> = 25°C                                                |                                | 14  | 120  | mV    |
|                                  |                                                   | 5.0 mA ≤ I <sub>O</sub> ≤ 1.5A                                       |                                | 4.0 | 60   |       |
| V <sub>O</sub>                   | Output Voltage                                    | 8.0V ≤ V <sub>I</sub> ≤ 21V, 5.0 mA ≤ I <sub>O</sub> ≤ 1.0A, P ≤ 15W | 5.7                            |     | 6.3  | V     |
| I <sub>Q</sub>                   | Quiescent Current                                 | T <sub>J</sub> = 25°C                                                |                                | 4.3 | 8.0  | mA    |
| ΔI <sub>Q</sub>                  | Quiescent Current Change                          | With Line                                                            | 8.0V ≤ V <sub>I</sub> ≤ 25V    |     | 1.3  | mA    |
|                                  |                                                   | With Load                                                            | 5.0 mA ≤ I <sub>O</sub> ≤ 1.0A |     | 0.5  |       |
| N <sub>O</sub>                   | Noise                                             | T <sub>A</sub> = 25°C, 10 Hz ≤ f ≤ 100 kHz                           |                                | 45  |      | μV    |
| ΔV <sub>I</sub> /ΔV <sub>O</sub> | Ripple Rejection                                  | f = 2400 Hz, I <sub>O</sub> = 350 mA, T <sub>J</sub> = 25°C          | 59                             | 75  |      | dB    |
| V <sub>DO</sub>                  | Dropout Voltage                                   | I <sub>O</sub> = 1.0A, T <sub>J</sub> = 25°C                         |                                | 2.0 |      | V     |
| R <sub>O</sub>                   | Output Resistance                                 | f = 1.0 kHz                                                          |                                | 19  |      | mΩ    |
| I <sub>OS</sub>                  | Output Short Circuit Current                      | T <sub>J</sub> = 25°C, V <sub>I</sub> = 35V                          |                                | 550 |      | mA    |
| I <sub>pk</sub>                  | Peak Output Current                               | T <sub>J</sub> = 25°C                                                |                                | 2.2 |      | A     |
| ΔV <sub>O</sub> /ΔT              | Average Temperature Coefficient of Output Voltage | I <sub>O</sub> = 5.0 mA, 0°C ≤ T <sub>A</sub> ≤ +125°C               |                                | 0.8 |      | mV/°C |

## LM7808

### Electrical Characteristics

−55°C ≤ T<sub>A</sub> ≤ +125°C, V<sub>I</sub> = 14V, I<sub>O</sub> = 500 mA, C<sub>I</sub> = 0.33 μF, C<sub>O</sub> = 0.1 μF, unless otherwise specified

| Symbol              | Parameter                | Conditions (Note 1)                                                   | Min                            | Typ | Max | Units |
|---------------------|--------------------------|-----------------------------------------------------------------------|--------------------------------|-----|-----|-------|
| V <sub>O</sub>      | Output Voltage           | T <sub>J</sub> = 25°C                                                 | 7.7                            | 8.0 | 8.3 | V     |
| V <sub>R LINE</sub> | Line Regulation          | T <sub>J</sub> = 25°C                                                 |                                | 6.0 | 80  | mV    |
|                     |                          | 10.5V ≤ V <sub>I</sub> ≤ 25V                                          |                                | 2.0 | 40  |       |
| V <sub>R LOAD</sub> | Load Regulation          | T <sub>J</sub> = 25°C                                                 |                                | 12  | 100 | mV    |
|                     |                          | 5.0 mA ≤ I <sub>O</sub> ≤ 1.5A                                        |                                | 4.0 | 40  |       |
| V <sub>O</sub>      | Output Voltage           | 11.5V ≤ V <sub>I</sub> ≤ 23V, 5.0 mA ≤ I <sub>O</sub> ≤ 1.0A, P ≤ 15W | 7.6                            |     | 8.4 | V     |
| I <sub>Q</sub>      | Quiescent Current        | T <sub>J</sub> = 25°C                                                 |                                | 4.3 | 6.0 | mA    |
| ΔI <sub>Q</sub>     | Quiescent Current Change | With Line                                                             | 11.5V ≤ V <sub>I</sub> ≤ 25V   |     | 0.8 | mA    |
|                     |                          | With Load                                                             | 5.0 mA ≤ I <sub>O</sub> ≤ 1.0A |     | 0.5 |       |

**LM7808****Electrical Characteristics** (Continued)
 $-55^{\circ}\text{C} \leq T_A \leq +125^{\circ}\text{C}$ ,  $V_I = 14\text{V}$ ,  $I_O = 500\text{ mA}$ ,  $C_I = 0.33\text{ }\mu\text{F}$ ,  $C_O = 0.1\text{ }\mu\text{F}$ , unless otherwise specified

| Symbol                  | Parameter                                         | Conditions (Note 1)                                                       | Min | Typ  | Max | Units                            |
|-------------------------|---------------------------------------------------|---------------------------------------------------------------------------|-----|------|-----|----------------------------------|
| $N_O$                   | Noise                                             | $T_A = 25^{\circ}\text{C}$ , $10\text{ Hz} \leq f \leq 100\text{ kHz}$    |     | 8.0  | 40  | $\mu\text{V}/V_O$                |
| $\Delta V_I/\Delta V_O$ | Ripple Rejection                                  | $f = 2400\text{ Hz}$ , $I_O = 350\text{ mA}$ , $T_J = 25^{\circ}\text{C}$ | 62  | 72   |     | dB                               |
| $V_{DO}$                | Dropout Voltage                                   | $I_O = 1.0\text{ A}$ , $T_J = 25^{\circ}\text{C}$                         |     | 2.0  | 2.5 | V                                |
| $R_O$                   | Output Resistance                                 | $f = 1.0\text{ kHz}$                                                      |     | 16   |     | $\text{m}\Omega$                 |
| $I_{OS}$                | Output Short Circuit Current                      | $T_J = 25^{\circ}\text{C}$ , $V_I = 35\text{V}$                           |     | 0.75 | 1.2 | A                                |
| $I_{pk}$                | Peak Output Current                               | $T_J = 25^{\circ}\text{C}$                                                | 1.3 | 2.2  | 3.3 | A                                |
| $\Delta V_O/\Delta T$   | Average Temperature Coefficient of Output Voltage | $I_O = 5.0\text{ mA}$                                                     |     |      | 0.4 | $\text{mV}/^{\circ}\text{C}/V_O$ |
|                         |                                                   | $-55^{\circ}\text{C} \leq T_A \leq +25^{\circ}\text{C}$                   |     |      |     |                                  |
|                         |                                                   | $+25^{\circ}\text{C} \leq T_A \leq +125^{\circ}\text{C}$                  |     |      | 0.3 |                                  |

**LM7808C****Electrical Characteristics**
 $0^{\circ}\text{C} \leq T_A \leq +125^{\circ}\text{C}$ ,  $V_I = 14\text{V}$ ,  $I_O = 500\text{ mA}$ ,  $C_I = 0.33\text{ }\mu\text{F}$ ,  $C_O = 0.1\text{ }\mu\text{F}$ , unless otherwise specified

| Symbol                  | Parameter                                         | Conditions (Note 1)                                                                                        | Min                                        | Typ | Max | Units                        |
|-------------------------|---------------------------------------------------|------------------------------------------------------------------------------------------------------------|--------------------------------------------|-----|-----|------------------------------|
| $V_O$                   | Output Voltage                                    | $T_J = 25^{\circ}\text{C}$                                                                                 | 7.7                                        | 8.0 | 8.3 | V                            |
| $V_{R\text{ LINE}}$     | Line Regulation                                   | $T_J = 25^{\circ}\text{C}$                                                                                 |                                            | 6.0 | 160 | mV                           |
|                         |                                                   | $10.5\text{V} \leq V_I \leq 25\text{V}$                                                                    |                                            |     |     |                              |
|                         |                                                   | $11\text{V} \leq V_I \leq 17\text{V}$                                                                      |                                            | 2.0 | 80  |                              |
| $V_{R\text{ LOAD}}$     | Load Regulation                                   | $T_J = 25^{\circ}\text{C}$                                                                                 |                                            | 12  | 160 | mV                           |
|                         |                                                   | $5.0\text{ mA} \leq I_O \leq 1.5\text{ A}$                                                                 |                                            |     |     |                              |
|                         |                                                   | $250\text{ mA} \leq I_O \leq 750\text{ mA}$                                                                |                                            | 4.0 | 80  |                              |
| $V_O$                   | Output Voltage                                    | $10.5\text{V} \leq V_I \leq 23\text{V}$ , $5.0\text{ mA} \leq I_O \leq 1.0\text{ A}$ , $P \leq 15\text{W}$ | 7.6                                        |     | 8.4 | V                            |
| $I_Q$                   | Quiescent Current                                 | $T_J = 25^{\circ}\text{C}$                                                                                 |                                            | 4.3 | 8.0 | mA                           |
| $\Delta I_Q$            | Quiescent Current Change                          | With Line                                                                                                  | $10.5\text{V} \leq V_I \leq 25\text{V}$    |     | 1.0 | mA                           |
|                         |                                                   | With Load                                                                                                  | $5.0\text{ mA} \leq I_O \leq 1.0\text{ A}$ |     | 0.5 |                              |
| $N_O$                   | Noise                                             | $T_A = 25^{\circ}\text{C}$ , $10\text{ Hz} \leq f \leq 100\text{ kHz}$                                     |                                            | 52  |     | $\mu\text{V}$                |
| $\Delta V_I/\Delta V_O$ | Ripple Rejection                                  | $f = 2400\text{ Hz}$ , $I_O = 350\text{ mA}$ , $T_J = 25^{\circ}\text{C}$                                  | 56                                         | 72  |     | dB                           |
| $V_{DO}$                | Dropout Voltage                                   | $I_O = 1.0\text{ A}$ , $T_J = 25^{\circ}\text{C}$                                                          |                                            | 2.0 |     | V                            |
| $R_O$                   | Output Resistance                                 | $f = 1.0\text{ kHz}$                                                                                       |                                            | 16  |     | $\text{m}\Omega$             |
| $I_{OS}$                | Output Short Circuit Current                      | $T_J = 25^{\circ}\text{C}$ , $V_I = 35\text{V}$                                                            |                                            | 450 |     | mA                           |
| $I_{pk}$                | Peak Output Current                               | $T_J = 25^{\circ}\text{C}$                                                                                 |                                            | 2.2 |     | A                            |
| $\Delta V_O/\Delta T$   | Average Temperature Coefficient of Output Voltage | $I_O = 5.0\text{ mA}$                                                                                      |                                            | 0.8 |     | $\text{mV}/^{\circ}\text{C}$ |

**LM7818****Electrical Characteristics**
 $-55^{\circ}\text{C} \leq T_A \leq +125^{\circ}\text{C}$ ,  $V_I = 27\text{V}$ ,  $I_O = 500\text{ mA}$ ,  $C_I = 0.33\text{ }\mu\text{F}$ ,  $C_O = 0.1\text{ }\mu\text{F}$ , unless otherwise specified

| Symbol                  | Parameter                                         | Conditions (Note 1)                                                                                     | Min  | Typ  | Max  | Units                      |
|-------------------------|---------------------------------------------------|---------------------------------------------------------------------------------------------------------|------|------|------|----------------------------|
| $V_O$                   | Output Voltage                                    | $T_J = 25^{\circ}\text{C}$                                                                              | 17.3 | 18.0 | 18.7 | V                          |
| $V_{R\text{ LINE}}$     | Line Regulation                                   | $T_J = 25^{\circ}\text{C}$                                                                              |      | 15   | 180  | mV                         |
|                         |                                                   | $21\text{V} \leq V_I \leq 33\text{V}$                                                                   |      |      |      |                            |
|                         |                                                   | $24\text{V} \leq V_I \leq 30\text{V}$                                                                   |      | 5.0  | 90   |                            |
| $V_{R\text{ LOAD}}$     | Load Regulation                                   | $T_J = 25^{\circ}\text{C}$                                                                              |      | 12   | 180  | mV                         |
|                         |                                                   | $5.0\text{ mA} \leq I_O \leq 1.5\text{A}$                                                               |      |      |      |                            |
|                         |                                                   | $250\text{ mA} \leq I_O \leq 750\text{ mA}$                                                             |      | 4.0  | 90   |                            |
| $V_O$                   | Output Voltage                                    | $22\text{V} \leq V_I \leq 33\text{V}$ , $5.0\text{ mA} \leq I_O \leq 1.0\text{A}$ , $P \leq 15\text{W}$ | 17.1 |      | 18.9 | V                          |
| $I_Q$                   | Quiescent Current                                 | $T_J = 25^{\circ}\text{C}$                                                                              |      | 4.5  | 6.0  | mA                         |
| $\Delta I_Q$            | Quiescent Current Change                          | With Line                                                                                               |      |      | 0.8  | mA                         |
|                         |                                                   | With Load                                                                                               |      |      | 0.5  |                            |
| $N_O$                   | Noise                                             | $T_A = 25^{\circ}\text{C}$ , $10\text{ Hz} \leq f \leq 100\text{ kHz}$                                  |      | 8.0  | 40   | $\mu\text{V}/V_O$          |
| $\Delta V_I/\Delta V_O$ | Ripple Rejection                                  | $f = 2400\text{ Hz}$ , $I_O = 350\text{ mA}$ , $T_J = 25^{\circ}\text{C}$                               | 59   | 69   |      | dB                         |
| $V_{DO}$                | Dropout Voltage                                   | $I_O = 1.0\text{A}$ , $T_J = 25^{\circ}\text{C}$                                                        |      | 2.0  |      | V                          |
| $R_O$                   | Output Resistance                                 | $f = 1.0\text{ kHz}$                                                                                    |      | 22   |      | m $\Omega$                 |
| $I_{OS}$                | Output Short Circuit Current                      | $T_J = 25^{\circ}\text{C}$ , $V_I = 35\text{V}$                                                         |      | 0.75 |      | A                          |
| $I_{pk}$                | Peak Output Current                               | $T_J = 25^{\circ}\text{C}$                                                                              | 1.3  | 2.2  | 3.3  | A                          |
| $\Delta V_O/\Delta T$   | Average Temperature Coefficient of Output Voltage | $I_O = 5.0\text{ mA}$                                                                                   |      |      | 0.4  | mV/ $^{\circ}\text{C}/V_O$ |
|                         |                                                   | $-55^{\circ}\text{C} \leq T_A \leq +25^{\circ}\text{C}$                                                 |      |      |      |                            |
|                         |                                                   | $+25^{\circ}\text{C} \leq T_A \leq +125^{\circ}\text{C}$                                                |      |      | 0.3  |                            |

**LM7818C****Electrical Characteristics**
 $0^{\circ}\text{C} \leq T_A \leq +125^{\circ}\text{C}$ ,  $V_I = 27\text{V}$ ,  $I_O = 500\text{ mA}$ ,  $C_I = 0.33\text{ }\mu\text{F}$ ,  $C_O = 0.1\text{ }\mu\text{F}$ , unless otherwise specified.

| Symbol              | Parameter         | Conditions (Note 1)                                                                                     | Min  | Typ  | Max  | Units |
|---------------------|-------------------|---------------------------------------------------------------------------------------------------------|------|------|------|-------|
| $V_O$               | Output Voltage    | $T_J = 25^{\circ}\text{C}$                                                                              | 17.3 | 18.0 | 18.7 | V     |
| $V_{R\text{ LINE}}$ | Line Regulation   | $T_J = 25^{\circ}\text{C}$                                                                              |      | 15   | 360  | mV    |
|                     |                   | $21\text{V} \leq V_I \leq 33\text{V}$                                                                   |      |      |      |       |
|                     |                   | $24\text{V} \leq V_I \leq 30\text{V}$                                                                   |      | 5.0  | 180  |       |
| $V_{R\text{ LOAD}}$ | Load Regulation   | $T_J = 25^{\circ}\text{C}$                                                                              |      | 12   | 360  | mV    |
|                     |                   | $5.0\text{ mA} \leq I_O \leq 1.5\text{A}$                                                               |      |      |      |       |
|                     |                   | $250\text{ mA} \leq I_O \leq 750\text{ mA}$                                                             |      | 4.0  | 180  |       |
| $V_O$               | Output Voltage    | $21\text{V} \leq V_I \leq 33\text{V}$ , $5.0\text{ mA} \leq I_O \leq 1.0\text{A}$ , $P \leq 15\text{W}$ | 17.1 |      | 18.9 | V     |
| $I_Q$               | Quiescent Current | $T_J = 25^{\circ}\text{C}$                                                                              |      | 4.5  | 8.0  | mA    |

**LM7818C****Electrical Characteristics** (Continued)0°C ≤ T<sub>A</sub> ≤ +125°C, V<sub>I</sub> = 27V, I<sub>O</sub> = 500 mA, C<sub>I</sub> = 0.33 μF, C<sub>O</sub> = 0.1 μF, unless otherwise specified

| Symbol                           | Parameter                                         | Conditions (Note 1)                                         | Min | Typ | Max | Units |
|----------------------------------|---------------------------------------------------|-------------------------------------------------------------|-----|-----|-----|-------|
| ΔI <sub>Q</sub>                  | Quiescent Current Change                          | With Line<br>21V ≤ V <sub>I</sub> ≤ 33V                     |     |     | 1.0 | mA    |
|                                  |                                                   | With Load<br>5.0 mA ≤ I <sub>O</sub> ≤ 1.0A                 |     |     | 0.5 |       |
| N <sub>O</sub>                   | Noise                                             | T <sub>A</sub> = 25°C, 10 Hz ≤ f ≤ 100 kHz                  |     | 110 |     | μV    |
| ΔV <sub>I</sub> /ΔV <sub>O</sub> | Ripple Rejection                                  | f = 2400 Hz, I <sub>O</sub> = 350 mA, T <sub>J</sub> = 25°C | 53  | 69  |     | dB    |
| V <sub>DO</sub>                  | Dropout Voltage                                   | I <sub>O</sub> = 1.0A, T <sub>J</sub> = 25°C                |     | 2.0 |     | V     |
| R <sub>O</sub>                   | Output Resistance                                 | f = 1.0 kHz                                                 |     | 22  |     | mΩ    |
| I <sub>OS</sub>                  | Output Short Circuit Current                      | T <sub>J</sub> = 25°C, V <sub>I</sub> = 35V                 |     | 200 |     | mA    |
| I <sub>pk</sub>                  | Peak Output Current                               | T <sub>J</sub> = 25°C                                       |     | 2.1 |     | A     |
| ΔV <sub>O</sub> /ΔT              | Average Temperature Coefficient of Output Voltage | I <sub>O</sub> = 5.0 mA                                     |     | 1.0 |     | mV/°C |

**LM7824****Electrical Characteristics**-55°C ≤ T<sub>A</sub> ≤ +125°C, V<sub>I</sub> = 33V, I<sub>O</sub> = 500 mA, C<sub>I</sub> = 0.33 μF, C<sub>O</sub> = 0.1 μF, unless otherwise specified

| Symbol                           | Parameter                                         | Conditions (Note 1)                                                 | Min  | Typ  | Max  | Units                    |
|----------------------------------|---------------------------------------------------|---------------------------------------------------------------------|------|------|------|--------------------------|
| V <sub>O</sub>                   | Output Voltage                                    | T <sub>J</sub> = 25°C                                               | 23.0 | 24.0 | 25.0 | V                        |
| V <sub>R LINE</sub>              | Line Regulation                                   | T <sub>J</sub> = 25°C<br>27V ≤ V <sub>I</sub> ≤ 38V                 |      | 18   | 240  | mV                       |
|                                  |                                                   | 30V ≤ V <sub>I</sub> ≤ 36V                                          |      | 6.0  | 120  |                          |
| V <sub>R LOAD</sub>              | Load Regulation                                   | T <sub>J</sub> = 25°C<br>5.0 mA ≤ I <sub>O</sub> ≤ 1.5A             |      | 12   | 240  | mV                       |
|                                  |                                                   | 250 mA ≤ I <sub>O</sub> ≤ 750 mA                                    |      | 4.0  | 120  |                          |
| V <sub>O</sub>                   | Output Voltage                                    | 28V ≤ V <sub>I</sub> ≤ 38V, 5.0 mA ≤ I <sub>O</sub> ≤ 1.0A, P ≤ 15W | 22.8 |      | 25.2 | V                        |
| I <sub>Q</sub>                   | Quiescent Current                                 | T <sub>J</sub> = 25°C                                               |      | 4.6  | 6.0  | mA                       |
| ΔI <sub>Q</sub>                  | Quiescent Current Change                          | With Line<br>28V ≤ V <sub>I</sub> ≤ 38V                             |      |      | 0.8  | mA                       |
|                                  |                                                   | With Load<br>5.0 mA ≤ I <sub>O</sub> ≤ 1.0A                         |      |      | 0.5  |                          |
| N <sub>O</sub>                   | Noise                                             | T <sub>A</sub> = 25°C, 10 Hz ≤ f ≤ 100 kHz                          |      | 8.0  | 40   | μV/V <sub>O</sub>        |
| ΔV <sub>I</sub> /ΔV <sub>O</sub> | Ripple Rejection                                  | f = 2400 Hz, I <sub>O</sub> = 350 mA, T <sub>J</sub> = 25°C         | 56   | 66   |      | dB                       |
| V <sub>DO</sub>                  | Dropout Voltage                                   | I <sub>O</sub> = 1.0A, T <sub>J</sub> = 25°C                        |      | 2.0  | 2.5  | V                        |
| R <sub>O</sub>                   | Output Resistance                                 | f = 1.0 kHz                                                         |      | 28   |      | mΩ                       |
| I <sub>OS</sub>                  | Output Short Circuit Current                      | T <sub>J</sub> = 25°C, V <sub>I</sub> = 35V                         |      | 0.75 | 1.2  | A                        |
| I <sub>pk</sub>                  | Peak Output Current                               | T <sub>J</sub> = 25°C                                               | 1.3  | 2.2  | 3.3  | A                        |
| ΔV <sub>O</sub> /ΔT              | Average Temperature Coefficient of Output Voltage | I <sub>O</sub> = 5.0 mA<br>-55°C ≤ T <sub>A</sub> ≤ +25°C           |      |      | 0.4  | mV/°C/<br>V <sub>O</sub> |
|                                  |                                                   | +25°C ≤ T <sub>A</sub> ≤ +125°C                                     |      |      | 0.3  |                          |


**LM7824C****Electrical Characteristics**0°C ≤ T<sub>A</sub> ≤ +125°C, V<sub>I</sub> = 33V, I<sub>O</sub> = 500 mA, C<sub>I</sub> = 0.33 μF, C<sub>O</sub> = 0.1 μF, unless otherwise specified

| Symbol              | Characteristics   | Conditions (Note 1)                                                 | Min  | Typ  | Max  | Units |
|---------------------|-------------------|---------------------------------------------------------------------|------|------|------|-------|
| V <sub>O</sub>      | Output Voltage    | T <sub>J</sub> = 25°C                                               | 23.0 | 24.0 | 25.0 | V     |
| V <sub>R LINE</sub> | Line Regulation   | T <sub>J</sub> = 25°C<br>27V ≤ V <sub>I</sub> ≤ 38V                 |      | 18   | 480  | mV    |
|                     |                   | 30V ≤ V <sub>I</sub> ≤ 36V                                          |      | 6.0  | 240  |       |
| V <sub>R LOAD</sub> | Load Regulation   | T <sub>J</sub> = 25°C<br>5.0 mA ≤ I <sub>O</sub> ≤ 1.5A             |      | 12   | 480  | mV    |
|                     |                   | 250 mA ≤ I <sub>O</sub> ≤ 750 mA                                    |      | 4.0  | 240  |       |
| V <sub>O</sub>      | Output Voltage    | 27V ≤ V <sub>I</sub> ≤ 38V, 5.0 mA ≤ I <sub>O</sub> ≤ 1.0A, P ≤ 15W | 22.8 |      | 25.2 | V     |
| I <sub>Q</sub>      | Quiescent Current | T <sub>J</sub> = 25°C                                               |      | 4.6  | 8.0  | mA    |

**LM7824C****Electrical Characteristics** (Continued)
 $0^{\circ}\text{C} \leq T_A \leq +125^{\circ}\text{C}$ ,  $V_I = 33\text{V}$ ,  $I_O = 500\text{ mA}$ ,  $C_I = 0.33\text{ }\mu\text{F}$ ,  $C_O = 0.1\text{ }\mu\text{F}$ , unless otherwise specified

| Symbol                    | Parameter                                         | Conditions (Note 1)                                                       | Min | Typ | Max | Units                        |
|---------------------------|---------------------------------------------------|---------------------------------------------------------------------------|-----|-----|-----|------------------------------|
| $\Delta I_Q$              | Quiescent Current Change                          | With Line<br>$27\text{V} \leq V_I \leq 38\text{V}$                        |     |     | 1.0 | mA                           |
|                           |                                                   | With Load<br>$5.0\text{ mA} \leq I_O \leq 1.0\text{A}$                    |     |     | 0.5 |                              |
| $N_O$                     | Noise                                             | $T_A = 25^{\circ}\text{C}$ , $10\text{ Hz} \leq f \leq 100\text{ kHz}$    |     | 170 |     | $\mu\text{V}$                |
| $\Delta V_I / \Delta V_O$ | Ripple Rejection                                  | $f = 2400\text{ Hz}$ , $I_O = 350\text{ mA}$ , $T_J = 25^{\circ}\text{C}$ | 50  | 66  |     | dB                           |
| $V_{DO}$                  | Dropout Voltage                                   | $I_O = 1.0\text{A}$ , $T_J = 25^{\circ}\text{C}$                          |     | 2.0 |     | V                            |
| $R_O$                     | Output Resistance                                 | $f = 1.0\text{ kHz}$                                                      |     | 28  |     | $\text{m}\Omega$             |
| $I_{OS}$                  | Output Short Circuit Current                      | $T_J = 25^{\circ}\text{C}$ , $V_I = 35\text{V}$                           |     | 150 |     | mA                           |
| $I_{pk}$                  | Peak Output Current                               | $T_J = 25^{\circ}\text{C}$                                                |     | 2.1 |     | A                            |
| $\Delta V_O / \Delta T$   | Average Temperature Coefficient of Output Voltage | $I_O = 5.0\text{ mA}$                                                     |     | 1.5 |     | $\text{mV}/^{\circ}\text{C}$ |


**Note 1:** For all tables, all characteristics except noise voltage and ripple rejection ratio are measured using pulse techniques ( $t_W \leq 10\text{ ms}$ , duty cycle  $\leq 5\%$ ). Output voltage changes due to changes in internal temperature must be taken into account separately.

**Equivalent Circuit**


TL/H/10052-3

# Typical Performance Characteristics


Worst Case Power Dissipation vs Ambient Temperature (TO-3)




Worst Case Power Dissipation vs Ambient Temperature (TO-220)




Peak Output Current vs Input/Output Voltage Differential




Output Voltage vs Junction Temperature




Current-Limiting Characteristics




Dropout Voltage vs Junction Temperature




Dropout Characteristics




Quiescent Current vs Input Voltage




Quiescent Current vs Junction Temperature




Ripple Rejection vs Frequency



Line Transient Response




Load Transient Response



TL/H/10052-4


# Typical Performance Characteristics (Continued)



TL/H/10052-5

**Note:** The other LM7800 series devices have similar curves.

## DC Parameter Test Circuit



TL/H/10052-6

## Design Considerations


The LM7800 fixed voltage regulator series has thermal overload protection from excessive power dissipation, internal short circuit protection which limits the regulator's maximum current, and output transistor safe-area compensation for reducing the output current as the voltage across the pass transistor is increased.

Although the internal power dissipation is limited, the junction temperature must be kept below the maximum specified temperature (150°C for LM7800, 125°C for LM7800C) in order to meet data sheet specifications. To calculate the maximum junction temperature or heat sink required, the following thermal resistance values should be used:

| Package | Typ $\theta_{JC}$<br>°C/W | Max $\theta_{JC}$<br>°C/W | Typ $\theta_{JA}$<br>°C/W | Max $\theta_{JA}$<br>°C/W |
|---------|---------------------------|---------------------------|---------------------------|---------------------------|
| TO-3    | 3.5                       | 5.5                       | 35                        | 40                        |
| TO-220  | 3.0                       | 5.0                       | 40                        | 60                        |

## Typical Applications

### Fixed Output Regulator




TL/H/10052-7


**Note 1:** To specify an output voltage, substitute voltage value for "00".

**Note 2:** Bypass capacitors are recommended for optimum stability and transient response, and should be located as close as possible to the regulator.

### High Input Voltage Circuits




TL/H/10052-8



TL/H/10052-9

### High Current Voltage Regulator



TL/H/10052-10

$$P_{D \text{ Max}} = \frac{T_{J \text{ Max}} - T_A}{\theta_{JC} + \theta_{CA}} \text{ or}$$

$$= \frac{T_{J \text{ Max}} T_A}{\theta_{JA}} \text{ (without heat sink)}$$

$$\theta_{CA} = \theta_{CS} + \theta_{SA}$$

Solving for  $T_J$ :

$$T_J = T_A + P_D (\theta_{JC} + \theta_{CA}) \text{ or}$$

$$= T_A + P_D \theta_{JA} \text{ (without heat sink)}$$

Where:

$T_J$  = Junction Temperature

$T_A$  = Ambient Temperature

$P_D$  = Power Dissipation

$\theta_{JC}$  = Junction-to-Case Thermal Resistance

$\theta_{CA}$  = Case-to-Ambient Thermal Resistance


$\theta_{CS}$  = Case-to-Heat Sink Thermal Resistance

$\theta_{SA}$  = Heat Sink-to-Ambient Thermal Resistance

$\theta_{JA}$  = Junction-to-Ambient Thermal Resistance


# Typical Applications (Continued)

## High Output Current, Short Circuit Protected



TL/H/10052-11

## Positive and Negative Regulator



TL/H/10052-12