




| Product Details                                                                   |                                   |                                                                                    |                 |
|-----------------------------------------------------------------------------------|-----------------------------------|------------------------------------------------------------------------------------|-----------------|
| Model Name                                                                        | <b>LT</b>                         | ECCO Group Europe Part Number                                                      | <b>31105372</b> |
| Internal ERP Description                                                          | BEACON, LT, XEN, 5W, 230 VAC, RED | Application                                                                        | Industrial      |
| Product Type                                                                      | Xenon Beacon                      |                                                                                    |                 |
| Product Image – Amber beacon only shown                                           |                                   | Product Dimensions                                                                 |                 |
|  |                                   |  |                 |

| Electrical Characteristics |              |                     |                 |
|----------------------------|--------------|---------------------|-----------------|
| Input Voltage              | 207 – 253Vac | Input current       | 40mA @ 230Vac   |
| Frequency                  | 90 FPM       | Light Source        | Non-replaceable |
| Flash Mode                 | Single flash | Flash Pattern       | N/A             |
| Technology                 | Xenon        | Power rating        | 5 W             |
|                            |              | Estimated Tube Life | 3,000 Hours     |

| Photometric Characteristics                                                         |        |                                                                                      |
|-------------------------------------------------------------------------------------|--------|--------------------------------------------------------------------------------------|
| Colour                                                                              | Red    | Polar Plot                                                                           |
| Max intensity at HV0                                                                | 4.2 cd |  |
| Min intensity                                                                       | 4.2 cd |                                                                                      |
| Timing Diagram                                                                      |        |                                                                                      |
|  |        |                                                                                      |

| Enclosure            |                         |                      |                                  |
|----------------------|-------------------------|----------------------|----------------------------------|
| IP rating            | IP 67                   | Fixing centres       | 45 mm                            |
| Cable exit           | Central base grommet    | Fastening hardware   | 2 x M5 x 14mm studs with M5 nuts |
| Cable dimensions     | 2 x 0.75mm <sup>2</sup> | Packaging            | Thin wall carton                 |
| Recommended Mounting | Upright                 | Max Fastening Torque | 5 N/m                            |
| Weight (unboxed)     | 130g                    | Weight (boxed)       | 150g                             |

| Approvals and Certifications |                    |      |                                           |
|------------------------------|--------------------|------|-------------------------------------------|
| EMC                          | UN ECE R10-03 6101 | WEEE | Yes (marking only for own brand products) |
| CE                           | Yes                | RoHS | Yes                                       |