




PIN NUMBER	DIM. L(PIN LENGTH)
25, 26	3.50
ALL OTHER PINS	4.25
1,13,38,50	5.00



THE PUSH BUTTON POSITION



mot'l. code				tolerances unless otherwise specified				CUSTOMER COPY		title	
lir	ecn no	dr	date	linear	angles	dr	engl	projection	scale	product family	code
A	T05-0258	A.C.	11/21/05	.XX ± 0.20	0° ± 2°	dr	allen chang	11/03/05	MM	CF ASSY,BELOW MOUNT	TWN
B	T06-0038	A.C.	3/03/06	.XXX ± 0.10		engl	allen chang	11/03/05	NA	LEFT PUSH, S/O=0mm	1 of 4
C	T08-1174	S.LIN	10/12/08			dr	allen chang	11/03/05	NA	CF	1 of 4
sheet	revision	C	C	C	C	chr	STERLING LIN	11/03/05	NA	10061862	1 of 4
index	sheet	1	2	3		oppl	H.C LIU	11/03/05			



Recommended PCB Pattern


mot'l. code		tolerances unless otherwise specified		CUSTOMER COPY		title		product family		code	
l/r	ecn no	dr	date	linear	projection	scale	size	dwg no	CF	code	sheet
A	T05-0258	A.C.	11/21/05	.XX ± 0.20	MM	NA	A4	10061862	CF	TWN	3 of 4
B	T06-0038	A.C.	3/03/06	.XXX ± 0.10							
C	T08-1174	S.LIN	10/12/08	0° ± 2°							
		dr	allen chang	11/03/05							
		eng	allen chang	11/03/05							
		chr	sterling lin	11/03/05							
		appd	h.c liou	11/03/05							
sheet	revision	C	C	C							
index	sheet	1	2	3							

NOTES :

1. THIS IS THE ASSEMBLY TYPE WHICH INCLUDES HEADER 10053868-E1501 AND EJECTOR 10053869-0050LF.
2. MATERIAL :
- INSULATOR : HIGH TEMPERATURE THERMOPLASTIC
- FLAMMABILITY RATING: UL94V-0
- COLOR: IVORY
- CONTACT : COPPER ALLOY
- GROUND MOUNTING EAR: COPPER ALLOY
- COVER: STAINLESS STEEL.
- ARM: STAINLESS STEEL.
- PUSH ROD : HIGH TEMPERATURE THERMOPLASTIC
- FLAMMABILITY RATING: UL94V-0
- COLOR: BLACK.
- RIVET : COPPER ALLOY
3. PLATING :
- CONTACT AREA: SELECTIVE GOLD (SEE P/N DESCRIPTION)
- UNDER PLATING: 50u" NICKEL OVERALL
- SOLDER TAIL AREA: 100u" TIN/LEAD OR 100u" MATTE TIN
- GROUND MOUNT EAR AREA: 100u" TIN/LEAD OR 100u" MATTE TIN
4. SOLDER TAILS TO BE WITHIN 0.05 UPWARD AND 0.2 DOWNWARD FROM Z-DATUM PLACE, AND COPLANARITY OF SOLDER TAILS TO BE WITHIN 0.10mm.
5. PRODUCT SPEC: GS-12-240.
6. PACKAGING SPEC: GS-14-1040.

7. Part Number Description:



P/N: 10061862-X150 X 0 X




8. THIS PRODUCT (10061862-XXXXXXLF) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008.
9. THIS PRODUCT (10061862-XXXXXX) MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED IN GS-22-008 EXCEPT FOR Pb.
10. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, IR OR VAPER PHASE REFLOW OVEN.
11. THE PRODUCTS WHERE THE PART NUMBER ENDS IN "LF" MEET THE CRITERIA SHOWN IN THE NOTES 8 AND 10.



mot'l. code			tolerances unless otherwise specified			CUSTOMER COPY		FCI	
litr	ecn no	dr	date	linear		projection	title	www.fciconnect.com	
A	T05-0258	A.C.	11/21/05	.XX ± 0.20			CF ASS'Y,BELOW MOUNT		
B	T06-0038	A.C.	3/03/06	.XXX ± 0.10			LEFT PUSH, S/O=0mm		
C	T08-1174	S.LIN	10/12/08	0° ±2°					
		dr	ALLEN CHANG	11/03/05	MM		product family	CF	code
		eng	ALLEN CHANG	11/03/05			size	dwg no	TWN
		chr	STERLING LIN	11/03/05	scale				
		appd	H.C LIU	11/03/05	NA				
sheet	revision	C	C	C					
index	sheet	1	2	3					




NOTES:
1.CARRIER TAPE: PS T=0.4MM
2.COVER TAPE: PE
3.PLASTIC HUB: PS



COMPOSITION OF PACKAGING

CONNECTOR PACKAGING
AREA QUANTITY:150PCS



mot'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCI	
lir	ecn no	dr	date	linear	.XX ± 0.30	projection	title
A	T05-0258	A.C.	11/21/05		.XX ± 0.20		CF ASS'Y,BELOW MOUNT
B	T06-0038	A.C.	3/03/06		.XX ± 0.10		LEFT PUSH, S/O=0mm
C	T08-1174	S.LIN	10/12/08	angles	0° ± 2°		
		dr	ALLEN CHANG	11/03/05			
		eng	ALLEN CHANG	11/03/05			
		chr	STERLING LIN	11/03/05			
		appd	H.C LIU	11/03/05			
sheet	revision	C	C	C		scale	product family
index	sheet	1	2	3		NA	CF

1 | 2

1 | 2

3 |

4