


CLIPLINE




QUICKON Terminal QT – Fast connection

QT QUICKON Terminal

Fast connection terminal blocks

The QUICKON-QT series features the new IDC connection. Depending on the connection system used, the time savings when working with the QUICKON fast connection method can amount to 60 % and more!

In the form of hybrid or pluggable terminal blocks, it is possible to combine all four connection systems to suit customer requirements.



Four connection technologies – one system

With CLIPLINE complete, the unique modular terminal block system from PHOENIX CONTACT, you are free to choose the connection method. All connection systems can be freely combined using the same range of accessories.

PHOENIX CONTACT



Patented insulation displacement contact

Conductors of 0.25 to 2.5 mm² and 24 A are connected using the patented insulation displacement contact. High-grade special alloys and snap fittings of the switching system ensure a reliable electrical connection.




Click for faster connection

Stripping and fitting splicing protection is no longer necessary thanks to the QUICKON fast connection system. Cut the conductors to the correct length and they can then be contacted within seconds.


QT accessories

Example of a 6 mm² central input with adapter bridges RB ST 6-(2,5/4) to 1.5 mm² QTC.



Mounting material	Type	Order No.
12 Test adapter, for 4 mm Ø test plug PS and 4 mm Ø safety test plug	PAI-4	3030925
13 35 x 7.5 mm DIN-rail, chromated, Length 2 m	NS 35/7,5 UNGELOCHT NS 35/7,5 GELOCHT	0801681 0801733
13 35 x 7.5 mm DIN-rail, galvanized, Length 2 m	NS 35/7,5 UNGELOCHT ZN NS 35/7,5 GELOCHT ZN	1206434 1206421
14 Snap-on end bracket	CLIPFIX 35-5	3022276
15 Screwdriver	SZF 1 - 6 x 0,35 mm	1204517
16 Operating instruction, as label for the control cabinet	QTC-IL	3039926
17 Terminal strip marker carrier, height-adjustable, for CLIPFIX 35-5, can be marked with a label	KLM 3-L	0814788

Power terminal block						Input I _{max.}	
Cross sect.	from	with	from	with	to	central	one-sided
4 mm ²	ST 4	FBS 2-5 3030161	UT 4	—	QTC 1,5 QTC 2,5	31 A 40 A	31 A 40 A
6 mm ²	ST 6	RB ST 6-(2,5/4) 3030860	UT 6	RB UT 6-ST(2,5/4) 3047264	QTC 1,5 QTC 2,5	35 A 40 A	40 A 56 A
10 mm ²	ST 10	RB ST 10-(2,5/4) 3030873	UT 10	RB UT 10-ST(2,5/4) 3047086	QTC 1,5 QTC 2,5	35 A 40 A	65 A 65 A
16 mm ²	ST 16	RB ST 16-(2,5/4) 3030886	UT 16	RB UT 16-ST(2,5/4) 3047099	QTC 1,5 QTC 2,5	35 A 40 A	70 A 80 A
35 mm ²	ST 35	RB ST 35-(2,5/4) 3030899	UT 35	RB UT 35-ST(2,5/4) 3047280	QTC 1,5 QTC 2,5	35 A 40 A	70 A 80 A



Terminal block	2-pos.	3-pos.	4-pos.	Bridges 5-pos.	10-pos.	20-pos.	50-pos.	I _{max.}	Separating plate	Cover	Cover segment	Modular test plug	Spacer plate for test plug	Marking center groove	Marking center and side groove	Marker carrier	Group marker label
QTC 1,5	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC 3206209	D-QTC 1,5 3205161	—	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCU 1,5	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC 3206209	D-QTCU 1,5 3206283	—	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCS 1,5	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC 3206209	D-QTC 1,5 3206270	—	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 1,5-TWIN	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC TWIN 3206212	D-QTC 1,5-TWIN 3205190	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCU 1,5-TWIN	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC TWIN 3206212	D-QTCU 1,5-TWIN 3206296	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCS 1,5-TWIN	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC TWIN 3206212	D-QTC 1,5-TWIN 3206403	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 1,5-QUATTRO	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC QUATTRO 3206225	D-QTC 1,5-QUATTRO 3205174	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 1,5-TWIN-MT/TG	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC QUATTRO 3206225	D-QTC 1,5-QUATTRO 3205174	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTTCB 1,5	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC QUATTRO 3206225	D-QTC 1,5-QUATTRO 3205174	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTTCBU 1,5	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC QUATTRO 3206225	D-QTC 1,5-QUATTRO 3205174	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTTCBS 1,5	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC QUATTRO 3206225	D-QTC 1,5-QUATTRO 3205174	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 1,5/1P	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC QUATTRO 3206225	D-QTC 1,5-QUATTRO 3205174	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTTCB 1,5/2P	FBS 2-5 3030161	FBS 3-5 3030174	FBS 4-5 3030187	FBS 5-5 3030190	FBS 10-5 3030213	FBS 20-5 3030226	FBS 50-5 3038930	24 A	ATP-QTC QUATTRO 3206225	D-QTC 1,5-QUATTRO 3205174	DS-QTC 1,5 3205200	PS-5 3030983	DP PS-5 3036725	ZB 5:UNBEDRUCKT 1050004	ZBF 5:UNBEDRUCKT 0808642	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 2,5	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC 3206209	D-QTC 2,5 3206568	—	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCU 2,5	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC 3206209	D-QTCU 2,5 3206597	—	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCS 2,5	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC 3206209	D-QTC 2,5 3206568	—	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 2,5-TWIN	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC TWIN 3206212	D-QTC 2,5-TWIN 3206571	DS-QTC 2,5 3206607	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 2,5-TWIN-MT/TG	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC TWIN 3206212	D-QTC 2,5-TWIN 3206571	DS-QTC 2,5 3206607	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCU 2,5-TWIN	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC TWIN 3206212	D-QTCU 2,5-TWIN 3206571	DS-QTC 2,5 3206607	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTCS 2,5-TWIN	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC TWIN 3206212	D-QTC 2,5-TWIN 3206571	DS-QTC 2,5 3206607	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	STP 5-2-ZB 3037643	GBS 5-25x12 0810588
QTC 2,5-HESI/HEDI	FBS 2-6 3030336	FBS 3-6 3030242	FBS 4-6 3030255	FBS 5-6 3030349	FBS 10-6 3030271	FBS 20-6 3030365	FBS 50-6 3032224	32 A	ATP-QTC TWIN 3206212	D-QTC 2,5-TWIN 3206571	DS-QTC 2,5 3206607	PS-6 3030996	DP PS-6 3036738	ZB 6:UNBEDRUCKT 1051003	ZBF 6:UNBEDRUCKT 0808710	—	—

2-conductor
modular terminal blocks



Type	Order No.	QTC 1,5 QTC 1,5 BU	3205019 3205022	QTC 1,5-PE	3205035
Width / Length / Height	[mm]	5.2 / 58.8 / 39.3		5.2 / 58.8 / 39.3	
Current / Voltage (IEC)	[A] / [V]	17.5 / 800		– / –	
Solid	[mm²]	0.25-1.5		0.25-1.5	
Stranded	[mm²]	0.25-1.5		0.25-1.5	
AWG	–	24-16		24-16	



Type	Order No.	QTC 2,5 QTC 2,5 BU	3206416 3206429	QTC 2,5-PE	3206432
Width / Length / Height	[mm]	6.2 / 62.6 / 39.3		6.2 / 62.6 / 39.3	
Current / Voltage (IEC)	[A] / [V]	24 / 800		– / –	
Solid	[mm²]	0.5-2.5		0.5-2.5	
Stranded	[mm²]	0.5-2.5		0.5-2.5	
AWG	–	20-14		20-14	

2-cond. hybrid terminals

– Screw connection



Type	Order No.	QTCU 1,5 QTCU 1,5 BU QTCU 1,5-PE	3050015 3050028 3050031	QTCU 2,5 QTCU 2,5 BU QTCU 2,5-PE	3206539 3206542 3206555
Width / Length / Height	[mm]	5.2 / 58.8 / 42.8		6.2 / 62.6 / 42.8	
Current / Voltage ¹⁾ (IEC)	[A] / [V]	17.5 / 800		24 / 800	
Screw		QTC		QTC	
Solid / AWG	[mm²] / –	0.14-4 / 26-12	0.25-1.5 / 24-16	0.14-6 / 26-10	0.5-2.5 / 20-14
Stranded / AWG	[mm²] / –	0.14-2.5 / 26-14	0.25-1.5 / 24-16	0.14-4 / 26-12	0.5-2.5 / 20-14
Stranded with ferrule	[mm²]	0.25-2.5	–	0.25-4	–

2-cond. hybrid terminals

– Spring-cage connection



Type	Order No.	QTCS 1,5 QTCS 1,5 BU QTCS 1,5-PE	3050138 3050141 3050154	QTCS 2,5 QTCS 2,5 BU QTCS 2,5-PE	3206500 3206513 3206526
Width / Length / Height	[mm]	5.2 / 54.4 / 39.3		6.2 / 59.7 / 39.3	
Current / Voltage ¹⁾ (IEC)	[A] / [V]	17.5 / 800		24 / 800	
Spring-cage		QTC		QTC	
Solid / AWG	[mm²] / –	0.08-4 / 28-12	0.25-1.5 / 24-16	0.08-6 / 28-10	0.5-2.5 / 20-14
Stranded / AWG	[mm²] / –	0.08-2.5 / 28-14	0.25-1.5 / 24-16	0.08-4 / 28-12	0.5-2.5 / 20-14
Stranded with ferrule	[mm²]	0.25-2.5	–	0.25-4	–

¹⁾ The max. load current must not be exceeded by the total current of all connected conductors.

²⁾ Derating curves available on request.

3-conductor
modular terminal blocks



Type	Order No.	QTC 1,5-TWIN QTC 1,5-TWIN BU	3205048 3205051	QTC 1,5-TWIN-PE	3205064
Width / Length / Height	[mm]	5.2 / 76.4 / 39.3		5.2 / 76.4 / 39.3	
Current / Voltage (IEC)	[A] / [V]	17.5 / 800		– / –	
Solid	[mm²]	0.25-1.5		0.25-1.5	
Stranded	[mm²]	0.25-1.5		0.25-1.5	
AWG	–	24-16		24-16	



Type	Order No.	QTC 2,5-TWIN QTC 2,5-TWIN BU	3206445 3206461	QTC 2,5-TWIN-PE	3206474
Width / Length / Height	[mm]	6.2 / 82.5 / 42.8		6.2 / 82.5 / 42.8	
Current / Voltage (IEC)	[A] / [V]	24 / 800		– / –	
Solid	[mm²]	0.5-2.5		0.5-2.5	
Stranded	[mm²]	0.5-2.5		0.5-2.5	
AWG	–	20-14		20-14	

3-cond. hybrid terminals

– Screw connection



Type	Order No.	QTCU 1,5-TWIN QTCU 1,5-TWIN BU QTCU 1,5-TWIN-PE	3050044 3050057 3050060	QTCU 2,5-TWIN QTCU 2,5-TWIN BU QTCU 2,5-TWIN-PE	3050303 3050316 3050329
Width / Length / Height	[mm]	5.2 / 76.4 / 42.8		6.2 / 82.5 / 42.8	
Current / Voltage ¹⁾ (IEC)	[A] / [V]	17.5 / 800		24 / 800	
Screw		QTC		QTC	
Solid / AWG	[mm²] / –	0.14-4 / 26-12	0.25-1.5 / 24-16	0.14-6 / 26-10	0.5-2.5 / 20-14
Stranded / AWG	[mm²] / –	0.14-2.5 / 26-14	0.25-1.5 / 24-16	0.14-4 / 26-12	0.5-2.5 / 20-14
Stranded with ferrule	[mm²]	0.25-2.5	–	0.25-4	–

3-cond. hybrid terminals

– Spring-cage connection



Type	Order No.	QTCS 1,5-TWIN QTCS 1,5-TWIN BU QTCS 1,5-TWIN-PE	3206348 3206351 3206364	QTCS 2,5-TWIN QTCS 2,5-TWIN BU QTCS 2,5-TWIN-PE	3050332 3050345 3050358
Width / Length / Height	[mm]	5.2 / 71.6 / 39.3		6.2 / 82.5 / 39.3	
Current / Voltage ¹⁾ (IEC)	[A] / [V]	17.5 / 800		24 / 800	
Spring-cage		QTC		QTC	
Solid / AWG	[mm²] / –	0.08-4 / 28-12	0.25-1.5 / 24-16	0.08-6 / 28-10	0.5-2.5 / 20-14
Stranded / AWG	[mm²] / –	0.08-2.5 / 28-14	0.25-1.5 / 24-16	0.08-4 / 28-12	0.5-2.5 / 20-14
Stranded with ferrule	[mm²]	0.25-2.5	–	0.25-4	–

³⁾ For power dissipation, see CLIPLINE catalog.

⁴⁾ For PE terminal blocks [A] / [V]: – / –

⁵⁾ For LED versions, see CLIPLINE catalog.

4-conductor
modular terminal blocks



Type	Order No.	QTC 1,5-QUATTRO QTC 1,5-QUATTRO BU	3205077 3205080	QTC 1,5-QUATTRO-PE	3205093
Width / Length / Height	[mm]	5.2 / 94.0 / 39.3		5.2 / 94.0 / 39.3	
Current / Voltage (IEC)	[A] / [V]	17.5 / 800		– / –	
Solid	[mm²]	0.25-1.5		0.25-1.5	
Stranded	[mm²]	0.25-1.5		0.25-1.5	
AWG	–	24-16		24-16	

Double-level
modular terminal blocks

Also available as diode terminal blocks - see CLIPLINE catalog.



Type	Order No.	QTTCB 1,5 QTTCB 1,5 BU QTTCB 1,5-PV ¹⁾	3205116 3205129 3205153	QTTCB 1,5-PE	3205132
Width / Length / Height	[mm]	5.2 / 99.6 / 49.9		5.2 / 99.6 / 49.9	
Current / Voltage (IEC)	[A] / [V]	17.5 / 500		– / –	
Solid	[mm²]	0.25-1.5		0.25-1.5	
Stranded	[mm²]	0.25-1.5		0.25-1.5	
AWG	–	24-16		24-16	

Double-level hybrid terminals

– Screw connection



Type	Order No.	QTTCBU 1,5 QTTCBU 1,5 BU QTTCBU 1,5-PV ¹⁾	3050264 3050280 3050361	QTTCBU 1,5-PE	3050277
Width / Length / Height	[mm]	5.2 / 93.5 / 55.5		5.2 / 93.5 / 55.5	
Current / Voltage (IEC)	[A] / [V]	17.5 / 500		– / –	
Screw		QTC		QTC	
Solid / AWG	[mm²] / –	0.14-4 / 26-12	0.25-1.5 / 24-16	0.14-4 / 26-12	0.25-1.5 / 24-16
Stranded / AWG	[mm²] / –	0.14-2.5 / 26-14	0.25-1.5 / 24-16	0.14-2.5 / 26-14	0.25-1.5 / 24-16
Stranded with ferrule	[mm²]	0.25-2.5	–	0.25-2.5	–

Double-level hybrid terminals


– Spring-cage connection



Type	Order No.	QTTCBS 1,5 QTTCBS 1,5 BU QTTCBS 1,5-PV ¹⁾	3050222 3050235 3206380	QTTCBS 1,5-PE	3050248
Width / Length / Height	[mm]	5.2 / 88.2 / 49.9		5.2 / 88.2 / 49.9	
Current / Voltage (IEC)	[A] / [V]	17.5 / 500		– / –	
Spring-cage		QTC		QTC	
Solid / AWG	[mm²] / –	0.08-4 / 28-12	0.25-1.5 / 24-16	0.08-4 / 28-12	0.25-1.5 / 24-16
Stranded / AWG	[mm²] / –	0.08-2.5 / 28-14	0.25-1.5 / 24-16	0.08-2.5 / 28-14	0.25-1.5 / 24-16
Stranded with ferrule	[mm²]	0.25-2.5	–	0.25-2.5	–

¹⁾ With QTC 1,5-TG, cannot be used as combination.

Knife/disconnect and
fuse terminal blocks



Type	Order No.	QTC 1,5-MT QTC 1,5-TG	3205103 3205145	QTC 1,5-TWIN-MT QTC 1,5-TWIN-TG	3050407 3050413
Width / Length / Height	[mm]	5.2 / 76.4 / 39.3		5.2 / 94.0 / 39.3	
Current / Voltage (IEC)	[A] / [V]	17.5 / 500		17.5 / 400	
Solid	[mm²]	0.25-1.5		0.25-1.5	
Stranded	[mm²]	0.25-1.5		0.25-1.5	
AWG	–	24-16		24-16	



Type	Order No.	QTC 2,5-MT QTC 2,5-TG	3206487 3206490	QTC 2,5-HESI (5x20) ³⁾	3050293	QTC 2,5-HEDI	3206678
Width / Length / Height	[mm]	6.2 / 82.5 / 42.8		6.2 / 82.5 / 64.0		6.2 / 82.5 / 64.0	
Current / Voltage (IEC)	[A] / [V]	20 / 500		6.3 / 250 (fuse)		20 / 500	
Solid	[mm²]	0.5-2.5		0.5-2.5		0.5-2.5	
Stranded	[mm²]	0.5-2.5		0.5-2.5		0.5-2.5	
AWG	–	20-14		20-14		20-14	

QT-Combi terminal blocks

– pluggable connection



Type	Order No.	QTC 1,5/1P QTC 1,5/1P BU	3050073 3050086	QTC 1,5/1P-PE	3050099	See table Plugs with fast connection system
Width / Length / Height	[mm]	5.2 / 53.5 / 39.3		5.2 / 53.5 / 39.3		5.2 / 20.0 / 39.0
Current / Voltage (IEC)	[A] / [V]	17.5 ³⁾ / 500		– / –		17.5 ³⁾ / 500
Solid	[mm²]	0.25-1.5		0.25-1.5		0.25-1.5
Stranded	[mm²]	0.25-1.5		0.25-1.5		0.25-1.5
AWG	–	24-16		24-16		24-16



QP 1,5/1-L (1-pos.)	3051014
QP 1,5/1-L BU	3051027
QP 1,5/1-L GNYE	3051030
QP 1,5/1-M	3051043
QP 1,5/1-M BU	3051056
QP 1,5/1-M GNYE	3051069
QP 1,5/1-R	3051072
QP 1,5/1-R BU	3051085
QP 1,5/1-R GNYE	3051098

Type	Order No.	QTTCB 1,5/2P QTTCB 1,5/2P BU QTTCB 1,5/2P-PV ¹⁾	3050196 3050206 3206377	QTTCB 1,5/2P-PE	3050219
Width / Length / Height	[mm]	5.2 / 87.8 / 49.9		5.2 / 87.8 / 49.9	
Current / Voltage (IEC)	[A] / [V]	17.5 ³⁾ / 500		– / –	
Solid	[mm²]	0.25-1.5		0.25-1.5	
Stranded	[mm²]	0.25-1.5		0.25-1.5	
AWG	–	24-16		24-16	

Further versions of the COMBI plugs including other connection systems are documented in the Supplement Catalog 2006.

Fax

☐ I would like to receive information on the subject of "CLIPLINE"

☐ I would like to receive further information on:

☐ Please send your newsletter to the e-mail address below.

☐ I would like a personal consultation without obligation.

Name

Company

Department

Address/P.O. Box

Postal Code/City

Phone

e-mail

☐ Catalog
Modular Terminal Blocks, Marking
and Mounting Materials, Tools
CLIPLINE



☐ Catalog
Industrial Plug Connectors
PLUSCON



☐ Catalog
PCB Connection Systems and
Electronic Housings
COMBICON



☐ Catalog
Surge Protection
TRABTECH



☐ Catalog
Signal Conditioning
INTERFACE



☐ Catalog
Automation Systems
AUTOMATIONWORX



☐ CD-ROM Complete Catalog

☐ Supplement Catalog

PHOENIX CONTACT GmbH & Co. KG
32823 Blomberg, Germany
Phone: ++49/52 35/3-00
Fax: ++49/52 35/3-1 07 99
www.phoenixcontact.com