

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



VARIOFACE front adapter, for SIMATIC® S7-300, only in connection with MINI MCR-2-V8-FLK 16. Connectable card: 331-1KF0...-0AB01.

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 301664
GTIN	4046356301664
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	85369010
Country of origin	Germany

Technical data

Dimensions

Width	23 mm
Height	30 mm
Depth	117 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Degree of protection	IP00

General

Max. permissible operating voltage	25 V AC
	60 V DC

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Technical data

General

Max. permissible current	50 mA (per path)
Mounting position	any

Standards and Regulations

Connection in acc. with standard	CUL
Standards/regulations	IEC 60664
	DIN EN 50178
Rated insulation voltage	63 V
Rated surge voltage	0.6 kV
Insulation	Functional insulation
Pollution degree	2
Overvoltage category	II

Connection data

Connection name	Field level
Connection method	IDC/FLK pin strip
Number of connections	1
Number of positions	16
Pitch	2.54 mm

Connection data 2

Connection name	Supply
Connection method	Screw connection
Conductor cross section solid	0.14 mm² ... 1.5 mm²
Conductor cross section flexible	0.14 mm² ... 1.5 mm²
Conductor cross section AWG	26 ... 16

Supported controller

Controller	SIEMENS S7-300 / ET 200 M
- suitable I/O card	6ES7 331-1KF0x-0AB0


Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Front adapters - FLKM 16-PA- 331-1KF//MINI-MCR - 2318237

Circuit diagram



Connection scheme FLKM 16-PA-331-1KF//MINI-MCR

Classifications

eCl@ss

eCl@ss 10.0.1	27242292
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27250300
eCl@ss 6.0	27249200
eCl@ss 7.0	27249290
eCl@ss 8.0	27249290
eCl@ss 9.0	27242292

ETIM

ETIM 4.0	EC002584
ETIM 5.0	EC002584
ETIM 6.0	EC002584
ETIM 7.0	EC002584

UNSPSC

UNSPSC 6.01	30211824
-------------	----------

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Classifications

UNSPSC

UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	32151601
UNSPSC 18.0	32151601
UNSPSC 19.0	32151601
UNSPSC 20.0	32151601
UNSPSC 21.0	32151601

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized			http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		30 V		
Nominal current IN		0.05 A		

cUL Recognized			http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		30 V		
Nominal current IN		0.05 A		

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Approvals

EAC



RU C-
DE.A*30.B.01742

cULus Recognized



Accessories

Accessories

System adapter

System adapter - MINI MCR-2-V8-FLK 16 - 2901993



Eight MINI Analog Pro signal conditioners and measuring transducers can be connected to a controller with minimal cabling effort and without any errors using system adapters and system cabling.

System cable

Cable - FLK 16/EZ-DR/ 50/KONFEK - 2299291



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 0.5 m

Cable - FLK 16/EZ-DR/ 100/KONFEK - 2299301



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 1 m

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Accessories

Cable - FLK 16/EZ-DR/ 150/KONFEK - 2299314



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 1.5 m

Cable - FLK 16/EZ-DR/ 200/KONFEK - 2299327



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 2 m

Cable - FLK 16/EZ-DR/ 300/KONFEK - 2299330



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 3 m

Cable - FLK 16/EZ-DR/ 400/KONFEK - 2299343



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 4 m

Cable - FLK 16/EZ-DR/ 600/KONFEK - 2299356



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 6 m

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Accessories

Cable - FLK 16/EZ-DR/ 800/KONFEK - 2299369



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 8 m

Cable - FLK 16/EZ-DR/1000/KONFEK - 2299372



Round cable set; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position); cable length: 10 m

Cable - FLK 16/EZ-DR/ 100/KONFEK/S - 2304542



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 1 m

Cable - FLK 16/EZ-DR/ 200/KONFEK/S - 2304555



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 2 m

Cable - FLK 16/EZ-DR/ 150/KONFEK/S - 2304623



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 1.5 m

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Accessories

Cable - FLK 16/EZ-DR/ 600/KONFEK/S - 2314477



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 6 m

Cable - FLK 16/EZ-DR/ 50/KONFEK/S - 2318075



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 0.5 m

Cable - FLK 16/EZ-DR/ 300/KONFEK/S - 2318088



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 3 m

Cable - FLK 16/EZ-DR/ 400/KONFEK/S - 2318091



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 4 m

Cable - FLK 16/EZ-DR/ 800/KONFEK/S - 2318101



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 8 m

Front adapters - FLKM 16-PA- 331-1KF/I/MINI-MCR - 2318237

Accessories

Cable - FLK 16/EZ-DR/1000/KONFEK/S - 2318114



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 10 m

Cable - FLK 16/EZ-DR/ 500/KONFEK/S - 2318965



Assembled shielded round cable; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 16-position) (The braided shield is routed to a separate cable end.); cable length: 5 m
