


PCB 继电器

HJR-3FF

- 10A switching capability
- Small footprint
- Sealed type available
- Class B/F available
- Conform to RoHS,ELV directive



19.2×15.5×15.5

■ ORDERING CODE 订购代码

HJR-3FF— <u>S</u> — <u>H</u> <u>F</u> (<u>TBF-1</u>) / <u>12VDC</u>					
1	2	3	4	5	6
1. Relay Model 继电器型号				4. Temperature Range 环境温度	5. Insulated Level 绝缘等级
2. Sealed 密封				F: UL/TUV 105°C	TBF-1: Class F 级
3. 触点转换形式				VDE 85°C	Nil: 标准
H: Form A				Nil: UL/TUV 85°C	6. Coil Nominal Voltage 线圈额定电压
Z: Form C				VDE 70°C	3,5,6,9,12,18,24,48VDC

■ COIL DATA 线圈参数 (at 20°C)

Nominal Voltage额定电压(VDC)	3	5	6	9	12	18	24	48	0.36W
Coil Resistance线圈阻值 (Ω ±10%)	25	69	100	225	400	900	1600	6400	
Rated Current额定电流(mA)	120	71.4	60	40	30	20	15	7.5	
Max Operate Voltage 最大吸合电压(VDC)	2.25	3.75	4.5	6.75	9	13.5	18	36	
Min Release Voltage最小释放电压(VDC)	0.15	0.25	0.3	0.45	0.6	0.9	1.2	2.4	
Max ApplicableVoltage 最大过载电压	70℃时额定电压的130%，23℃时额定电压的170%								

■ CONTACT DATA 触点参数

Contact Form触点形式	1H/1Z
Contact Material触点材料	Silver Alloy
Load负载	Resistive load(COS Φ =1)
Contact Ratings触点负载	1H:10A 240VAC 12A 120VAC 1Z: 7A 240VAC 10A 120VAC
Minimum load 最小负载	100mA 5VDC
Max Switching Voltage最大转换电压	250VAC/30VDC
Max Switching Current最大转换电流	15A
Max Switching Power 最大转换功率	2770VA/240W
Contact Resistance接触电阻	100m Ω Max at 6VDC 1A
Life Expectancy寿命	Electrical 电气寿命: 100,000 Operations(at30Operations/minute)
	Mechanical机械寿命: 10,000,000 Operations(at300Operations/minute)


■ CHARACTERISTICS DATA 性能参数

Insulation Resistance绝缘阻值	100M Ω Min at 500VDC
Dielectric Strength Between Open Contacts触点间耐压	750VAC(50/60Hz for one minute)
Between Contacts and coil触点与线圈间耐压	1500VAC(50/60Hz for one minute)
Operate Time吸合时间	10ms
Release Time释放时间	5ms
Temperature Range环境温度	-40℃to+85℃
Shock Resistance冲击	Operating Extremes动作极限: 10G
	Damage Limits破坏极限: 100G
Vibration Resistance振动	10-55Hz, 1.5mm
Max. switching frequency最大转换频率	Mechanical: 18,000 operations/hr
	Electrical: 1,800 operations/hr
Humidity湿度	40-85%
Weight重量	Approx 10g
Safety Standard安全标准	UL cUL TÜV CQC VDE


■ APPROVED STANDARDS 安全标准

Model(型号)	Coiling rating (线圈电压)	Safety Standard (安全标准)	Contact rating (触点负载)
HJR-3FF	3 to 48VDC	TÜV	1H: 15A 125VAC
			10A 240VAC
			1Z: 15A 125VAC
			7A 240VAC
		UL/cUL	1H: 10A 240VAC
			12A 120VAC
			1Z: 7A 240VAC
			10A 120VAC
		VDE	1H: 7A 250VAC/30VDC
			1Z: 7A 250VAC/30VDC
		CQC	7A 240VAC
			1H: 10A 240VAC

■ ENGINEERING DATA 设计参数



■ OVERALL AND MOUNTING DIMENSIONS 安装图



声 明:
本产品规格书仅供客户使用时参考，如有更改，恕不另行通知。