





features

- Varistors own two-way symmetries and can absorb positive and negative surges
- Multilayer construction allows its small size to absorb a large surge
- Small space and high density mounting available due to the small package
- Suitable for both flow and reflow solderings
- Products with lead free termination meet EU RoHS requirements

dimensions and construction



Type (Inch Size Code)	Dimensions inches (mm)			
	L	W	t	d
1J (0603)	.063±.006 (1.6±0.15)	.031±.006 (0.8±0.15)	.031±.006 (0.8±0.15)	.016 ^{+0.006} _{-.008} (0.4 ^{+0.15} _{-0.2})
2A (0805)	.079±.008 (2.0±0.2)	.049±.008 (1.25±0.2)	.051 max. (1.3 max.)	.02±.010 (0.5±0.25)
2B (1206)	.126±.008 (3.2±0.2)	.063±.008 (1.6±0.2)	.065 max. (1.65 max.)	.02 ^{+0.014} _{-.010} (0.5 ^{+0.35} _{-0.25})

ordering information

NV73	A	1J	T	TE	12
Type	Energy Code	Size	Termination Material	Packaging	Varistor Voltage
	A B C	1J: 0603 2A: 0805 2B: 1206	T: Sn	TE: 7" embossed plastic (2,500 pieces/reel)	

The terminal surface material lead free is standard.

Contact us when you have control request for environmental hazardous material other than the substance specified by EU-RoHS.

For further information on packaging, please refer to Appendix A.

applications and ratings

Part Designation	Varistor Voltage Vc	Maximum Allowable Voltage		Clamping Voltage		Maximum Energy E (J)	Maximum Peak Current I _P (A) (2 times)	Operating Temp. T _{opt} (°C)	Storage Temp. T _{stg} (°C)
	I _c = 1mA (V)	a.c rms (V)	d.c (V)	V _{1A}	V _{2A}				
NV73A1JTTE8.2	6.8 - 9.8	4.2	6.0	—	21	0.1	30	-40°C to +85°C	-40°C to +125°C
NV73A1JTTE12	10 - 14.4	6.1	8.6	—	29				
NV73A1JTTE15	12.5 - 18	7.6	10.8	—	35				
NV73A1JTTE18	16 - 20	9.1	12.8	—	37				
NV73A1JTTE20	18 - 22	10.6	15.0	—	40				
NV73A1JTTE22	19 - 24	12.0	16.5	—	42				
NV73A1JTTE24	21.8 - 26.5	14.0	18.0	—	46				
NV73A1JTTE27	25 - 32	17.0	22.0	—	49	0.01	10		
NV73A2ATTE8.2	6.8 - 9.8	4.2	6.0	18	—	0.03	20		
NV73A2ATTE12	10 - 14.4	6.1	8.6	24	—	0.04			
NV73A2ATTE15	12.5 - 18	7.6	10.8	29	—				
NV73A2ATTE18	16 - 20	9.1	12.8	29	—				
NV73A2ATTE20	18 - 22	10.6	15.0	33	—	0.05			
NV73A2ATTE22	19 - 24	12.0	16.5	39	—				
NV73A2ATTE24	21.8 - 26.5	14.0	18.0	42	—	0.06			
NV73A2ATTE27	25 - 32	17.0	22.0	50	—	0.07			
NV73A2ATTE33	30 - 39	20.0	26.0	60	—	0.12			
NV73A2ATTE39	37 - 47	25.0	31.0	72	—	0.14	25		
NV73A2ATTE47	45 - 54	30.0	38.0	86	—	0.16			
NV73B2ATTE8.2	6.8 - 9.8	4.2	6.0	—	18	0.03	20		
NV73B2ATTE12	10 - 14.4	6.1	8.6	—	24	0.05	35		
NV73B2ATTE15	12.5 - 18	7.6	10.8	—	30	0.07			
NV73B2ATTE18	16 - 20	9.1	12.8	—	32	0.08			
NV73B2ATTE20	18 - 22	10.6	15.0	—	36	0.09			
NV73B2ATTE22	19 - 24	12.0	16.5	—	40	0.11			
NV73B2ATTE24	21.8 - 26.5	14.0	18.0	—	42	0.12			
NV73B2ATTE27	25 - 32	17.0	22.0	—	58	0.24			
NV73B2ATTE33	30 - 39	20.0	26.0	—	66	0.25	50		
NV73C2ATTE8.2	6.8 - 9.8	4.2	6.0	—	18	0.04	25		
NV73C2ATTE12	10 - 14.4	6.1	8.6	—	24	0.09	50		
NV73C2ATTE15	12.5 - 18	7.6	10.8	—	29	0.11			
NV73C2ATTE18	16 - 20	9.1	12.8	—	32	0.13			
NV73C2ATTE20	18 - 22	10.6	15.0	—	35	0.14			
NV73C2ATTE22	19 - 24	12.0	16.5	—	40	0.17			
NV73C2ATTE24	21.8 - 26.5	14.0	18.0	—	42	0.18			
NV73A2BTTE27	25 - 32	17.0	22.0	—	55	0.13			
NV73A2BTTE33	30 - 39	20.0	26.0	—	60	0.15	40		
NV73A2BTTE39	37 - 47	25.0	31.0	—	72	0.18			
NV73A2BTTE47	45 - 54	30.0	38.0	—	85	0.22			
NV73A2BTTE56	52 - 62	35.0	45.0	—	100	0.26			

applications and ratings (continued)

Part Designation	Varistor Voltage Vc	Maximum Allowable Voltage		Clamping Voltage		Maximum Energy E (J)	Maximum Peak Current I _P (A) (2 times)	Operating Temp. T _{opt} (°C)	Storage Temp. T _{stg} (°C)
	I _c = 1mA (V)	a.c rms (V)	d.c (V)	V _{1A}	V _{2A}				
NV73B2BTTE8.2	6.8 - 9.8	4.2	6.0	—	18	0.03	30	-40°C to +85°C	-40°C to +125°C
NV73B2BTTE12	10 - 14.4	6.1	8.6	—	24	0.07	50		
NV73B2BTTE15	12.5 - 18	7.6	10.8	—	29	0.09			
NV73B2BTTE18	16 - 20	9.1	12.8	—	32	0.1			
NV73B2BTTE20	18 - 22	10.6	15.0	—	35	0.11			
NV73B2BTTE22	19 - 24	12.0	16.5	—	40	0.12			
NV73B2BTTE24	21.8 - 26.5	14.0	18.0	—	42	0.14			
NV73B2BTTE27	25 - 32	17.0	22.0	—	52	0.16			
NV73C2BTTE8.2	6.8 - 9.8	4.2	6.0	—	18	0.06	40		
NV73C2BTTE12	10 - 14.4	6.1	8.6	—	24	0.1	70		
NV73C2BTTE15	12.5 - 18	7.6	10.8	—	29	0.13			
NV73C2BTTE18	16 - 20	9.1	12.8	—	29	0.15			
NV73C2BTTE20	18 - 22	10.6	15.0	—	31	0.17			
NV73C2BTTE22	19 - 24	12.0	16.5	—	35	0.19			
NV73C2BTTE24	21.8 - 26.5	14.0	18.0	—	38	0.2			
NV73C2BTTE27	25 - 32	17.0	22.0	—	48	0.24			

environmental applications

Performance Characteristics


Parameter	Requirement Δ V±%	Test Method
Varistor Voltage	Within specified tolerance	Voltage between terminals when 1mA is flowed
Solderability	95% coverage minimum	230°C ± 5°C, 4 seconds ± 1 second
Resistance to Solder Heat	±10%	270°C ± 5°C, 3 seconds ± 0.5 second
Rapid Change of Temperature	±10%	-40°C (30 minutes), +125°C (30 minutes), 30 cycles
Maximum Peak Current	±10%	A single standard impulse of 8/20μ seconds, positive/negative applied once each
Maximum Energy	±10%	A single standard impulse of 2ms, once
High Temperature Life with d.c. Bias	±10%	85°C ± 5°C, 1000h, Load: Maximum allowable circuit voltage (d.c.)
High Temperature Life with a.c. Bias**	±10%	85°C ± 5°C, 1000h, Load: Maximum allowable circuit voltage (V _{a.c.r.m.s.})
High Temperature & High Humidity Life with d.c. Bias	±10%	40°C ± 5°C, 95% RH, 500h, Load: Maximum allowable voltage (d.c.)
Capacitance*	Typical	1kHz: Others, 1MHz: Varistor voltage 120V
High Temperature Storage Life	±10%	125°C ± 5°C, 1000h
Low Temperature Storage Life	±10%	-40°C ± 5°C, 1000h

For Voltage Current Curves Graphs see Environmental Applications. Additional environmental applications can also be found at www.koaspeer.com


environmental applications (continued)

Voltage-Current Curves (Ta = 25°C)


NV73A 1J




NV73A 2A




NV73B 2A



NV73C 2A



NV73A 2B




Specifications given herein may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

3/28/25


environmental applications (continued)

Voltage-Current Curves (Ta = 25°C)

NV73B 2B



NV73C 2B



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KOA Speer:](#)

[NV73A1JTTE27](#) [NV73A2BTTE56](#) [NV73A2BTTE47](#) [NV73A2ATTE27](#) [NV73A1ETTP18](#) [NV73A1ETTP8](#)
[NV73A1HTTBM12](#) [NV73A1JTTE12](#) [NV73A1JTTE15](#) [NV73A1JTTE18](#) [NV73A1JTTE20](#) [NV73A1JTTE22](#)
[NV73A1JTTE24](#) [NV73A1JTTE8.2](#) [NV73A2ATTE12](#) [NV73A2ATTE15](#) [NV73A2ATTE18](#) [NV73A2ATTE20](#)
[NV73A2ATTE22](#) [NV73A2ATTE24](#) [NV73A2ATTE33](#) [NV73A2ATTE39](#) [NV73A2ATTE47](#) [NV73A2ATTE8.2](#)
[NV73A2BTTE27](#) [NV73A2BTTE33](#) [NV73A2BTTE39](#) [NV73A2ETTE110](#) [NV73A2ETTE18](#) [NV73A2ETTE33](#)
[NV73A2LTTE110](#) [NV73A2LTTE12](#) [NV73A2LTTE15](#) [NV73A2LTTE18](#) [NV73A2LTTE24](#) [NV73A2LTTE33](#)
[NV73A2LTTE68](#) [NV73AL1ETTP12](#) [NV73AL1ETTP120](#) [NV73AL1ETTP21](#) [NV73AL1ETTP28](#) [NV73B2ATTE12](#)
[NV73B2ATTE15](#) [NV73B2ATTE18](#) [NV73B2ATTE20](#) [NV73B2ATTE22](#) [NV73B2ATTE24](#) [NV73B2ATTE27](#)
[NV73B2ATTE33](#) [NV73B2ATTE8.2](#) [NV73B2BTTE12](#) [NV73B2BTTE15](#) [NV73B2BTTE18](#) [NV73B2BTTE20](#)
[NV73B2BTTE22](#) [NV73B2BTTE24](#) [NV73B2BTTE27](#) [NV73B2BTTE8.2](#) [NV73B2JTTE27](#) [NV73B2JTTE33](#)
[NV73B2LTTE24](#) [NV73C2ATTE12](#) [NV73C2ATTE15](#) [NV73C2ATTE18](#) [NV73C2ATTE20](#) [NV73C2ATTE22](#)
[NV73C2ATTE24](#) [NV73C2ATTE8.2](#) [NV73C2BTTE12](#) [NV73C2BTTE15](#) [NV73C2BTTE18](#) [NV73C2BTTE20](#)
[NV73C2BTTE22](#) [NV73C2BTTE24](#) [NV73C2BTTE27](#) [NV73C2BTTE8.2](#) [NV73TK001KIT](#)