





PC card drilling dimensions(after plating)
(thickness 1.60±0.20mm)



FOR ROHS DETAILS REFER DWG.NO:C01-8646-0000

European Views

www.fciconnect.com			surface ISO 1302		✓	tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED								
Dr	JOHN SLEEBA	1999/05/17	ANGULAR		LINEAR		0.X	±0.1	size A3	Scale 1:1	
Eng	GEORGE VJ	1999/05/17					0.XX	±0.1			
Chr	GEORGE VJ	2005/07/27					0.XX* ±1°	0.XXX			
Appr	KVSD	2005/07/27	Product family					D-SUB	Spec ref -		
			title MALE CONNECT.DELTA D RIGHT ANGLE WITH FEMALE SCREWLOCK.					dwg no C01-8646-0673		Rev. B	

						PART NUMBER	
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	G±0.25	Plating,0.76μ AU	Plating,Flash AU
09	30.81	24.99	16.96	16.79	5.90	D09P23B6PV00**	D09P23B4PV00**
15	39.14	33.32	25.18	25.12	5.90	D15P23B6PV00**	D15P23B4PV00**
25	53.03	47.04	39.12	38.84	5.70	D25P23B6PV00**	D25P23B4PV00**
37	69.32	63.50	55.68	55.30	5.70	D37P23B6PV00**	D37P23B4PV00**

Technical characteristics:
Shell, steel tin/Zinc Cr3 plated
Insulators: self-extinguishing black polyster, UL class 94V0
Contacts size 20: brass, gold on mating end, bright tin
on termination end over nickel on entire contact
Cycles : 500 for protection 6
 : 200 for protection 4

Female screwlock:brass,tin plated torque:0.7N/m

Electrical characteristics.

max.current rating:5A
Test voltage:1000V
Rated voltage:300V
Contact resistance:≤15mΩ
Shell resistance:≤5mΩ
Insulation resistance:≥5000MΩ

Climatic characteristics:

Operating temperature range, -55°C +125°C

Dimensions:

In accordance with MIL-C-24308

LF FOR LEAD FREE

REV F - 2006-04-17

PDM: Rev:C STATUS:Released Printed: Jan 18, 2011