





SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ○ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	
		7		
		LAST NO. USED	5	

DWG STATUS				REVISION HISTORY			AUTH	DR	AP/VD
DATE	STG	REV	N/P	CHG	ZONE				
13NO02	R	01	-	-		REDRAWN TO PD	233309	JYD	6M
13JA03	R	02	-	-		UPDATED PDM ATTRIBUTES	235437	JYD	6M
01FE06	R	03	-	-		12089247 - MAT'L SPEC WAS M3592002	276997	RTV	JVM/EST
05JN07	R	04	-	-		ALL PARTS - UPDATED MATERIAL SPEC AND REMOVED RECYCLING CODE AND NOTE	401610	ECB	AUG/BDG



NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 12047785
- THIS CONNECTOR WILL PASS THRU A ϕ 18.5 MIN. HOLE.
- THIS PART ACCEPTS THE FOLLOWING COMPONENTS OR EQUIVALENT:
SECONDARY LOCK 12047787
(1 PER CONNECTOR)
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- THIS CONNECTOR LIMITED TO A MAX INSULATION CRIMP 3 HIGH AND 2.6 WIDE.
- (2.3X10.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.



12089247	02	AA	-	-	POLYAMIDE COMPOUND-CRM	12089248	2.142
12066037	A9	-	-	-	POLYAMIDE COMPOUND-WHT	12066036	2.142
12047786	A9	-	-	-	POLYAMIDE COMPOUND-BLK	12047785	2.142
PART NO	REV	N/P	STATUS		MATERIAL AND COLOR	MATING CONNECTOR	VOLUME (CM³)

(N/A) PROCESS SENSITIVE DIMENSION									
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED									
DIMENSIONAL RANGE (MM)									
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
TO	20	30	70	100	150	200	250	300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED									
±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2									
ANGULAR TOLERANCE 22°									

DWG TYPE		PART DRAWING	
STYLE		DISTR CODE	
VOLUME (CM³)		SEE CHART	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2003 DIMENSIONING AND TOLERANCE MANUAL (Y14.5M-2003). ALL DIMENSIONS AND RELATED DATUMS APPLY UNLESS OTHERWISE SPECIFIED. DIMENSIONS NOT APPLICABLE WHEN RELATIONSHIP BETWEEN FEATURES IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES. SEPARATE PART OR CALLOUTS MAY BE SHOWN SEPARATELY, REMAINING OF DATUM REFERENCE. ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		USE MATH DATA	

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WYOMING, OH	
DR	DATE
APVD1 JESUS YEE	13NO02
APVD2 JESUS YEE	13NO02
APVD3 GERARDO MACIAS	13NO02
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME	
TAXI CONN M M/P 150	
DRAWING NUMBER	
12066047	
SIZE A0	SCALE 5:1
FRAME NO 1	SHEET NO 1
STG REV N/P	R 04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[12047786-B](#)