



Specification


400ST120	Transmitter
400SR120	Receiver
Center Frequency	40.0±1.0Khz
Bandwidth (-6dB)	400ST120 2.0Khz
	400SR120 2.0Khz
Transmitting Sound Pressure Level	115dB min.
at 40.0Khz; 0dB re 0.0002μbar per 10Vrms at 30cm	
Receiving Sensitivity	-67dB min.
at 40.0Khz 0dB = 1 volt/μbar	
Capacitance at 1Khz	±20% 2400 pF
Max. Driving Voltage (cont.)	20Vrms
Total Beam Angle	-6dB 85° typical
Operation Temperature	-30 to 80°C
Storage Temperature	-40 to 85°C

All specification taken typical at 25°C
Closer frequency tolerance can be supplied upon request.

Model available:

1	400ST/R120	Aluminum Housing
2	400ST/R12B	Black Al. Housing


Dimensions: dimensions are in mm



Impedance/Phase Angle vs. Frequency


Tested under 1Vrms Oscillation Level

400SR120 Impedance ——— (red solid line)
400SR120 Phase ——— (blue solid line)
400ST120 Impedance (red dotted line)
400ST120 Phase (blue dotted line)




Sensitivity/Sound Pressure Level

Tested under 10Vrms @30cm




Beam Angle: Tested at 40.0Khz frequency




400SR120 Receiver

400ST120 Transmitter


Sensitivity Variation vs. Loaded Resistor




SPL Variation vs. Driving Voltage




Center Frequency Shift vs. Loaded Resistor




Center Frequency Shift vs. Driving Voltage




Sensitivity Variation vs. Temperature



SPL Variation vs. Temperature



Center Frequency Shift vs. Temperature



Center Frequency Shift vs. Temperature

