


PRODUCT NUMBER
SEE TABLE



mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE				
ltr	ecn no	dr	date	tolerances unless otherwise specified							title			
L	J10329	CRG	6/6/01	angles	linear	.XX±.01/0.3					RIBCAGE III T/M			
M	M05-0123	MHT	6/6/05			.XXX±.005/0.13					VERT. HEADER ASS'Y			
N	M06-0225	ERE	06/12/06	0±2"		.XXXX±.0020/0.051					scale 4:1			
P	M06-0370	MHT	9/26/06	dr	M. CORNMAN	6/6/95			dwg no		sheet 1 of 6		size	
R	M09-0058	MHT	4/04/09	enrg	D. WHITING	6/6/95			95776				A3	
S	N10-0122	YO	5/10/10	chr	D. WHITING	6/6/95								
T	ELX-N-009749	YO	1/31/12	appd	D. WHITING	6/6/95								
sheet	revision	T	T	T	T	T	T			type	Product	Customer	Drawing	
index	sheet	1	2	3	4	5	6							




FCIconnect.com


Copyright FCI

PRODUCT NUMBER
SEE TABLE

SIZE	DIM H	DIM J	DIM K	DIM L
2X5	.275/6.99	.200/5.08	.372/9.45	.320/8.13
2X10	.525/13.34	.450/11.43	.622/15.80	.570/14.48
2X15	.775/19.68	.700/17.78	.872/22.15	.820/20.83
2X20	1.025/26.03	.950/24.13	1.122/28.50	1.070/27.18
2X25	1.275/32.38	1.200/30.48	1.372/34.85	1.320/33.53
2X30	1.525/38.74	1.450/36.83	1.622/41.20	1.570/39.88
2X35	1.775/45.08	1.700/43.18	1.872/47.55	1.820/46.23
2X40	2.025/51.43	1.950/49.53	2.122/53.90	2.070/52.58
2X45	2.275/57.78	2.200/55.88	2.372/60.25	2.320/58.93
2X50	2.525/64.14	2.450/62.23	2.622/66.60	2.570/65.28



SECTION X-X
ROTATED 90° CW




SECTION Y-Y

mat'l. code -				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family RIBCAGE			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		scale 4:1	title RIBCAGE III T/M VERT. HEADER ASS'Y		
T					angles	linear		dwg no 95776		
					0.002					
					dr	M. CORNMAN	6/6/95	sheet 2 of 6		size
					enr	D. WHITING	6/6/95			A3
					chr	D. WHITING	6/6/95			
					appd	D. WHITING	6/6/95			
sheet index	revision sheet							type Product Customer Drawing		


PRODUCT NUMBER
SEE TABLE

LOCATOR/HOLDDOWN VARIATIONS


STYLE
1





STYLE
2




STYLE
4



STYLE
6



STYLE
7




mat'l. code -				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family RIBCAGE				
ltr	ecn	no	dr	date	tolerances unless otherwise specified				INCH/MM		title RIBCAGE III T/M VERT. HEADER ASS'Y			
T					angles	linear	.XX±.01/0.3	scale 4:1						
							.XXX±.005/0.13							
					0.002?		.XXXX±.0020/0.051							
					dr	M. CORNMAN	6/6/95			dwg no		sheet3 of 6	size	
					engr	D. WHITING	6/6/95			95776		A3		
					chr	D. WHITING	6/6/95							
					appd	D. WHITING	6/6/95			type Product Customer Drawing				
sheet index		revision sheet												


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
6




STYLE
2



STYLE
7



STYLE
4




mat'l. code				surface	tolerance	projection	product family		
-				ISO 1302 ✓	ISO 406 ISO 1101		RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title		
T					angles linear	INCH/MM	RIBCAGE III T/M		
					0.001		VERT. HEADER ASS'Y		
					0.002	scale 4:1	dwg no		
					0.005		sheet 4 of 6		
					0.010		95776		
					0.020		A3		
					0.051	type	Product Customer Drawing		
					0.100				
sheet	revision								
index	sheet								


PRODUCT NUMBER
SEE TABLE

RECOMMENDED P. C. B. LAYOUT


STYLE
1




STYLE
2



STYLE
4



STYLE
6



mat'l. code -				surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 	product family RIBCAGE		
ltr	ecn	no	dr	date	tolerances unless otherwise specified				title		
T					angles	linear	.XX±.01/0.3	INCH/MM	RIBCAGE III T/M VERT. HEADER ASS'Y		
					0氣2?		.XXX±.005/0.13				
							.XXXX±.0020/0.051	scale 4:1	dwg no sheet 5 of 6 size		
					dr	M. CORNMAN	6/6/95		95776		
					enr	D. WHITING	6/6/95		A3		
					chr	D. WHITING	6/6/95				
					appd	D. WHITING	6/6/95		type Product Customer Drawing		
sheet index	revision sheet										

