THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	S2	REVISED PER ECR-16-017000	07DEC16	N.L	D.Z



SECTION B-B
SCALE 20:1



SECTION C-C
SCALE 20:1







SECTION A-A
SCALE 20:1

2. 0.0008 MIN GOLD INSIDE RECEPTACLE IN LOCALIZED PLATE AREA, OVER 0.0008 MIN NICKEL.

3. EITHER CAVITY WILL ACCEPT RECEPTACLE 350628,640392 OR PIN 350629,640391.

4. REELED ON PLASTIC REELS.

5. DOUBLE BAGGED VERSION OF 350628-8

-	-
.660	16.76
.375	9.53
.330	8.38
.200	5.08
.145	3.68
.130	3.30
.115	2.92
.110	2.79
.105	2.67
.095	2.41
.090	2.29
.085	2.16
.084	2.13
.082	2.08
.081	2.06
.079	2.01
.075	1.91
.050	1.27
.040	1.02
.025	0.63
.008	0.20
.005	0.13
.000030	0.0008
IN	MM
CONVERSION TABLE	



TYPICAL RECEPTACLE CAVITY SECTION
REFERENCE



TYPICAL PLUG CAVITY SECTION
REFERENCE

5	PRE-TIN	0.20 BRASS	1.27-2.79	24-18	350628-9
4	PRE-TIN	0.20 BRASS	1.27-2.79	24-18	350628-8
2		0.20 PH.BRZ.	1.27-2.79	24-18	350628-6
2		0.20 BRASS	1.27-2.79	24-18	350628-5
	PRE-TIN	0.20 PH.BRZ.	1.27-2.79	24-18	350628-2
	PRE-TIN	0.20 BRASS	1.27-2.79	24-18	350628-1
	FINISH	MATERIAL	INSULATION DIAMETER	WIRE RANGE	PART NO

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± 0.13
4 PLC ± -
ANGLES ± 0° 30'

MATERIAL: SEE TABLE
FINISH: SEE TABLE

DWN K. SALMON 9-30-91
CHK R. SWING 9-30-91
APVD C. CASH 10-1-91
PRODUCT SPEC 108-1037
APPLICATION SPEC 114-1013
WEIGHT —

TE Connectivity

NAME .062 SOCKET COMMERCIAL PIN & SOCKET -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-350628	—

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV S2