



Circuit Diagram



Dimensions: (In.)

## ■ Specifications:

- Primary voltage: 117/220VAC 50/60Hz
- Primary exciting current: 40/20mA max.
- Secondary voltage: 4.7, 6.4, 8.4, 12.3, 15.0VDC  $\pm 5\%$  (no load)  
2.3, 3.6, 5.1, 8.1, 10.8VDC  $\pm 5\%$  (full load)
- Rated secondary current: 300mA
- Temperature rise:  $<45^{\circ}\text{C}$
- Breakdown voltage (hipot): 1500VAC 50Hz for 1 minute
- Coil~coil insulation:  $100\text{M}\Omega$  min. @ 500VDC
- Cabinet: ABS materials
- Color: brown
- Capacitor 470mfd x 16V
- Rectifier: 1N4001 (4)
- Resistor:  $470\Omega$  7/4W
- Polarity: reversible polarity switch (+) ~ (-)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

41AC116