



OPTICALLY COUPLED BILATERAL SWITCH NON-ZERO CROSSING TRIAC

APPROVALS

- UL recognised, File No. E91231

'X' SPECIFICATION APPROVALS

- VDE 0884 in 3 available lead forms : -
- STD
- G form
- SMD approved to CECC 00802

DESCRIPTION

The MOC302_ series are optically coupled isolators consisting of a Gallium Arsenide infrared emitting diode coupled with a light activated silicon bilateral switch performing the functions of a triac mounted in a standard 6 pin dual-in-line package.


FEATURE

- Options :-
10mm lead spread - add G after part no.
Surface mount - add SM after part no.
Tape&reel - add SMT&R after part no.
- High Isolation Voltage ($5.3\text{kV}_{\text{RMS}}, 7.5\text{kV}_{\text{PK}}$)
- 400V Peak Blocking Voltage
- All electrical parameters 100% tested
- Custom electrical selections available



APPLICATIONS

- CRTs
- Power Triac Driver
- Motors
- Consumer appliances
- Printers

**OPTION SM
SURFACE MOUNT**



OPTION G



ABSOLUTE MAXIMUM RATINGS (25 °C unless otherwise noted)

Storage Temperature _____ -55°C - +150°C
Operating Temperature _____ -40°C - +100°C
Lead Soldering Temperature _____ 260°C
(1.6mm from case for 10 seconds)
Input-to-output Isolation Voltage (Pk) _____ 7500 Vac
(60 Hz , 1sec. duration)

INPUT DIODE

Forward Current _____ 50mA
Reverse Voltage _____ 6V
Power Dissipation _____ 70mW
(derate linearly 0.93mW/°C above 25°C)

OUTPUT PHOTO TRIAC

Off-State Output Terminal Voltage _____ 400V
RMS Forward Current _____ 100mA
Forward Current (Peak) _____ 1A
Power Dissipation _____ 300mW
(derate linearly 4.0mW/°C above 25°C)

POWER DISSIPATION

Total Power Dissipation _____ 330mW
(derate linearly 4.4mW/°C above 25°C)

ISOCOM COMPONENTS LTD
Unit 25B, Park View Road West,
Park View Industrial Estate, Brenda Road
Hartlepool, Cleveland, TS25 1YD
Tel: (01429) 863609 Fax : (01429) 863581

ISOCOM INC
1024 S. Greenville Ave, Suite 240,
Allen, TX 75002 USA
Tel: (214) 495-0755 Fax: (214) 495-0901
e-mail info@isocom.com
http://www.isocom.com

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ Unless otherwise noted)


PARAMETER		MIN	TYP	MAX	UNITS	TEST CONDITION
Input	Forward Voltage (V_F) Reverse Current (I_R)		1.2	1.5 100	V μA	$I_F = 10\text{mA}$ $V_R = 6\text{V}$
Output	Peak Off-state Current (I_{DRM}) Peak Blocking Voltage (V_{DRM}) On-state Voltage (V_{TM}) Critical rate of rise of off-state Voltage (dv/dt) (note 1) Critical rate of rise of commutating Voltage (dv/dt) (note 1)	400	1.5 10 0.1	100 3.0	nA V V $\text{V}/\mu\text{s}$ $\text{V}/\mu\text{s}$	$V_{\text{DRM}} = 400\text{V}$ (note 1) $I_{\text{DRM}} = 100\text{nA}$ $I_{\text{TM}} = 100\text{mA}$ (peak) $I_{\text{load}} = 15\text{mA}$, $V_{\text{IN}} = 30\text{V}$ (fig 1.)
Coupled	Input Current to Trigger (I_{FT}) (note 2) MOC3020 MOC3021 MOC3022 MOC3023 Holding Current , either direction (I_H) Input to Output Isolation Voltage V_{ISO}			30 15 10 5	mA mA mA mA μA V_{RMS} V_{PK}	$V_D = 3\text{V}$ (note 2) See note 3 See note 3

Note 1. Test voltage must be applied within dv/dt rating.


Note 2. Guaranteed to trigger at an I_F value less than or equal to max. I_{FT} , recommended I_F lies between Rated I_{FT} and absolute max. I_{FT} .

Note 3. Measured with input leads shorted together and output leads shorted together.


FIGURE 1




RMS On-state Current vs. Ambient Temperature




Normalised Repetitive Peak Off-state Voltage vs. Ambient Temperature




Forward Current vs. Ambient Temperature



On-state Voltage vs. Ambient Temperature



Normalised Input Trigger Current vs. Ambient Temperature



On-state Current vs. On-state Voltage

