


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .03$	W $\pm .01$	C $\pm .02$	M $\pm .03$	H $\pm .01$
PN22-4F	#4	.67 (17.02)	.20 (5.08)	.21 (5.33)	.57 (14.49)	.12 (3.05)
PN22-6F	#6	.77 (19.56)	.25 (6.35)	.26 (6.60)	.63 (16.00)	.15 (3.81)

NOTES:

- USED FOR:
 - #26-22 AWG SOLID OR STRANDED COPPER WIRE
 - 221° [105°C] MAX. TEMP. RATING
 - 300V MAX. VOLTAGE RATING
- INSTALLATION TOOLS: CT-520
- WIRE STRIP LENGTH: 3/16 $\pm \frac{1}{32}$ [4,8 ± 0.8]
- MATERIAL:
 - STAMPING: .02" [0,5] THK COPPER, TIN PLATED
 - HOUSING: NYLON, YELLOW
 - SLEEVE: BRASS, TIN PLATED
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT.



						TITLE	
						FORK TERMINALS, NYLON INSULATED	
						#26-22	
						CUSTOMER DRAWING	
						ITEM REVISION NAME	
						N41235BA/07	
						DATASET FILE NAME	
						N41235BA_DC/07A	
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL:
						.X $\pm$.1 [2.54] .XXX $\pm$.005 [.127]	SEE NOTES
						.XX $\pm$.01 [.25] ANGLES $\pm$ 5°	DRAWING NUMBER:
						THIRD ANGLE PROJECTION	A41235
07	04-26-13	JBN	RTFI	RTFI	UPDATED DRAWING BORDER & TITLE BLOCK	A41235	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	