

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

71349-1037

Status:

Active

Overview:

C-Grid® Products

Description:

2.54mm Pitch C-Grid® Header, Surface Mount, Dual Row, Vertical, Shrouded, 10 Circuits, 0.38µm Gold (Au) Selective Plating, without Press-fit Plastic Pegs

Documents:

3D Model

Drawing (PDF)

Product Specification PS-71349-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Overview

Product Name

UPC

PCB Headers

71349

Signal, Wire-to-Board

C-Grid® Products

C-Grid®

800753524415

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Retention

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Plating min - Mating

Plating min - Termination

Polarized to Mating Part

Shrouded

Stackable

Temperature Range - Operating

Termination Interface: Style

No

10

10

Black

50

No

94V-0

No

No

None

Yes

Brass, Phosphor Bronze

Gold

Tin

High Temperature Thermoplastic

2.356/g

2

Vertical

No

None

Tube

2.54mm

2.54mm

0.381µm

1.905µm

Yes

Fully

No

-40°C to +105°C

Surface Mount


Electrical

Current - Maximum per Contact

Voltage - Maximum

3A

250V



EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

71349Series

Mates With

70013 Interim Clip, 70450 Version A Crimp Housing, 71850 Through-hole Receptacle, 71395 SMT Receptacle

Solder Process Data

Duration at Max. Process Temperature (seconds)	30
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	245

Material Info

Reference - Drawing Numbers

Product Specification	PS-71349-001
Sales Drawing	SDA-71349-****

This document was generated on 12/27/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION