


Multilayer Chip Inductors for High Frequency Applications (HK series)

HK16081N2S-T



■ Features

- Item Summary
1.2nH±0.3nH, 0.3A, 0603/1608 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping paper 4000pcs

■ Products characteristics table

Inductance	1.2 nH ± 0.3nH
Case Size (EIA/JIS)	0603/1608
Rated Current (max)	0.3 A
DC Resistance (typ)	15 mΩ
DC Resistance (max)	50 mΩ
Q (min)	8
Q (typ)	14
LQ Measuring Frequency	100 MHz
Self Resonant Frequency (min)	10000 MHz
Self Resonant Frequency (typ)	13000 MHz
Operating Temp. Range	-40 to +85 °C
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow/Wave

■ External Dimensions

Dimension L	1.6 ±0.15 mm
Dimension W	0.8 ±0.15 mm
Dimension T	0.8 ±0.15 mm
Dimension e	0.3 ±0.2 mm

2016.05.21

The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the Date at any time without notice. Before making final selection, please check product specification.