

BSW-115-04-G-D

BSW-124-04-T-S-S

BSW-110-24-L-S

(2,54 mm) .100"

BSW SERIES

BOTTOM MOUNT SOCKET STRIPS

Mates with:
TSW, MTSW, HTSW,
MTLW, TSM, EW, ZW,
HW, DW, PHT

FEATURES

- Bottom mount socket strips accept .025" SQ terminals.
- Ideal for soldering and plugging from the same side of the board.
- For low profile connections and high temperature soldering.

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?BSW

Insulator Material:

Black Thermoplastic

Insulation Resistance:

5000 MΩ min

Contact Material:

Phosphor Bronze

Plating:

Au or Sn over
50μ" (1,27 μm) Ni

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Withstanding Voltage:

1000 VRMS @ 60 Hz

Contact Resistance:

10 mΩ

Insertion Depth:

(3,68 mm) .145" to

(6,35 mm) .250"

Insertion Force:

(Single contact only)

Standard = 8 oz (2,23 N) avg.

Low Insertion Force = 3 oz

(0,83 N) avg.

Withdrawal Force:

(Single contact only)

Standard = 8 oz (2,23 N) avg.

Low Insertion Force = 3 oz

(0,83 N) avg.

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



Note: Some lengths, styles and options are non-standard, non-returnable.

BSW	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OTHER OPTION
			-04 = Standard Lead	-L = 10μ" (0,25 μm) Gold contact, Matte Tin on tail		-S = Standoffs for single and double rows only.
			-24 = Low Insertion Force	-G = 20μ" (0,51 μm) Gold contact, Gold Flash on tail		
				-T = Matte Tin (N/A with Low Insertion Force)		

02 thru 36

Row Option	Z
-S*	(4,31) .170
-M	(3,43) .135
-E	(2,54) .100
-D*	(4,32) .170

*Less (0,38 mm) .015" with standoffs

ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

TIGER BUY CONTACT™

Row Option	X	Y
-S	(2,54) .100	(5,08) .200
-M	(3,81) .150	(6,35) .250
-E	(4,31) .170	(6,86) .270

Body design may vary slightly from drawing shown.


-S = Single Row

-M = Single Row More Plug Space

-E = Single Row Extended Plug Space

-D = Double Row

APPLICATIONS



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685