



Capacitors for Power Electronics

Series/Type: **B25667A**

The following products presented in this data sheet are being withdrawn.

Ordering Code	Substitute Product	Date of Withdrawal	Deadline Last Orders	Last Shipments
B25667A2317A375	B25667B3297A375	2004-09-10		

For further information please contact your nearest EPCOS sales office, which will also support you in selecting a suitable substitute. The addresses of our worldwide sales network are presented at www.epcos.com/sales.

Characteristics

C_N	Δ	3x 104,4 μ F $\pm$ 5 %
U_N		AC 230 V
f_N		50 Hz 60 Hz
Q_N		5,2 kvar 6,2 kvar
I_N		3x 13 A 16 A

$\tan\delta_0$ 0,2 W/kvar (dielectric)

Maximum ratings

$U_{\max}$	AC 250 V, 8 h daily AC 300 V, 1 min
$I_{r(40)}$	3x 25 A ($\Theta_A = 40^\circ\text{C}$, U_N)
I_s	4500 A
$(du/dt)_{\max}$	10 V/ μ s
$(du/dt)_s$	25 V/ μ s

Test data

U_{TT}	AC 500 V, 10 s
U_{TC}	AC 3000 V, 10 s

$\tan\delta$ (50 Hz) $\leq$ 0,6 W/kvar (total)

Climatic category -40/D


$\Theta_{\min}$	-40 °C
$\Theta_{\max}$	+55 °C
Humidity	Max. relative Humidity $\leq$ 95 %
Θ_{stg}	-55 bis +70 °C

Life expectancy

t_{LD}	100 000 h
----------	-----------

Remarks

Natural cooling


Design data

Dimensions $\varnothing \times l$	121,6 x 164 mm (4,79 x 6,46 in)
Approx. weight	1,3 kg (2,9 lb)
Impregnation	Gas
Fixing	Threaded bolt M12
Mounting hole	14 mm (0,55 in)
Max. torque	10 Nm
Terminals	Isolated terminal, IP20
Max. torque	1,2 Nm
Terminal cross section	16 mm ² (5 AWG)
Creepage distance	12,7 mm (0,50 in)
Clearance	9,6 mm (0,38 in)
Overpressure disconnecter	
Any mounting position possible	