

FO patch cable - FL SM PATCH 5,0 ST-ST - 2901838

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Assembled fiber optic cable, break-out cable, fiberglass single mode 9/125 µm (OS2, Low Water Peak Fiber), connector: B-FOC(ST®)/B-FOC(ST®), degree of protection: IP20, for installation in cable ducts or control cabinets, length: 5 m



Your advantages

- Single-mode patch cable for indoor installation
- Ideal for use in distributor systems and for connecting termination devices
- 2.8 mm single elements made from halogen-free and flame-retardant material



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 634113
GTIN	4046356634113

Technical data

Cable type

Cable abbreviation	I-V(ZN)H
Cable type	Single-mode fiberglass

Ambient conditions

Ambient temperature (operation)	-5 °C ... 70 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Ambient temperature (installation)	-5 °C ... 50 °C
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes

External sheath

Outer sheath, material	FRNC
External sheath, color	yellow
External sheath, strain relief elements	Non-metallic, aramide fiber
External diameter max.	5.7 mm

FO patch cable - FL SM PATCH 5,0 ST-ST - 2901838

Technical data

External sheath

External diameter min.	2.8 mm
------------------------	--------

Single wire

Single wires, quantity	2
Individual wire, diameter	900 µm
Single wire, strain relief elements	Non-metallic, aramide fibers

Mechanical properties

Bending radius short term/long term	30 mm
Bending radius, long-term	60 mm
Lateral pressure, long-term	60.00 N/cm
Tensile strength short-term/long-term	600 N
Cable, attenuation	0.38 dB/km
	0.28 dB/km

General

Conductor length	5.00 m
Cable weight	15.80 kg/km
Transmission characteristics (category)	OS2
Transmission speed	10 Gbps

Behavior in fire

Flame resistance	according to DIN 60332-1-2
	IEC 60332-3-22 (Cat. A)
Concentration of fumes	in accordance with IEC 61034
Halogen-free	According to IEC 60754-2
Behavior in fire	No corrosive or toxic fumes
	0.36 MJ/m

Attenuation

1300 nm	0.38 dB/km
1550 nm	0.28 dB/km

Standards and Regulations

Concentration of fumes	in accordance with IEC 61034
Flame resistance	according to DIN 60332-1-2
	IEC 60332-3-22 (Cat. A)
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Halogen-free	According to IEC 60754-2
Behavior in fire	No corrosive or toxic fumes
	0.36 MJ/m

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50

FO patch cable - FL SM PATCH 5,0 ST-ST - 2901838

Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	--

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>