

(1,27 mm) .050"

FTR-107-02-G-D-A

FTR-110-52-G-S

FTR-132-52-G-D-P

FTR SERIES

SMT MICRO HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FTR

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50µ" (1,27 µm) Ni

Current Rating (FTR/RSM):

3.1 A per pin

(1 pin powered per row)

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (02-20)

(0,15 mm) .006" max (21-40)

Mates with:
RSM, SMS, SLM

OPTIONS

-P OPTION

Single and
double row

(2,54 mm)
.100"

Surface
Mount

Micro pitch
(1,27 mm) .050"

Available with optional
Pick & Place Pad

RECOGNITIONS

For complete scope of
recognitions see
www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

Note: Some sizes, styles and options are non-standard, non-returnable.

FTR	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	ROW OPTION	OPTION																						
02 thru 40			Specify LEAD STYLE from chart	-L = 10µ" (0,25 µm) Gold on post, Matte Tin on tail -G = 10µ" (0,25 µm) Gold on post, Gold flash on tail	-S = Single Row -D = Double Row	-“XX” = Polarized -A = Alignment Pin (5 positions minimum -D only) (Metal or plastic at Samtec discretion) (N/A with -LC) -LC = Locking Clip (6 positions minimum -D only) (N/A with -A) (Manual placement required) -P = Plastic Pick & Place Pad (-D = 5 positions minimum) (-S = 8 positions minimum) -TR = Tape & Reel (-S = 4 positions minimum)																						
				<table border="1"> <thead> <tr> <th>LEAD STYLE</th> <th>B</th> </tr> </thead> <tbody> <tr><td>-01</td><td>(5,84) .230</td></tr> <tr><td>-02</td><td>(2,54) .100</td></tr> <tr><td>-03</td><td>(3,18) .125</td></tr> <tr><td>-51</td><td>(4,83) .190</td></tr> <tr><td>-52</td><td>(5,21) .205</td></tr> <tr><td>-53</td><td>(7,24) .285</td></tr> <tr><td>-54</td><td>(8,51) .335</td></tr> <tr><td>-55</td><td>(9,91) .390</td></tr> <tr><td>-56</td><td>(10,29) .405</td></tr> <tr><td>-57</td><td>(10,92) .430</td></tr> </tbody> </table>			LEAD STYLE	B	-01	(5,84) .230	-02	(2,54) .100	-03	(3,18) .125	-51	(4,83) .190	-52	(5,21) .205	-53	(7,24) .285	-54	(8,51) .335	-55	(9,91) .390	-56	(10,29) .405	-57	(10,92) .430
LEAD STYLE	B																											
-01	(5,84) .230																											
-02	(2,54) .100																											
-03	(3,18) .125																											
-51	(4,83) .190																											
-52	(5,21) .205																											
-53	(7,24) .285																											
-54	(8,51) .335																											
-55	(9,91) .390																											
-56	(10,29) .405																											
-57	(10,92) .430																											

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: +1-800-SAMTEC-9 or +1-812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: +1-408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: +1-800-726-8329
 SAMTEC SOUTH AMERICA • Tel: +55 31 3786 3227 SAMTEC UNITED KINGDOM • Tel: +44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: +33 1 60 95 06 60 SAMTEC ITALY • Tel: +39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46 8 4477280 SAMTEC BENELUX • Tel: +44 01236 739292
 SAMTEC ISRAEL • Tel: +972 3 7526600 SAMTEC INDIA • Tel: +91 80 3272 1612 SAMTEC ANZ • Tel: +613 9580 0683 SAMTEC SINGAPORE • Tel: +65 6745 5955 SAMTEC JAPAN • Tel: +81 45 475 1385
 SAMTEC SHANGHAI • Tel: +86 21 6083 3766 SAMTEC SHENZHEN • Tel: +86 755 83776780 SAMTEC TAIWAN • Tel: +886 2 2735 6109 SAMTEC HONG KONG • Tel: +852 26904658 SAMTEC KOREA • Tel: +82 31 717 5685