





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		N	REVISED PER ECR-13-011489	04DEC2013	KH	PD


SUGGESTED MATING TAB




- MATL: #2 HARD BRASS OR NICKEL PLATE STEEL.
 - NO BURRS PERMISSIBLE AT HOLE.
 - TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERTURE IS OVER 225° F.
 - MUST BE FLAT WITHIN 0.076[.003] OVER THIS LENGTH.
 - HOLE MUST BE SYMMETRICAL ABOUT TAB ϕ WITHIN 0.076[.003].
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



VIEW Y-Y
SCALE 10:1



SECTION X-X
SCALE 10:1



SECTION Z-Z
SCALE 10:1

OBSOLETE	PRE-TIN	1.52-2.79 [.060 - .110] DIA	0.2-0.5mm ² [20-16] AWG	63407-2	
	TIN 0.002032 [.000080] MIN			63407-1	
	FINISH	INSULATION RANGE	WIRE SIZE	PART NO	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JR RUTH	1/24/91	TE Connectivity
		CHK	MS FEHER	1/24/91	
DIMENSIONS: mm [INCHES]		APVD	J GILLESPIE	1/24/91	NAME
		PRODUCT SPEC			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC			SIZE
MATERIAL		WEIGHT	-		CAGE CODE
FINISH		CUSTOMER DRAWING			DRAWING NO
SEE TABLE		SCALE	4:1	SHEET	1 OF 1
		REV	N		