


OA172S Series *



172 x 150 x 51mm
(6.7"x 5.9" x 2.0")



Frame	Diecast Aluminum	<u>Operating Temperature</u> Ball Bearing -40C ~ +70C <u>Life Expectancy</u> Ball Bearing 60,000 hours (L10 at 40C) m0	
Impeller	PBT, UL94V-O plastic		
Connection	2x Lead Wires or Terminals		
Motor	Capacitor drive, impedance protected		
Bearing System	Dual ball		
Insulation Resistance	>100M ohm between lead-wire and frame (500VDC)		
Dielectric Strength	1 min at 1500 VAC, 50/60Hz		

Model Number	Speed (RPM)	Airflow (CFM)	Noise (dB)	Volts AC	Voltage Range	Watts	Max. Static Pressure (\"H2O)
OA172SAP-11-1()B	3200	235	52	115	80~130	35	0.70
OA172SAP-11-2()B	2400	170	42	115	80~130	20	0.49
OA172SAP-11-3()B	1800	135	33	115	80~130	16	0.43
OA172SAP-22-1()B	3200	235	52	230	160~260	35	0.70
OA172SAP-22-2()B	2400	170	42	230	160~260	20	0.49
OA172SAP-22-3()B	1800	135	33	230	160~260	16	0.43

() Indicate "T" for Terminal or "W" for Wire Leads



* Use prefix OA172AP instead of OA172SAP to specify round frame instead of the flat-sided, "stackable" version.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OA172SAP-22-1TBXC](#) [OA172SAP-22-2WB](#) [OA172SAP-11-3TB](#) [OA172SAP-11-1TBXC](#) [OA172SAP-11-3WB](#)
[OA172SAP-22-1WB](#) [OA172SAP-22-1TB](#) [OA172SAP-11-2WB](#) [OA172SAP-11-2TB](#) [OA172SAP-22-2TB](#) [OA172SAP-](#)
[22-3WB](#) [OA172SAP-22-3TB](#) [OA172SAP-11-1WB](#) [OA172SAP-11-1TB](#) [OA172AP-22-1WB](#) [OA172AP-11-1WB](#)
[OA172AP-11-1TB](#) [OA172AP-22-1TB](#) [OA172AP-11-3TB](#) [OA172AP-22-3TB](#) [OA172AP-11-2WB](#) [OA172SAP-11-](#)
[1WB03](#) [OA172AP-11-2TB](#) [OA172AP-11-3WB](#) [OA172AP-22-2TB](#) [OA172AP-22-2WB](#) [OA172AP-22-3WB](#)
[OA172SAP-11-1WB XC](#) [OA172SAP-22-1WB XC](#)