
Item no.: 282-122
Product description: 2-conductor fuse terminal block for glass cartridge type fuses
WITHOUT INDICATOR 5 X 20 MM / 0.195 X 0.78 IN



Produkt kann von Bild abweichen / product may differ

Packing unit 40 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.2 - 6 mm ²
Cross section [AWG]	24 - 10 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Measured voltage EN	500 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	10 A
Weight	28.217 g
Color	gray
Wiring type	Side-entry
No. of connection Points	2
No. of potentials	2
Height	54.5 mm
Height	2.146 in
Width	13 mm
Width	0.512 in
Depth	62 mm
Depth	2.44 in

Strip length from	12 mm
Strip length to	13 mm
Strip length	0.49 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm²]
282-122	CCA	NL5470	500	10	6
282-122	CSA	154112-1505033	250	10	24-10
282-122	KEMA	98.2759.05	500		6
282-122	KR	HMB05880-EL001	500/800	10/46	6
282-122	PRS	TE/1718/880590/08	500	10	6
282-122	UR	E45172	600	10	24-10

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected