

PFC Series

Features:

- High stability tantalum nitride film
- Available in 0402, 0603, 0805 and 1206
- TCR to $\pm 10\text{ppm}/^\circ\text{C}$
- Sulfur resistant to ASTM B809-95
- Both Pb-free and SnPb finish available
- AEC-Q200 qualified



All Pb-free parts comply with EU Directive 2011/65/EU amended by (EU) 2015/863 (RoHS3)


Electrical Data

		PFC0402	PFC0603	PFC0805	PFC1206
Power rating (@70°C)	mW	50	100	250	333
Rated operating voltage (not to exceed $V(\text{PxR})$)	V	75		100	200
Resistance range	ohms	40R to 35K	40R to 100K	10R to 267K	10R to 1M0
Tolerance	%	0.05, 0.1, 0.25, 0.5, 1, 2, 5			
TCR	ppm/°C	10, 15, 25, 50, 100			
ESD withstand ¹ (HBM)	kV	0.5	1	1.5	2
Noise	dB	<-25			
Operating temperature	°C	-65 to 150			
Values		E24 or E192			

Note 1: This product is not considered ESD sensitive for packaging and handling purposes.

Physical Data

Dimensions in inches / (mm) and weight in mg						
Size	L	W	H	a	b	Wt. nom.
0402	0.04 ±0.003 (1.02 ±0.08)	0.021 ±0.005 (0.53 ±0.13)	0.012 ±0.003 (0.3 ±0.08)	0.01 ±0.006 (0.25 ±0.15)		0.55
0603	0.063 ±0.004 (1.6 ±0.1)	0.031 ±0.004 (0.79 ±0.1)	0.02 ±0.006 (0.51 ±0.15)	0.012 ±0.008 (0.3 ±0.2)	0.015 ±0.009 (0.38 ±0.23)	1.97
0805	0.081 ±0.006 (2.06 ±0.15)	0.05 ±0.007 (1.27 ±0.18)		0.015 ±0.009 (0.38 ±0.23)	0.016 ±0.008 (0.41 ±0.2)	4.48
1206	0.126 ±0.008 (3.2 ±0.2)	0.063 ±0.005 (1.6 ±0.13)	0.024 ±0.006 (0.61 ±0.15)	0.025 ±0.017 (0.64 ±0.43)		8.93



Note: For PCB mounting pad recommendations see:

<https://www.ttelectronics.com/TTElectronics/media/ProductFiles/Application-Note/TN006-Recommended-Layouts-for-SMD-Resistors.pdf>


Construction

Conductors and tantalum nitride resistive element are applied to an alumina substrate. The product is laser trimmed to value, and a protective epoxy coat is applied. The product is then metallized and plated to provide a wrap-around solderable termination with a 100% matte tin or a 60/40 SnPb finish on a nickel barrier layer. It is 100% tested then packed in carrier tape. Pb-free parts use paper carrier tape, whilst SnPb parts use plastic carrier tape.

Performance Data

Test per MIL-PRF-55342	±ΔR/R%	
	Typical	Maximum
Thermal shock	0.02	0.1
Low temperature operation	0.01	0.05
Short-time overload	0.01	0.05
High temperature exposure	0.03	0.1
Effects of solder	0.01	0.1
Moisture resistance	0.03	0.1
Life	0.03	0.1
Sulfuration test: ASTM B809 (modified) 105°C, dry, 1000 hours	0.02	0.05

Temperature Derating



Ordering Procedure

Global Part Number Example: PFC0402LFD1002BT5 (0402, 25ppm/°C at 10 kilohms ±0.1%, Pb-free)

P	F	C	0	4	0	2	L	F	D	1	0	0	2	B	T	5	
1	2		3	4	5		6	7									

1	2	3	4	5	6	7		
Series	Size	Termination ¹	TCR (ppm/°C)	Value	Tolerance	Packing		
PFC	0402	LF = Pb-free (100%Sn)	T = ±10	3 digits + multiplier R = ohms for values <100 ohms	A = ±0.05%	Pb-free (LF) product		
	0603	PB = SnPb (60/40) (0603, 0805, 1206 only)	Y = ±15		B = ±0.1%	T10	0402	10,000/reel
	0805		D = ±25	C = ±0.25%	T5	0603, 0805, 1206	5000/reel	
	1206		C = ±50	D = ±0.5%	T1	All sizes ²		1000/reel
			Z = ±100		F = ±1%	SnPb (PB) product		
					G = ±2%	T1	0603, 0805, 1206	1000/reel
					J = ±5%			


Note 1: Terminations are anti-sulfur as standard.

Note 2: Non-standard packing option – consult factory for availability.

Legacy Part Numbers

This product has two legacy part number formats. These are still available for ordering, but for new designs use of the Global Part Number is recommended.


European Legacy Part Number: W1206R-01-1K0B1 (1206, 100ppm/°C, 1 kilohm ±0.1%, Pb-free)



1	2	3	4	5	6	7			
Series	Size	Option ¹	TCR (ppm/°C)	Value	Tolerance	Termination & Packing			
W = PFC	0402	R	Anti-sulfur	-12 = ±10	E24/E96 = 3/4 characters	A = ±0.05%	I	All sizes	Pb-free, Standard pack
	0603	AS		-11 = ±15		B = ±0.1%	PB	0603, 0805, 1206	SnPb finish, 1000/reel
	0805		Blank = ±25	R = ohms	C = ±0.25%	Standard Pack			
	1206		-02 = ±50	K = kilohms	D = ±0.5%	0402	10,000/reel		
			-01 = ±100	M = megohms	F = ±1%	0603, 0805, 1206	5000/reel		
				G = ±2%					
				J = ±5%					

Note 1: Terminations are anti-sulfur as standard.

USA Legacy Part Number: PFC-W1206LF-01-1001-B (1206, 100ppm/°C, 1 kilohm ±0.1%, Pb-free)



1	2	3		4	5	6	Standard Packing			
Series	Model	Termination ¹		TCR (ppm/°C)	Value	Tolerance				
PFC	W0402	LF	All sizes	Anti-sulfur & Pb-free (100%Sn)	12 = ±10	3 digits + multiplier	A = ±0.05%	0402	10,000/reel	
	W0603	ASLF			11 = ±15		B = ±0.1%	0603, 0805,	Pb-free	5000/reel
	W0805	R	0603, 0805,	Anti-sulfur & SnPb (60/40)	03 = ±25	R = ohms for values <100 ohms	C = ±0.25%	1206	SnPb	1000/reel
	W1206	AS	1206		02 = ±50		D = ±0.5%			
					01 = ±100	F = ±1%				
					G = ±2%					
					J = ±5%					

Note 1: Terminations are anti-sulfur as standard.