





PRODUCT NUMBER
SEE SHEET 2



spec ref -				dr Andrew Yong		2010/10/25		projection 	MM 	size A3	scale 12:1
tolerance std				eng Guo-Min Sun		2014/08/26				ecn no ELX-N-18628-1	
ISO 406 ISO 1101				chr -		-					
TOLERANCES UNLESS OTHERWISE SPECIFIED				appr Rick Bian		2014/08/26		product family -		rel level Released	
surface  ISO 1302	linear	0.X ± -			title MINITEK II R/R SMT STR HDR WITH LOCATOR				dwg no 10065491		rev M
		0.XX ±0.25									
		0.XXX ± -									
	angular	0° ±3°			www.fci.com		cat. no. -		Product - Customer Drw		

NOTES:

1. MATERIAL:
BODY : GLASS FILLED PCT UL 94V-0 NATURAL (BEIGE)
PIN : PHOSPHOR BRONZE

2. TOLERANCE UNLESS OTHERWISE NOTED ± 0.25

3. DIM 1.0 ± 0.15 FOR MOLDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES.

4. RECESS APPLIES TO MOLDED SIDE(S) ONLY.

5. POLARISATION BY OMISSION OF PIN. POSITION REFER TO TABLE.

6. P/N 10065491-XXXT TO BE PACKED IN TUBE.

7. P/N 10065491-XXXTC TO BE PACKED IN TUBE WITH PICK-UP CAP INSTALLED IN THE CENTRE OF THE PRODUCT. SEE FIG 1.

8. P/N 10065491-XXXTR TO BE PACKED IN TAPE & REEL WITH PICK-UP CAP INSTALLED IN THE CENTRE OF THE PRODUCT. SEE FIG 1.

9. P/N 10065491-XXXTRN TO BE PACKED IN TAPE & REEL WITHOUT PICK-UP CAP.

10. PRODUCT PART NUMBER DESCRIPTIONS:
10065491-XXX LF
 LEAD FREE. SEE NOTE 11
 NO. OF POSITIONS (RANDOM)

11. 10065491-XXXLF IS SAME TO 10065491-XXX. THE SUFFIX 'LF' IS ADDED JUST FOR EASY LEAD FREE IDENTIFICATION.



12. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

13. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD.

14. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

15. A Δ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.

16. DIM C=DIM B+4.0



RECOMMENDED PAD LAYOUT

spec ref		-		dr		Andrew Yong		2010/10/25		projection		MM		size		A3		scale		5:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Guo-Min Sun		2014/08/26						ecn no		ELX-N-18628-1							
ISO 406																							
ISO 1101																							
				chr		-		-		appr		Rick Bian		2014/08/26		product family		-		rel level		Released	
surface		linear		0.X		± -				title		MINITEK II R/R		dwg no		10065491		rev		M			
				0.XX		±0.25																	
				0.XXX		± -																	
ISO 1302		angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 3 of 3							