

# 2MBI100PC-140

## IGBT Module P-Series

1400V / 100A 2 in one-package




### ■ Features

- Small temperature dependence of the turn-off switching loss
- Easy to connect in parallel
- Wide RBSOA (square up to 2 time of rated current) and high short-circuit withstand capability
- Low loss and soft-switching (reduction of EMI noise)

### ■ Applications

- General purpose inverter
- AC and DC Servo drive amplifier
- Uninterruptible power supply

### ■ Equivalent Circuit Schematic



### ■ Maximum ratings and characteristics

#### ● Absolute maximum ratings (at Tc=25°C unless otherwise specified)

| Item                        |                                     |  | Symbol                | Conditions | Rating               | Unit |   |
|-----------------------------|-------------------------------------|--|-----------------------|------------|----------------------|------|---|
| Collector-Emitter voltage   |                                     |  | V <sub>CES</sub>      |            | 1400                 | V    |   |
| Gate-Emitter voltage        |                                     |  | V <sub>GES</sub>      |            | ±20                  | V    |   |
| Collector current           |                                     |  | I <sub>c</sub>        | Continuous | T <sub>C</sub> =25°C | 150  | A |
|                             |                                     |  |                       |            | T <sub>C</sub> =80°C | 100  |   |
|                             |                                     |  | I <sub>cp</sub>       | 1ms        | T <sub>C</sub> =25°C | 300  |   |
|                             |                                     |  |                       |            | T <sub>C</sub> =80°C | 200  |   |
|                             |                                     |  | -I <sub>c</sub>       |            |                      | 100  |   |
|                             |                                     |  | -I <sub>c</sub> pulse |            |                      | 200  |   |
| Collector Power Dissipation |                                     |  | P <sub>C</sub>        | 1 device   | 780                  | W    |   |
| Junction temperature        |                                     |  | T <sub>j</sub>        |            | +150                 | °C   |   |
| Storage temperature         |                                     |  | T <sub>stg</sub>      |            | -40 to +125          |      |   |
| Isolation voltage           | between terminal and copper base *1 |  | V <sub>iso</sub>      | AC:1min.   | 2500                 | VAC  |   |
| Screw Torque                |                                     |  | Mounting *2           |            | 3.5                  | N·m  |   |
|                             |                                     |  | Terminals *2          |            | 3.5                  |      |   |

\*1 : All terminals should be connected together when isolation test will be done.

\*2 : Recommendable value : 2.5 to 3.5 N·m(M5)

#### ● Electrical characteristics (at Tj=25°C unless otherwise specified)







| Item                                 | Symbols              | Conditions                                                        | Characteristics |       |      | Unit |
|--------------------------------------|----------------------|-------------------------------------------------------------------|-----------------|-------|------|------|
|                                      |                      |                                                                   | Min.            | Typ.  | Max. |      |
| Zero gate voltage collector current  | I <sub>CES</sub>     | V <sub>GE</sub> =0V, V <sub>CE</sub> =1400V                       | —               | —     | 2.0  | mA   |
| Gate-Emitter leakage current         | I <sub>GES</sub>     | V <sub>CE</sub> =0V, V <sub>GE</sub> =±20V                        | —               | —     | 400  | nA   |
| Gate-Emitter threshold voltage       | V <sub>GE(th)</sub>  | V <sub>CE</sub> =20V, I <sub>c</sub> =100mA                       | 6.0             | 8.0   | 9.0  | V    |
| Collector-Emitter saturation voltage | V <sub>CE(sat)</sub> | V <sub>GE</sub> =15V, I <sub>c</sub> =100A, T <sub>j</sub> =25°C  | —               | 2.7   | 3.0  | V    |
|                                      |                      | V <sub>GE</sub> =15V, I <sub>c</sub> =100A, T <sub>j</sub> =125°C | —               | 3.3   | —    |      |
| Input capacitance                    | C <sub>ies</sub>     | V <sub>CE</sub> =10V                                              | —               | 10000 | —    | pF   |
| Output capacitance                   | C <sub>oes</sub>     | V <sub>GE</sub> =0V                                               | —               | 1500  | —    |      |
| Reverse transfer capacitance         | C <sub>res</sub>     | f=1MHz                                                            | —               | 650   | —    |      |
| Turn-on time                         | t <sub>on</sub>      | V <sub>CC</sub> =600V                                             | —               | —     | 1.20 | μs   |
|                                      | t <sub>r</sub>       | I <sub>c</sub> =100A                                              | —               | —     | 0.60 |      |
| Turn-off time                        | t <sub>off</sub>     | V <sub>GE</sub> =±15V                                             | —               | —     | 1.00 |      |
|                                      | t <sub>f</sub>       | R <sub>G</sub> =9.1 Ω                                             | —               | —     | 0.30 |      |
| Diode forward on voltage             | V <sub>F</sub>       | I <sub>F</sub> =100A, V <sub>GE</sub> =0V                         | —               | 2.4   | 3.3  | V    |
| Reverse recovery time                | t <sub>rr</sub>      | I <sub>F</sub> =100A                                              | —               | —     | 0.35 | μs   |







#### ● Thermal resistance characteristics



| Items                      | Symbols                | Conditions              | Characteristics |       |      | Unit |
|----------------------------|------------------------|-------------------------|-----------------|-------|------|------|
|                            |                        |                         | Min.            | Typ.  | Max. |      |
| Thermal resistance         | R <sub>th(j-c)</sub>   | IGBT                    | —               | —     | 0.16 | °C/W |
|                            | R <sub>th(j-c)</sub>   | Diode                   | —               | —     | 0.33 | °C/W |
| Contact Thermal resistance | R <sub>th(c-f)*4</sub> | the base to cooling fin | —               | 0.025 | —    | °C/W |

\*4 : This is the value which is defined mounting on the additional cooling fin with thermal compound.

Characteristics (Representative)







■ Outline Drawings, mm

M233

