


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PART NUMBER	STUD SIZE	WIRE RANGE mm ² (AWG)	DIMENSIONS mm				
			A $\begin{smallmatrix} \pm,80 \\ (.03) \end{smallmatrix}$	W $\begin{smallmatrix} \pm,25 \\ (.01) \end{smallmatrix}$	C $\begin{smallmatrix} \pm,38 \\ (.01) \end{smallmatrix}$	M $\begin{smallmatrix} \pm,50 \\ (.02) \end{smallmatrix}$	H $\begin{smallmatrix} \pm,50 \\ (.02) \end{smallmatrix}$
PMN2-3R-3K	M3	1,5-2,5 (16-14)	21,6 (.85)	5,8 (.23)	5,1 (.20)	16,5 (.65)	3,3 (.13)
PMN2-35R-3K	M3,5	1,5-2,5 (16-14)	21,6 (.85)	5,8 (.23)	5,1 (.20)	16,5 (.65)	3,8 (.15)
PMN2-4R-3K	M4	1,5-2,5 (16-14)	24,1 (.95)	7,9 (.31)	6,5 (.26)	18,0 (.71)	4,6 (.18)
PMN2-5R-3K	M5	1,5-2,5 (16-14)	24,6 (.97)	8,9 (.35)	6,5 (.26)	18,0 (.71)	5,3 (.21)
PMN2-6R-3K	M6	1,5-2,5 (16-14)	26,7 (1.05)	10,9 (.43)	9,7 (.38)	21,3 (.84)	6,9 (.27)

NOTES:

1. USED FOR:
 - A. 600V MAX. BUILDING WIRE
1000V MAX. IN SIGNS, FIXTURES, AND LUMINAIRES
 - B. 105°C (221°F) MAX. TEMP. RATING OF INSUL. MAT'L.
 - C. STRANDED COPPER WIRE ONLY
2. PACKAGE QTY:
3K = 3000 PCS. ON CONTINUOUSLY MOLDED CARRIER STRIP
3. MATERIAL:
 - A. STAMPING: .81 (.03)THK. COPPER, TIN PLATED
 - B. SLEEVE: BRASS, TIN PLATED
 - C. HOUSING: TYPE 6/6 NYLON, BLUE
4. WIRE STRIP LENGTH: $5,6^{+8}_{-0}$ ($7/32^{+1/32}_{-0}$)
5. DIMENSIONS IN BRACKETS ARE IN INCHES OR AWG
6. UL LISTED AND CSA CERTIFIED WITH COPPER 16-14AWG WIRE ONLY



		PANDUIT PRESS					
		CP-851 <i>DISCONTINUED</i>	CP-860 <i>DISCONTINUED</i>	CP-861	CP-862	CP-871 60HZ	CP-871/E 50HZ
APPLICATORS	CA-800		X	X			
	CA-800EZ	X				X	X
	CA9				X	X	X



A41608_01

								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
01	3/06	DAW	DAW	ADDED PMN2-35R-3K AND PANDUIT PRESS AND APPLICATOR CHART	TR00083			1,5-2,5 mm ² METRIC CONTINUOUSLY MOLDED, NYLON INSULATED RING TERMINAL			
00	9/97	TM		RELEASED	6191	LCA	CBH				
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	CHK'D	SCALE	DRAWING NO.
								TSM		NONE	A41608