

H

G

F

E

D

C

B

A

H

G

F


E

D


C

B

A



NOTES
1 - SILVER PLATED TERMINALS
2 - TESTED TO SHOW COMPLIANCE WITH UL 858 OVEN LATCH REQUIREMENTS UNDER THE FOLLOWING PARAMETERS: ELECTRICAL ENDURANCE FOR 100K OPERATIONS AT 200°C FOR 250 HOURS MINIMUM WHILE CONTROLLING AN INDUCTIVE LOAD OF 6A, 277VAC

CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE: ☒ US (inch) CUSTOMARY ☐ SI (mm) METRIC NO PLACE X ±.040 ±1 ONE PLACE .X ±.030 ±0,4 TWO PLACE .XX ±.015 ±0,15 THREE PLACE .XXX ±.005 ± ANGLES ± ± RAW MATERIAL-COMMERCIAL STANDARD		DRAWN	TSM	5FEB02	Honeywell				
OPERATING FORCE----- 66 GRAMS MAX		CONTACT ARRANGEMENT S P N O				CHECK	SAV	5FEB02					
RELEASE FORCE----- 5 GRAMS MIN		L278 6A, 1/8HP 125, <u>250</u> OR 277 VAC Ⓟ 		THIRD ANGLE PROJECTION 		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH, BASIC				
DIFFERENTIAL TRAVEL----- .027 MAX													
OVERTRAVEL----- .068 MIN						SIZE	DWG TYPE	DRAWING NAME			REV		
RELEASE TRAVEL----- .016 MIN						B	I	V7-1X2AD8-295			4		
		PTC 2D	ASME Y14.5M-1994		SCALE	2 : 1	WEIGHT		SHEET	1	OF	1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V7-1X2AD8-295](#)