


YG838C04R (30A)

(40V / 30A)

SCHOTTKY BARRIER DIODE

■ Outline drawings, mm




■ Features

- Low V_F
- Super high speed switching
- High reliability by planer design

■ Applications

- High speed power switching

■ Connection diagram



■ Maximum ratings and characteristics

- Absolute maximum ratings

Item	Symbol	Conditions	Rating	Unit
Repetitive peak reverse voltage	V_{RRM}		40	V
Non-repetitive peak reverse voltage	V_{RSM}	$t_w=500ns$, duty=1/40	40	V
Average output current	I_o	Square wave, duty=1/2 $T_c=85^\circ C$	30*	A
Surge current	I_{FSM}	Sine wave 10ms	180	A
Operating junction temperature	T_j		-40 to +150	$^\circ C$
Storage temperature	T_{stg}		-40 to +150	$^\circ C$


* Average forward current of centertap full wave connection

- Electrical characteristics ($T_a=25^\circ C$ Unless otherwise specified)


Item	Symbol	Conditions	Max.	Unit
Forward voltage drop	V_{FM}	$I_{FM}=12.5A$	0.53	V
Reverse current	I_{RRM}	$V_R=V_{RRM}$	8	mA
Thermal resistance	$R_{th(j-c)}$	Junction to case	2.0	$^\circ C/W$

Characteristics


Forward Characteristic (typ.)




Reverse Characteristic (typ.)




Forward Power Dissipation



Reverse Power Dissipation



Current Derating (I_o - T_c)



Junction Capacitance Characteristic (typ.)

