




- No OF POSITIONS
-03,-04,-05,-08,-10,-12,
-13,-15,-17,-20,-22,-25
NOTE: OTHER POSITIONS
AVAILALE AS ASO. TOOL
IS CAPABLE OF POSITIONS 2-25
- END ASSEMBLY
-D: DOUBLE END
-S: SINGLE END
-T: TRANSFER END
- ASSEMBLY LENGTH
(2 INCH MINIMUM)
- OPTION
SEE OPTIONS BELOW
- OPTION
SEE OPTIONS BELOW
- OPTION
LEAVE BLANK FOR STANDARD
-F: FLASH GOLD PLATING
TRANSFER END ONLY
(USE TCSD-XX-01-F)
- LEAD STYLE






TABLE 1	
ITEM #	PART
1	TCSD-XX-01-XXX
2	TCB-50
3	TCMD-XX-01
4	TCMD-XX-01-SR
5	TMSR-XX
6	TTC-XX-D
7	T-1S14-XX-X

- NOTES:
1. © REPRESENTS A CRITICAL DIMENSION.
 2. AS OF REV C ON TCB-50 CABLE, ASSEMBLIES WILL BE LEAD FREE.
 3. ALL ASSEMBLIES TO BE 100 % ELECTRONICALLY TESTED FOR SHORTS AND OPENS.
 4. ALL ASSEMBLIES TO BE 100 % HI-POT TESTED AT 800V.
 5. STRAIN RELIEF TO WITHSTAND 5LBS STRAIGHT PULL.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS	ANGLES
.XX: ±.01 [.3]	2°
.XXX: ±.005 [.13]	
.XXXX: ±.0020 [.051]	

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1

INSULATOR: VALOX 420 SEO, COLOR: BLACK
CONTACT : #25 BeCu 1/2 HARD, AGE HARDENED
TERMINAL: SPRING TEMPER PHOS BRONZE, ALLOY 510
STRAIN RELIEF: CELANEX 3300, COLOR: BLACK

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322


DESCRIPTION:
2MM DOUBLE ROW MALE IDC CABLE ASSEMBLY

DWG. NO.
TCMD-XX-X-XX.XX-01-X-XXX-XXX


BY: B RAY 11/26/2007 SHEET 1 OF 4

REVISION T


-SR:
STRAIN RELIEF
(NOT AVAILABLE WITH -O, -M, -R, -DXX, OR -BXX)
(SOLD AS ASSEMBLIES ONLY)
(SAME AS -D UNLESS SPECIFIED)




IN-PROCESS 1 -SR ONLY




IN-PROCESS 2 -SR ONLY




-N
NOTCH POLARIZATION
(FOR -T ONLY)
(IF OPTION IS SPECIFIED
USE TCSD-XX-01-N)




-RW
REVERSE WIRING




-T
TRANSFER END
(SAME AS -D UNLESS SPECIFIED)



-P"XX"
POLARIZED MATING
(USE PK-07-N POLARIZING KEY)
(THE SAME POSITION WILL
BE POLARIZED ON BOTH ENDS)



-BXX
BREAKOUT OPTION
"XX" = NO OF CONDUCTORS PER ROW
BROKEN OUT FROM THE FIRST POSITION



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:5:1

samtec


520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

DESCRIPTION:
2MM DOUBLE ROW MALE IDC CABLE ASSEMBLY

DWG. NO.
TCMD-XX-X-XX.XX-01-X-XXX-XXX


BY: B RAY 11/26/2007 SHEET 2 OF 4

-O
OUTSIDE REVERSED




FIRST POSITION INDICATOR

$XX.XX[XX.X \times 25.4] \pm .125[3.18]$




OUTSIDE SOCKET REVERSED
WHEN DAISY CHAINED

-M
MIDDLE REVERSED




FIRST POSITION INDICATOR

$XX.XX[XX.X \times 25.4] \pm .125[3.18]$




MIDDLE TERMINAL REVERSED
WHEN DAISY CHAINED

-O
OUTSIDE TRANSFER




FIRST POSITION INDICATOR

$XX.XX[XX.X \times 25.4] \pm .125[3.18]$




OUTSIDE SOCKET REVERSED
WHEN DAISY CHAINED

-M
MIDDLE TRANSFER



FIRST POSITION INDICATOR

$XX.XX[XX.X \times 25.4] \pm .125[3.18]$



MIDDLE TERMINAL REVERSED
WHEN DAISY CHAINED

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:5:1


samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322



DESCRIPTION:
2MM DOUBLE ROW MALE IDC CABLE ASSEMBLY

DWG. NO.
TCMD-XX-X-XX.XX-01-X-XXX-XXX


BY: B RAY 11/26/2007 SHEET 3 OF 4




FIRST POSITION INDICATOR






FIRST POSITION INDICATOR



NOTE:
2" MINIMUM LENGTH
1" INCREMENTS ONLY



FIRST POSITION INDICATOR



NOTE:
2" MINIMUM LENGTH
1" INCREMENTS ONLY

PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC. DO NOT SCALE DRAWING SHEET SCALE: 1:5:1			
	520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail: info@SAMTEC.com code: 55322		
	DESCRIPTION: 2MM DOUBLE ROW MALE IDC CABLE ASSEMBLY		
	DWG. NO. TCMD-XX-X-XX.XX-01-X-XXX-XXX		
BY: B RAY		11/26/2007	SHEET 4 OF 4