

# 200 kPa On-Chip Temperature Compensated & Calibrated Pressure Sensors

The MPX2202/MPXV2202G device series is a silicon piezoresistive pressure sensor providing a highly accurate and linear voltage output - directly proportional to the applied pressure. The sensor is a single monolithic silicon diaphragm with the strain gauge and a thin-film resistor network integrated on-chip. The chip is laser trimmed for precise span and offset calibration and temperature compensation. They are designed for use in applications such as pump/motor controllers, robotics, level indicators, medical diagnostics, pressure switching, barometers, altimeters, etc.

## Features

- Temperature Compensated Over 0°C to +85°C
- Easy-to-Use Chip Carrier Package Options
- Available in Absolute, Differential and Gauge Configurations


## Typical Applications

- Pump/Motor Controllers
- Robotics
- Level Indicators
- Medical Diagnostics
- Pressure Switching
- Barometers
- Altimeters


## ORDERING INFORMATION

| Device Type                             | Options                      | Case No. | MPX Series Order No.   | Packing Options | Device Marking         |
|---|------------------------------|----------|------------------------|-----------------|------------------------|
| SMALL OUTLINE PACKAGE (MPX2202G SERIES) |                              |          |                        |                 |                        |
| Ported Elements                         | Gauge, Side Port, SMT        | 1369     | MPXV2202GP             | Trays           | MPXV2202GP             |
|   | Differential, Dual Port, SMT | 1351     | MPXV2202DP             | Trays           | MPXV2202DP             |
| UNIBODY PACKAGE (MPX2202 SERIES)        |                              |          |                        |                 |                        |
| Basic Element                           | Absolute, Differential       | 344      | MPX2202A<br>MPX2202D   | —               | MPX2202A<br>MPX2202D   |
| Ported Elements                         | Differential, Dual Port      | 344C     | MPX2202DP              | —               | MPX2202DP              |
|   | Absolute, Gauge              | 344B     | MPX2202AP<br>MPX2202GP | —               | MPX2202AP<br>MPX2202GP |
|   | Absolute                     | 344F     | MPX2202ASX             | —               | MPX2202A               |


## UNIBODY PACKAGES




MPX2202A/D  
CASE 344-15



MPX2202AP/GP  
CASE 344B-01



MPX2202DP  
CASE 344C-01




MPX2202ASX  
CASE 344F-01


## MPX2202 SERIES

0 TO 200 kPa (0 TO 29 psi)  
40 mV FULL SCALE SPAN  
(TYPICAL)

## SMALL OUTLINE PACKAGE SURFACE MOUNT



MPXV2202GP  
CASE 1369-01



MPXV2202DP  
CASE 1351-01

## SMALL OUTLINE PACKAGE PIN NUMBERS

|   |                    |   |     |
|---|--------------------|---|-----|
| 1 | GND <sup>(1)</sup> | 5 | N/C |
| 2 | +V <sub>OUT</sub>  | 6 | N/C |
| 3 | V <sub>S</sub>     | 7 | N/C |
| 4 | -V <sub>OUT</sub>  | 8 | N/C |


1. Pin 1 is noted by the notch in the lead.

## UNIBODY PACKAGE PIN NUMBERS

|   |                    |   |                   |
|---|--------------------|---|-------------------|
| 1 | GND <sup>(1)</sup> | 3 | V <sub>S</sub>    |
| 2 | +V <sub>OUT</sub>  | 4 | -V <sub>OUT</sub> |

1. Pin 1 is noted by the notch in the lead.

Figure 1 illustrates a block diagram of the internal circuitry on the stand-alone pressure sensor chip.



**Figure 1. Temperature Compensated Pressure Sensor Schematic**

### VOLTAGE OUTPUT VERSUS APPLIED DIFFERENTIAL PRESSURE

The differential voltage output of the sensor is directly proportional to the differential pressure applied.

The absolute sensor has a built-in reference vacuum. The output voltage will decrease as vacuum, relative to ambient, is drawn on the pressure (P1) side.

The output voltage of the differential or gauge sensor increases with increasing pressure applied to the pressure (P1) side relative to the vacuum (P2) side. Similarly, output voltage increases as increasing vacuum is applied to the vacuum (P2) side relative to the pressure (P1) side.

**Table 1. Maximum Ratings<sup>(1)</sup>**

| Rating                     | Symbol           | Value       | Unit |
|----------------------------|------------------|-------------|------|
| Maximum Pressure (P1 > P2) | P <sub>max</sub> | 800         | kPa  |
| Storage Temperature        | T <sub>stg</sub> | -40 to +125 | °C   |
| Operating Temperature      | T <sub>A</sub>   | -40 to +125 | °C   |

1. Exposure beyond the specified limits may cause permanent damage or degradation to the device.

**Table 2. Operating Characteristics**(V<sub>S</sub> = 10 Vdc, T<sub>A</sub> = 25°C unless otherwise noted, P1 > P2)

| Characteristics   | Symbol                             | Min               | Typ    | Max        | Unit              |
|---|------------------------------------|-------------------|--------|------------|-------------------|
| Pressure Range <sup>(1)</sup>                           | P <sub>OP</sub>                    | 0                 | -      | 200        | kPa               |
| Supply Voltage <sup>(2)</sup>                           | V <sub>S</sub>                     | —                 | 10     | 16         | Vdc               |
| Supply Current  | I <sub>O</sub>                     | —                 | 6.0    | -          | mAdc              |
| Full Scale Span <sup>(3)</sup>                          | V <sub>FSS</sub>                   | 38.5              | 40     | 41.5       | mV                |
| Offset <sup>(4)</sup>                                   | V <sub>off</sub>                   | -1.0              | —      | 1.0        | mV                |
| Sensitivity   | ΔV/ΔP                              | —                 | 0.2    | —          | mV/kPa            |
| Linearity <sup>(5)</sup>                                | MPX2202D Series<br>MPX2202A Series | —<br>-0.6<br>-1.0 | —<br>— | 0.4<br>1.0 | %V <sub>FSS</sub> |
| Pressure Hysteresis <sup>(5)</sup> (0 to 200 kPa)       | —                                  | —                 | ±0.1   | -          | %V <sub>FSS</sub> |
| Temperature Hysteresis <sup>(5)</sup> (-40°C to +125°C) | —                                  | —                 | ±0.5   | -          | %V <sub>FSS</sub> |
| Temperature Effect on Full Scale Span <sup>(5)</sup>    | TCV <sub>FSS</sub>                 | -2.0              | —      | 2.0        | %V <sub>FSS</sub> |
| Temperature Effect on Offset <sup>(5)</sup>             | TCV <sub>off</sub>                 | -1.0              | —      | 1.0        | mV                |
| Input Impedance   | Z <sub>in</sub>                    | 1000              | —      | 2500       | W                 |
| Output Impedance  | Z <sub>out</sub>                   | 1400              | —      | 3000       | W                 |
| Response Time <sup>(6)</sup> (10% to 90%)               | t <sub>R</sub>                     | —                 | 1.0    | —          | ms                |
| Warm-Up   | —                                  | —                 | 20     | —          | ms                |
| Offset Stability <sup>(7)</sup>                         | —                                  | —                 | ±0.5   | —          | %V <sub>FSS</sub> |

1. 1.0 kPa (kiloPascal) equals 0.145 psi.

2. Device is ratiometric within this specified excitation range. Operating the device above the specified excitation range may induce additional error due to device self-heating.

3. Full Scale Span (V<sub>FSS</sub>) is defined as the algebraic difference between the output voltage at full rated pressure and the output voltage at the minimum rated pressure.4. Offset (V<sub>off</sub>) is defined as the output voltage at the minimum rated pressure.

5. Accuracy (error budget) consists of the following:

- Linearity: Output deviation from a straight line relationship with pressure, using end point method, over the specified pressure range.
- Temperature Hysteresis: Output deviation at any temperature within the operating temperature range, after the temperature is cycled to and from the minimum or maximum operating temperature points, with zero differential pressure applied.
- Pressure Hysteresis: Output deviation at any pressure within the specified range, when this pressure is cycled to and from the minimum or maximum rated pressure, at 25°C.
- TcSpan: Output deviation at full rated pressure over the temperature range of 0 to 85°C, relative to 25°C.
- TcOffset: Output deviation with minimum rated pressure applied, over the temperature range of 0 to 85°C, relative to 25°C.

6. Response Time is defined as the time for the incremental change in the output to go from 10% to 90% of its final value when subjected to a specified step change in pressure.

7. Offset stability is the product's output deviation when subjected to 1000 hours of Pulsed Pressure, Temperature Cycling with Bias Test.

## LINEARITY

Linearity refers to how well a transducer's output follows the equation:  $V_{out} = V_{off} + \text{sensitivity} \times P$  over the operating pressure range. There are two basic methods for calculating nonlinearity: (1) end point straight line fit (see Figure 2) or (2) a least squares best line fit. While a least squares fit gives the "best case" linearity error (lower numerical value), the calculations required are burdensome.

Conversely, an end point fit will give the "worst case" error (often more desirable in error budget calculations) and the calculations are more straightforward for the user. Freescale's specified pressure sensor linearities are based on the end point straight line method measured at the midrange pressure.




Figure 2. Linearity Specification Comparison

## ON-CHIP TEMPERATURE COMPENSATION AND CALIBRATION

Figure 3 shows the output characteristics of the MPX2202/MPXV2202G series at 25°C. The output is directly proportional to the differential pressure and is essentially a straight line.

The effects of temperature on Full Scale Span and Offset are very small and are shown under Operating Characteristics.





Figure 3. Output versus Pressure Differential



**Figure 4. . Cross-Sectional Diagrams (Not to Scale)**

Figure 4 illustrates an absolute sensing die (right) and the differential or gauge die in the basic chip carrier (Case 344). A silicone gel isolates the die surface and wire bonds from the environment, while allowing the pressure signal to be transmitted to the silicon diaphragm.

The MPX2202/MPXV2202G series pressure sensor operating characteristics and internal reliability and

qualification tests are based on use of dry air as the pressure media. Media other than dry air may have adverse effects on sensor performance and long term reliability. Contact the factory for information regarding media compatibility in your application.

### PRESSURE (P1)/VACUUM (P2) SIDE IDENTIFICATION TABLE


Freescall designates the two sides of the pressure sensor as the Pressure (P1) side and the Vacuum (P2) side. The Pressure (P1) side is the side containing the silicone gel which isolates the die from the environment. The differential or gauge sensor is designed to operate with positive differential pressure applied,  $P1 > P2$ . The absolute sensor is designed for vacuum applied to P1 side.

The Pressure (P1) side may be identified by using the table below:

**Table 3. Pressure (P1)/Vacuum (P2) Side Identification Table**

| Part Number  | Case Type | Pressure (P1) Side Identifier |
|--------------|-----------|-------------------------------|
| MPX2202A/D   | 344       | Stainless Steel Cap           |
| MPX2202DP    | 344C      | Side with Part Marking        |
| MPX2202AP/GP | 344B      | Side with Port Attached       |
| MPX2202ASX   | 344F      | Side with Port Attached       |
| MPXV2202GP   | 1369      | Side with Port Attached       |
| MPXV2202DP   | 1351      | Side with Part Marking        |


\_\_\_\_\_



| DIM | INCHES   |      | MILLIMETERS |       | DIM | INCHES |      | MILLIMETERS |      |
|-----|----------|------|-------------|-------|-----|--------|------|-------------|------|
|     | MIN      | MAX  | MIN         | MAX   |     | MIN    | MAX  | MIN         | MAX  |
| A   | .300     | .330 | 7.11        | 7.62  | Ø   | 0*     | 7*   | 0*          | 7*   |
| A1  | .002     | .010 | 0.05        | 0.25  | -   | ----   | ---- | ----        | ---- |
| b   | .038     | .042 | 0.96        | 1.07  | -   | ----   | ---- | ----        | ---- |
| D   | .465     | .485 | 11.81       | 12.32 | -   | ----   | ---- | ----        | ---- |
| E   | .717 BSC |      | 18.21 BSC   |       | -   | ----   | ---- | ----        | ---- |
| E1  | .465     | .485 | 11.81       | 12.32 | -   | ----   | ---- | ----        | ---- |
| e   | .100 BSC |      | 2.54 BSC    |       | -   | ----   | ---- | ----        | ---- |
| F   | .245     | .255 | 6.22        | 6.47  | -   | ----   | ---- | ----        | ---- |
| K   | .120     | .130 | 3.05        | 3.30  | -   | ----   | ---- | ----        | ---- |
| L   | .061     | .071 | 1.55        | 1.80  | -   | ----   | ---- | ----        | ---- |
| M   | .270     | .290 | 6.86        | 7.36  | -   | ----   | ---- | ----        | ---- |
| N   | .080     | .090 | 2.03        | 2.28  | -   | ----   | ---- | ----        | ---- |
| P   | .009     | .011 | 0.23        | 0.28  | -   | ----   | ---- | ----        | ---- |
| T   | .115     | .125 | 2.92        | 3.17  | -   | ----   | ---- | ----        | ---- |

**MPX2202**

## PACKAGE DIMENSIONS



### NOTES:

1. CONTROLLING DIMENSION: INCH
2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.
3. DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS. MOLD FLASH AND PROTRUSIONS SHALL NOT EXCEED .006 PER SIDE.
4. DIMENSION DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE .008 MAXIMUM.

### STYLE 1:


PIN 1: GND  
 PIN 2: +Vout  
 PIN 3: Vs  
 PIN 4: -Vout  
 PIN 5: N/C  
 PIN 6: N/C  
 PIN 7: N/C  
 PIN 8: N/C

### STYLE 2:

PIN 1: N/C  
 PIN 2: Vs  
 PIN 3: GND  
 PIN 4: Vout  
 PIN 5: N/C  
 PIN 6: N/C  
 PIN 7: N/C  
 PIN 8: N/C

**CASE 1351-01  
 ISSUE A  
 SMALL OUTLINE PACKAGE**

## PACKAGE DIMENSIONS



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION -A- IS INCLUSIVE OF THE MOLD STOP RING. MOLD STOP RING NOT TO EXCEED 16.00 (0.630).

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 0.595     | 0.630 | 15.11       | 16.00 |
| B   | 0.514     | 0.534 | 13.06       | 13.56 |
| C   | 0.200     | 0.220 | 5.08        | 5.59  |
| D   | 0.016     | 0.020 | 0.41        | 0.51  |
| F   | 0.048     | 0.064 | 1.22        | 1.63  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| J   | 0.014     | 0.016 | 0.36        | 0.40  |
| L   | 0.695     | 0.725 | 17.65       | 18.42 |
| M   | 30° NOM   |       | 30° NOM     |       |
| N   | 0.475     | 0.495 | 12.07       | 12.57 |
| R   | 0.430     | 0.450 | 10.92       | 11.43 |
| Y   | 0.048     | 0.052 | 1.22        | 1.32  |
| Z   | 0.106     | 0.118 | 2.68        | 3.00  |

### STYLE 1:

- PIN 1: GROUND  
2: + OUTPUT  
3: + SUPPLY  
4: - OUTPUT


### STYLE 2:

- PIN 1: V<sub>CC</sub>  
2: - SUPPLY  
3: + SUPPLY  
4: GROUND

### STYLE 3:

- PIN 1: GND  
2: -VOUT  
3: VS  
4: +VOUT

## CASE 344-15 ISSUE AA UNIBODY PACKAGE



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 1.145     | 1.175 | 29.08       | 29.85 |
| B   | 0.685     | 0.715 | 17.40       | 18.16 |
| C   | 0.305     | 0.325 | 7.75        | 8.26  |
| D   | 0.016     | 0.020 | 0.41        | 0.51  |
| F   | 0.048     | 0.064 | 1.22        | 1.63  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| H   | 0.182     | 0.194 | 4.62        | 4.93  |
| J   | 0.014     | 0.016 | 0.36        | 0.41  |
| K   | 0.695     | 0.725 | 17.65       | 18.42 |
| L   | 0.290     | 0.300 | 7.37        | 7.62  |
| N   | 0.420     | 0.440 | 10.67       | 11.18 |
| P   | 0.153     | 0.159 | 3.89        | 4.04  |
| Q   | 0.153     | 0.159 | 3.89        | 4.04  |
| R   | 0.230     | 0.250 | 5.84        | 6.35  |
| S   | 0.220     | 0.240 | 5.59        | 6.10  |
| U   | 0.910 BSC |       | 23.11 BSC   |       |


### STYLE 1:

- PIN 1: GROUND  
2: + OUTPUT  
3: + SUPPLY  
4: - OUTPUT

## CASE 344B-01 ISSUE B UNIBODY PACKAGE



## PACKAGE DIMENSIONS



### NOTES:


1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 1.145     | 1.175 | 29.08       | 29.85 |
| B   | 0.685     | 0.715 | 17.40       | 18.16 |
| C   | 0.405     | 0.435 | 10.29       | 11.05 |
| D   | 0.016     | 0.020 | 0.41        | 0.51  |
| F   | 0.048     | 0.064 | 1.22        | 1.63  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| H   | 0.182     | 0.194 | 4.62        | 4.93  |
| J   | 0.014     | 0.016 | 0.36        | 0.41  |
| K   | 0.695     | 0.725 | 17.65       | 18.42 |
| L   | 0.290     | 0.300 | 7.37        | 7.62  |
| N   | 0.420     | 0.440 | 10.67       | 11.18 |
| P   | 0.153     | 0.159 | 3.89        | 4.04  |
| Q   | 0.153     | 0.159 | 3.89        | 4.04  |
| R   | 0.063     | 0.083 | 1.60        | 2.11  |
| S   | 0.220     | 0.240 | 5.59        | 6.10  |
| U   | 0.910 BSC |       | 23.11 BSC   |       |
| V   | 0.248     | 0.278 | 6.30        | 7.06  |
| W   | 0.310     | 0.330 | 7.87        | 8.38  |

### STYLE 1:

- PIN 1: GROUND  
2: + OUTPUT  
3: + SUPPLY  
4: - OUTPUT

### CASE 344C-01 ISSUE B UNIBODY PACKAGE



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 1.080     | 1.120 | 27.43       | 28.45 |
| B   | 0.740     | 0.760 | 18.80       | 19.30 |
| C   | 0.630     | 0.650 | 16.00       | 16.51 |
| D   | 0.016     | 0.020 | 0.41        | 0.51  |
| E   | 0.160     | 0.180 | 4.06        | 4.57  |
| F   | 0.048     | 0.064 | 1.22        | 1.63  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| J   | 0.014     | 0.016 | 0.36        | 0.41  |
| K   | 0.220     | 0.240 | 5.59        | 6.10  |
| N   | 0.070     | 0.080 | 1.78        | 2.03  |
| P   | 0.150     | 0.160 | 3.81        | 4.06  |
| Q   | 0.150     | 0.160 | 3.81        | 4.06  |
| R   | 0.440     | 0.460 | 11.18       | 11.68 |
| S   | 0.695     | 0.725 | 17.65       | 18.42 |
| U   | 0.840     | 0.860 | 21.34       | 21.84 |
| V   | 0.182     | 0.194 | 4.62        | 4.92  |

### STYLE 1:

- PIN 1: GROUND  
2: V (+) OUT  
3: V SUPPLY  
4: V (-) OUT

### CASE 344F-15 ISSUE B UNIBODY PACKAGE

## ***How to Reach Us:***

### **Home Page:**

[www.freescale.com](http://www.freescale.com)

### **Web Support:**

<http://www.freescale.com/support>

### **USA/Europe or Locations Not Listed:**

Freescale Semiconductor, Inc.  
Technical Information Center, EL516  
2100 East Elliot Road  
Tempe, Arizona 85284  
1-800-521-6274 or +1-480-768-2130  
[www.freescale.com/support](http://www.freescale.com/support)

### **Europe, Middle East, and Africa:**

Freescale Halbleiter Deutschland GmbH  
Technical Information Center  
Schatzbogen 7  
81829 Muenchen, Germany  
+44 1296 380 456 (English)  
+46 8 52200080 (English)  
+49 89 92103 559 (German)  
+33 1 69 35 48 48 (French)  
[www.freescale.com/support](http://www.freescale.com/support)

### **Japan:**

Freescale Semiconductor Japan Ltd.  
Headquarters  
ARCO Tower 15F  
1-8-1, Shimo-Meguro, Meguro-ku,  
Tokyo 153-0064  
Japan  
0120 191014 or +81 3 5437 9125  
[support.japan@freescale.com](mailto:support.japan@freescale.com)

### **Asia/Pacific:**

Freescale Semiconductor China Ltd.  
Exchange Building 23F  
No. 118 Jianguo Road  
Chaoyang District  
Beijing 100022  
China  
+86 10 5879 8000  
[support.asia@freescale.com](mailto:support.asia@freescale.com)

### **For Literature Requests Only:**

Freescale Semiconductor Literature Distribution Center  
P.O. Box 5405  
Denver, Colorado 80217  
1-800-441-2447 or +1-303-675-2140  
Fax: +1-303-675-2150  
[LDCForFreescaleSemiconductor@hibbertgroup.com](mailto:LDCForFreescaleSemiconductor@hibbertgroup.com)

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale™ and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc. 2008. All rights reserved.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Freescale Semiconductor:](#)

[MPX2202D](#)