


NOTES Bemerkungen	F9	Drawing clarification (see PCN: E-17-013001)	05SEP2017	FRAN	BECK
	F10	Drawing clarification (see PCN: E-17-017307)	24NOV2017	FRAN	BECK

THIS DRAWING IS A CONTROLLED DOCUMENT. DESIGN IDENTIFICATION AND DATE AND IS PROTECTED IDENTIFY. ÄNDERUNG: 01.01.2018 (KONTROLLIERTE IDENTIFIZIERUNG, DATUM UND VERZEICHNIS) THIS ENGINE IDENTIFICATION AND DATE AND IS PROTECTED IDENTIFY.		DWN KILLZ CH HASS APVD		260C194 260C194	
0 DIMENSION LINES MASS IN METERS (MM)		TOLERANCES UNLESS SPECIFIED: FRACTIONAL DECIMALS DECIMALS		 TE Connectivity	



[illegible][illegible]

21	6	38.5	30	45	42.5	38.5	36.5	B (GROOVES) Nuten A-C			8-966140-6 A	1-966140-6 A	18.3g	4	7	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	7	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	7	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														5	1	21 POS. HOUSING	PA66-GF13	NATURAL/natur
								A (GROOVES B-C) (Nuten B_C)			9-966140-6 F	966140-6 F	18.3g	4	7	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	7	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	7	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														1	1	21 POS. HOUSING	PA66-GF13	BLACK/schwarz
								A (GROOVES B-C) (Nuten B_C)			9-966140-1 F	966140-1 F	16.0g	4	6	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	6	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	6	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														1	1	18 POS. HOUSING	PA66-GF13	BLACK/schwarz
								A (GROOVES B-C) (Nuten B_C)			9-966140-2 F	966140-2 F	13.6g	4	5	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	5	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	5	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														1	1	15 POS. HOUSING	PA66-GF13	BLACK/schwarz
								B (GROOVES) Nuten A-C			8-966140-3 A	1-966140-3 A	11.2g	4	4	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	4	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	4	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														5	1	12 POS. HOUSING	PA66-GF13	NATURAL/natur
								A (GROOVES B-C) (Nuten B_C)			9-966140-3 F	966140-3 F	11.2g	4	4	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	4	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	4	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														1	1	12 POS. HOUSING	PA66-GF13	BLACK/schwarz
								A (GROOVES B-C) (Nuten B_C)			9-966140-4 F	966140-4 F	8.9g	4	3	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	3	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	3	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														1	1	9 POS. HOUSING	PA66-GF13	BLACK/schwarz
								A (GROOVES B-C) (Nuten B_C)			9-966140-5 F	966140-5 F	6.6g	4	2	TAB (43.4mm)	CuSn4	TINNED/verzinkt
														3	2	TAB (34.4mm)	CuSn4	TINNED/verzinkt
														2	2	TAB (25.4mm)	CuSn4	TINNED/verzinkt
														1	1	6 POS. HOUSING	PA66-GF13	BLACK/schwarz
POSITIONS Polzahl	n	a±0.2	b	c	d _{0.2}	e _{0.25}	f	CODING Kodierung	CAVITY NUMBERING Kammerbezeichnung	ORDER NO. REV. Bestell-Nr.	ORDER NO. REV. Bestell-Nr.	WEIGHT Gewicht	POS.	QTY Stueck	DESCRIPTION Benennung Einzelteil	MATERIAL Werkstoff	SURFACE/Oberflaeche COLOUR/ Farbe	

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN Mahinko, B.		160C 12014		 TE Connectivity	
		CHN Krauss, S.		170C 12014			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Goppel, C.		NAME	
mm				PRODUCT SPEC		TAB HEADER, 2.8x0.8, 6-21 POS.	
		0 P/LC ±		-		Messerleiste, 2.8x0.8, 6-21 pol.	
		2 P/LC ±		-		-	
		3 P/LC ±		APPLICATION SPEC			
		4 P/LC ±					
		ANGLES ±0.2°		WEIGHT		SIZE CASE CODE DRAWING NO RESTRICTED TO	
MATERIAL SEE PARTS LIST		FINISH SEE PARTS LIST		-		A1 00779 C=966140 -	
				Customer Drawing		SCALE 2:1 SHEET 2 OF 2 REF: F10	