




RECOMMENDED P.C.B. LAYOUT FROM COMPONENT SIDE
(PCB THICKNESS (1.60^{+0.20})/.063^{±.008})

90800 - 0 0 0 0
CIRCUIT SIZE
0= (3-5UM) / 120-200UIN TIN VERSION
3= (0.76UM) / 30UIN GOLD VERSION

90800-0026	26	(36.80)/1.449	(31.75)/1.250	14	YES
90800-0024	24	(34.26)/1.349	(29.21)/1.150	15	YES
90800-0022	22	(31.72)/1.249	(26.67)/1.050	16	YES
90800-0020	20	(29.18)/1.149	(24.13)/.950	18	YES
90800-0018	18	(26.64)/1.049	(21.59)/.850	20	YES
90800-0016	16	(24.10)/.949	(19.05)/.750	22	YES
90800-0014	14	(21.56)/.849	(16.51)/.650	24	YES
90800-0012	12	(19.02)/.749	(13.97)/.550	28	YES
90800-0010	10	(16.48)/.649	(11.43)/.450	32	YES
90800-0008	8	(13.94)/.549	(8.89)/.350	38	YES
90800-0006	6	(11.40)/.449	(6.35)/.250	46	YES
90800-0004	4	(8.86)/.349	(3.81)/.150	59	YES
PART NO.	NO. OF CKTS	DIMN. A	DIMN. B	QTY PER TUBE	TOOLED

NOTES:
1) MATERIAL: HOUSING: POLYESTER PBT 15% G.F., UL 94 V-0, BLACK.
TERMINAL: CARTRIDGE BRASS (.028)/.011 REF THICK
2) SEE PRODUCT SPECIFICATION PS-99020-0011.

ADD CKT.1 INDICATOR
EC NO: E2007-0083
DRWN: WASZKIEWICZ 2006/09/11
CHKD: J. DENNEHY 2006/09/11
APPR: J. DENNEHY 2006/09/13

DESCRIPTION

REV

QUALITY SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES (UNLESS SPECIFIED)
mm INCH
4 PLACES ± --- ± ---
3 PLACES ± --- ± .004
2 PLACES ± 0.10 ± ---
1 PLACE ± --- ± ---
ANGULAR ± 1/2°

DRAFT WHERE APPLICABLE
MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY DATE
PK 1994/01/28

CHECKED BY DATE
J. DENNEHY

APPROVED BY DATE
J. DENNEHY

MATERIAL NO.

DOCUMENT NO.
SDA-90800E

SCALE
10:1

DESIGN UNITS
METRIC

THIRD ANGLE PROJECTION

TITLE
RIGHT ANGLE STRAGGERED PICO FLEX HEADER ASSY (1.25)/.050 CENTRES

MOLEX INCORPORATED

SHEET NO.
1 OF 1