




NOTES:

1. RoHS COMPLIANT
2. SUITABLE FOR WAVESOLDERING
3. METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
4. INSULATORS: HIGH TEMPERATURE PLASTIC UL 94 V-0, BLACK
5. CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min. 50µin NICKEL
CONTACT TAILS PRETINNED
6. METAL BRACKET: ZINC DIE CAST; 300µin COPPER/40-120µin NICKEL/120-200µin TIN
7. THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
8. CAPACITANCE: 2 x 1300pF±20%
9. DIELECTRIC WITHSTANDING VOLTAGE: 300 VDC
10. P.C.B. HOLE DRILLINGS ON SHEET 2
11. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
12. CONNECTOR IS PART MARKED: 241A26320X CONEC ABC

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	


THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:				tolerance ISO 2768-m		 dim. in mm	
					date	name	
				drawn	10.09.07	Schmidt	
				appd.	10.09.07	Mickenbecker	
				norm	DIN 41652		
				d-old			
a	Origin						
rev.	description	date	name				

CONEC

scale:	2:1 (5:1)		
material:	see notes		
title:	D-SUB π Filter Male 90° 9pos., 0.590inch threaded insert, metal bracket and snap		
dwg no:	Inventor 10	DIN-A3	
®	24K1A1041		sh: 1
	part no: 241A26320X		




THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

finish:			
rev.	description	date	name
a	Origin		

tolerance
ISO 2768-m



date	name
drawn 10.09.07	Schmidt
appd. 10.09.07	Mickenbecker
norm	DIN 41652
d-old	

CONEC®

scale: 2:1
material: see sheet 1

title:
P.C.B. HOLE DRILLINGS
D-SUB π Filter Male 90° 9pos., 0,590inch
threaded insert, metal bracket and snap

dwg no: Inventor 10
24K1A1041
part no: see sheet 1
DIN-A4
sh: 2