




HONEYWELL
PART NUMBER
1XE122

REV	DOCUMENT	CHANGED BY	CHECK
B	0020191	BNA 22MAR06	AS



NOTES

- 1 MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON .188 $\pm$.002 CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- 3 WEIGHT OF SWITCH ONLY IS .16 OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS .55 OZ MAX
- 4 BASIC SWITCH HAS GOLD PLATED SILVER CONTACTS

CHARACTERISTICS		ELECTRICAL DATA		DESIGN UNITS: INCH		DRAWN	KRB	09SEP05	Honeywell					
OPERATING FORCE — — — — — 5-17 OZ		CONTACT ARRANGEMENT		TOLERANCES UNLESS NOTED:		CHECK	RJ	09SEP05						
RELEASE FORCE — — — — — 4 OZ MIN		S P D T		NO PLACE X ±		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE					
RELEASE TRAVEL — — — — — .004 MIN		28 VOLTS DC RATING		ONE PLACE .X ± 0.030										
DIFFERENTIAL TRAVEL — — — .005 MAX		INDUCTIVE — SEA LEVEL — 4 AMP		TWO PLACE .XX ± 0.015										
OVERTRAVEL — — — — — .004 MIN		RESISTIVE — SEA LEVEL — 7 AMP		THREE PLACE .XXX ± 0.005										
		50,000 FT — 7 AMP		FOUR PLACE .XXXX ±		INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV	
		LAMP — SEA LEVEL — 1 AMP		ANGLES ±					B	I	1XE122		B	
		MOTOR — " " — 2.5 AMP		THIRD ANGLE PROJECTION		RASTER			SCALE	2 : 1	WEIGHT	3	SHEET	1 OF 1
		115 V 400 CYCLES — SEA LEVEL												
		RESISTIVE — 7 AMP												
		INDUCTIVE — 4 AMP												
		LAMP — 1 AMP												
		MOTOR — 1.5 AMP												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1XE122](#)