

The diagram illustrates various circuit configurations and their dimensions. The configurations are arranged in a grid, with the number of circuits (CKTS.) indicated below each set of components.



Configuration	Number of Circuits (CKTS.)
6 CKTS.	6 CKTS.
8 CKTS.	8 CKTS.
18 CKTS.	18 CKTS.
20 CKTS.	20 CKTS.
4 CKTS.	4 CKTS.
10 CKTS.	10 CKTS.
16 CKTS.	16 CKTS.
22 CKTS.	22 CKTS.
2 CKTS.	2 CKTS.
12 CKTS.	12 CKTS.
14 CKTS.	14 CKTS.
24 CKTS.	24 CKTS.

CIRCUIT SIZE LAYOUT


The layout shows a series of components with dimensions and tolerances:

- Overall width: $A \pm 0.16$ / ± 0.40
- Component dimensions: $.11$ / 2.7 , $.17$ TYP / 4.2
- Spacing: $.02 \pm .01$, 0.4 ± 0.2
- Feature: $\varnothing .04 / 1.0$ Z Y

RIB INDICATES CIRCUIT NO. 1



LEGEND



12	11	10	9	8	7	6	5	4	3	2	1
----	----	----	---	---	---	---	---	---	---	---	---

12		11		10		9		8		7		6		5		4		3		2		1	
H				39-30-9245	5566-24AGS2-210	39-29-6248	5566-24AGS-210											39-28-8240	5566-24A-210	24	H		
				39-30-9225	5566-22AGS2-210	39-29-6228	5566-22AGS-210											39-28-8220	-22A-210	22			
	39-29-5207	5566-20APB-210	39-30-9205	5566-20AGS2-210	39-29-6208	5566-20AGS-210												39-28-8200	-20A-210	20			
	39-29-5187	5566-18APB-210	39-30-9185	5566-18AGS2-210	39-29-6188	5566-18AGS-210												39-28-8180	-18A-210	18			
			39-30-9165	5566-16AGS2-210	39-29-6168	5566-16AGS-210	39-30-6162	5566-16AS-210	39-28-8160	-16A-210	16							39-28-8140	-14A-210	14			
			39-30-9145	5566-14AGS2-210	39-29-6148	5566-14AGS-210												39-28-8120	-12A-210	12			
			39-30-9125	5566-12AGS2-210	39-29-6128	5566-12AGS-210												39-28-8100	-10A-210	10			
			39-30-9105	5566-10AGS2-210	39-29-6108	5566-10AGS-210												39-28-8080	-08A-210	8			
G			39-30-9085	5566-08AGS2-210	39-29-6088	5566-08AGS-210	39-30-6082	5566-08AS-210	39-28-8080	-08A-210	6							39-28-8060	-06A-210	4	G		
			39-30-9065	5566-06AGS2-210	39-29-6068	5566-06AGS-210	39-30-6062	5566-06AS-210	39-28-8060	-06A-210	4							39-28-8040	-04A-210	2			
			39-30-9045	5566-04AGS2-210	39-29-6048	5566-04AGS-210	39-30-6042	5566-04AS-210	39-28-8040	-04A-210	2							39-28-8020	5566-02A-210	CKT. SIZE			
	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.		CKT. SIZE	
	5566-NAPB-210		5566-NAGS2-210		5566-NAGS-210		5566-NAS-210		5566-NA-210		5566-NA-210		5566-NA-210		5566-NA-210		5566-NA-210		5566-NA-210			CKT. SIZE	
	39-29-5246	5566-24APB	39-30-9244	5566-24AGS2	39-29-0243	5566-24AGS			39-28-1243	5566-24A	24							39-28-1223	5566-22A	22			
			39-30-9224	5566-22AGS2	39-29-0223	5566-22AGS			39-28-1223	5566-22A	20							39-28-1203	5566-20A	18			
			39-30-9204	5566-20AGS2	39-29-0203	5566-20AGS			39-28-1203	5566-20A	16							39-28-1183	5566-18A	14			
F			39-30-9184	5566-18AGS2	39-29-0183	5566-18AGS			39-28-1183	5566-18A	12							39-28-1163	5566-16A	10	F		
			39-30-9164	5566-16AGS2	39-29-0163	5566-16AGS			39-28-1163	5566-16A	10							39-28-1143	5566-14A	8			
	39-29-5146	5566-14APB	39-30-9144	5566-14AGS2	39-29-0143	5566-14AGS			39-28-1143	5566-14A	8							39-28-1123	5566-12A	6			
			39-30-9124	5566-12AGS2	39-29-0123	5566-12AGS			39-28-1123	5566-12A	6							39-28-1103	5566-10A	4			
	39-29-5106	5566-10APB	39-30-9104	5566-10AGS2	39-29-0103	5566-10AGS	39-30-6101	5566-10AS	39-28-1103	5566-10A	4							39-28-1083	5566-08A	2			
	39-29-5086	5566-08APB	39-30-9084	5566-08AGS2	39-29-0083	5566-08AGS	39-30-6081	5566-08AS	39-28-1083	5566-08A	2							39-28-1063	5566-06A	2			
	39-29-5066	5566-06APB	39-30-9064	5566-06AGS2	39-29-0063	5566-06AGS			39-28-1063	5566-06A	2							39-28-1043	5566-04A	2			
	39-29-5046	5566-04APB	39-30-9044	5566-04AGS2	39-29-0043	5566-04AGS			39-28-1043	5566-04A	2							39-28-1023	5566-02A	2			
E	39-29-5026	5566-02APB	39-30-9024	5566-02AGS2	39-29-0023	5566-02AGS			39-28-1023	5566-02A	2							39-28-1023	5566-02A	2	E		
	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.	EDP NO.	ENG. NO.		CKT. SIZE	
	5566-NAPB		5566-NAGS2		5566-NAGS		5566-NAS		5566-NA		5566-NA		5566-NA		5566-NA		5566-NA		5566-NA			CKT. SIZE	

PARTS WITH OUT DRAIN HOLES

QUALITY SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																			
	= 0	UPDATE NOTE 2	2017/03/10 2017/05/12 2017/05/18	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE														
	= 0				IN/MM		1:1														
	= 0								MINI FIT JR VERTICAL HEADER ASSEMBLIES WITHOUT PEGS												
	= 0																				
	= 0																				
	= 0								PRODUCT CUSTOMER DRAWING												
	= 0																				
	= 0																				
	= 0												SERIES 5566								
																			MATERIAL NUMBER SEE TABLE		
										CUSTOMER GENERAL MARKET											
																DOC TYPE PSD					
																SHEET NUMBER 2 OF 5					
</																					

[illegible]

[illegible]

