

PERFECT cable gland


50.0xx PABSzzzz

Configuration

Dome nut	Polyamide PA6 V-2
Sealing ring	Polychloroprene-Nitrile rubber CR/NBR
Gland body	Polyamide PA6 V-2
Connecting thread	Pg as per DIN 40430

Properties

	• with spiral top, • for movable flexible cables • integrated anchorage • wide sealing and clamping range • easy-to-install
Temperature range	-20°C +100°C
Protection grade	IP68 5bar
Test standard	UL 514B
UL / CSA-File	E140310
Comment	details about test standards see annex



Features



RAL 9005

Connecting thread standard length

A	ØC	L	SW1	SW2	H		Part No.
	mm	mm	mm	mm	mm	Piece	
Pg 7	3 - 6,5	8	15	15	63	100	50.007 PABSSW
Pg 9	4 - 8	8	19	19	74	100	50.009 PABSSW
Pg 11	5 - 10	8	22	22	87	100	50.011 PABSSW
Pg 13,5	6 - 12	9	24	24	98	50	50.013 PABSSW
Pg 16	10 - 14	10	27	27	112	25	50.016 PABSSW
Pg 21	13 - 18	11	33	33	130	25	50.021 PABSSW



RAL 7035

Connecting thread standard length

A	ØC	L	SW1	SW2	H		Part No.
	mm	mm	mm	mm	mm	Piece	
Pg 7	3 - 6,5	8	15	15	63	100	50007PABS7035
Pg 9	4 - 8	8	19	19	74	100	50009PABS7035
Pg 11	5 - 10	8	22	22	87	100	50011PABS7035
Pg 13,5	6 - 12	9	24	24	98	50	50013PABS7035
Pg 16	10 - 14	10	27	27	112	25	50016PABS7035
Pg 21	13 - 18	11	33	33	130	25	50021PABS7035



RAL 7001

Connecting thread standard length

A	ØC	L	SW1	SW2	H		Part No.
	mm	mm	mm	mm	mm	Piece	
Pg 7	3 - 6,5	8	15	15	63	100	50.007 PA/BS
Pg 9	4 - 8	8	19	19	74	100	50.009 PA/BS
Pg 11	5 - 10	8	22	22	87	100	50.011 PA/BS
Pg 13,5	6 - 12	9	24	24	98	50	50.013 PA/BS
Pg 16	10 - 14	10	27	27	112	25	50.016 PA/BS
Pg 21	13 - 18	11	33	33	130	25	50.021 PA/BS