

LOC		DIST				REVISIONS						
AJ		16		P	F	ZONE	LTR	DESCRIPTION			DATE	APPD
				✓	✓		A	REV PER 0U20-0666-00			07DEC00	MO

- 1

ZINC PER QQ-Z-363.
- 2

POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3

PHOSPHOR BRONZE PER QQ-B-750.
- 4

BRASS PER ASTM-B-453.
- 5




BRASS PER ASTM-B-16.
- 6

NICKEL PLATE PER QQ-N-290,
3.81 μm [.000150] MINIMUM THICK.
- 7


TIN-LEAD PLATE PER MIL-P-81728,
3.81 μm [.000150] MINIMUM THICK.
- 8

GOLD PLATE PER MIL-G-45204,
0.76 μm [.000030] MINIMUM THICK.
9.

SEE INSTRUCTION SHEET 2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

414409-1
PART NUMBER

							PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.20 [.008] 3 PLC DEC ± - ANGLES ± -		DR 10-26-92 J. LIPPERT		AMP AMP Incorporated Harrisburg, PA 17105-3608				
		CHK 10-27-92 A. GABANY						
		APPD 10-27-92 A. GABANY						
		APPD 10-27-92 J. LIPPERT						
MATERIAL		PRODUCT SPEC		NAME JACK, RIGHT ANGLE, PCB 75 OHM, SERIES BNC				
SEE NOTES 1 THRU 5		108-12078						
FINISH		APPLICATION SPEC		SIZE	CAGE CODE	DRAWING NO		
SEE NOTES 6 THRU 8		-		D	00779	414409		
		WEIGHT _		SCALE	4:1			SHEET 1 OF 1