


# SMT MICRO HEADER & SOCKET

(1.27 mm) .050" PITCH • FTR/RSM SERIES







**FTR**  
Mates:  
RSM, SMS, SLM

**RSM**  
Mates:  
FTR, HTMS, HDWM,  
DWM, TML, ZML, TMS

## SPECIFICATIONS

**Insulator Material:**  
Black Liquid Crystal Polymer  
**Contact Material:**  
RSM: Phosphor Bronze  
**Terminal Material:**  
FTR: Phosphor Bronze  
**Plating:**  
Au or Sn over  
50  $\mu$ m (1.27  $\mu$ m) Ni  
**Operating Temp Range:**  
FTR: -55 °C to +105 °C with Tin;  
FTR: -55 °C to +125 °C with Gold  
RSM: -55 °C to +125 °C  
**Current Rating (FTR/RSM):**  
3.8 A per pin  
(2 pins powered)  
**Voltage Rating:**  
290 VAC/410 VDC  
**Lead Size Accepted:**  
RSM: (0.46 mm) .018" SQ  
**Insertion Depth:**  
RSM: Top Entry =  
(2.64 mm) .104" to (5.84 mm) .230"  
with (0.38 mm) .015" wipe, or  
pass-through.  
RSM: Bottom Entry =  
(5.49 mm) .216" minimum  
(Add board thickness for  
correct post OAL)



| FTR        | 1            | NO. PINS PER ROW | LEAD STYLE                    | PLATING OPTION  | ROW OPTION   | OPTION  |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
|------------|--------------|------------------|-------------------------------|---|--|---|---|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|-------------|-----|--------------|-----|--------------|--|
|            |              | 02 thru 40       | Specify LEAD STYLE from chart | <b>-F</b><br>= Gold flash on contact, Matte Tin on tail<br><br><b>-L</b><br>= 10 $\mu$ m (0.25 $\mu$ m) Gold on post, Matte Tin on tail<br><br><b>-G</b><br>= 10 $\mu$ m (0.25 $\mu$ m) Gold on post, Gold flash on tail  | <b>-S</b><br>= Single Row<br><br><b>-D</b><br>= Double Row | <b>-XX</b><br>= Polarized<br><br><b>-A</b><br>= Alignment Pin (5 positions min. for -D) (Metal or plastic at Samtec discretion) (Not available with -LC)<br><br><b>-LC</b><br>= Locking Clip (6 positions min. for -D) (Not available with -A) (Manual placement required)<br><br><b>-P</b><br>= Plastic Pick & Place Pad (5 positions min. for -D) (8 positions min. for -S)<br><br><b>-TR</b><br>= Tape & Reel (4 positions min. for -S)<br><br><b>-FR</b><br>= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) (4 positions min. for -S) |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
|            |              |                  |                               | <table border="1"> <thead> <tr> <th>LEAD STYLE</th> <th>A</th> </tr> </thead> <tbody> <tr><td>-01</td><td>(5.84) .230</td></tr> <tr><td>-02</td><td>(2.54) .100</td></tr> <tr><td>-03</td><td>(3.18) .125</td></tr> <tr><td>-51</td><td>(4.83) .190</td></tr> <tr><td>-52</td><td>(5.21) .205</td></tr> <tr><td>-53</td><td>(7.24) .285</td></tr> <tr><td>-54</td><td>(8.51) .335</td></tr> <tr><td>-55</td><td>(9.91) .390</td></tr> <tr><td>-56</td><td>(10.29) .405</td></tr> <tr><td>-57</td><td>(10.92) .430</td></tr> </tbody> </table> |  | LEAD STYLE  | A | -01 | (5.84) .230 | -02 | (2.54) .100 | -03 | (3.18) .125 | -51 | (4.83) .190 | -52 | (5.21) .205 | -53 | (7.24) .285 | -54 | (8.51) .335 | -55 | (9.91) .390 | -56 | (10.29) .405 | -57 | (10.92) .430 |  |
| LEAD STYLE | A            |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -01        | (5.84) .230  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -02        | (2.54) .100  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -03        | (3.18) .125  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -51        | (4.83) .190  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -52        | (5.21) .205  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -53        | (7.24) .285  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -54        | (8.51) .335  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -55        | (9.91) .390  |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -56        | (10.29) .405 |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |
| -57        | (10.92) .430 |                  |                               |   |  |   |   |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |             |     |              |     |              |  |

## PROCESSING

**Lead-Free Solderable:**  
Yes  
**SMT Lead Coplanarity:**  
RSM: (0.10 mm) .004" max  
FTR: (0.10 mm) .004" max (02-20)  
FTR: (0.15 mm) .006" max (21-40)\*  
\*(.004" stencil solution may be available; contact ipg@samtec.com)

| RSM | 1 | NO. PINS PER ROW | 02 | PLATING OPTION   | ROW OPTION   | OPTION  |
|-----|---|------------------|----|--|--|---|
|     |   | 02 thru 36       |    | <b>-F</b><br>= Gold flash on contact, Matte Tin on tail<br><br><b>-L</b><br>= 10 $\mu$ m (0.25 $\mu$ m) Gold on contact, Matte Tin on tail | <b>-S</b><br>= Single Row<br><br><b>-D</b><br>= Double Row | <b>-K</b><br>= (6.25 mm) .246" DIA Polyimide film Pick & Place Pad (5 positions minimum for -D) (7 positions minimum for -S)<br><br><b>-P</b><br>= Plastic Pick & Place Pad (5 positions minimum for -D) (6 positions minimum for -S)<br><br><b>-TR</b><br>= Tape & Reel<br><br><b>-FR</b><br>= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks) |
|     |   |                  |    | <p><b>ALSO AVAILABLE</b><br/>Contact Samtec</p> <p>Other platings<br/>Locking clips</p>  |  |   |
|     |   |                  |    |  |  |   |
|     |   |                  |    |  |  |   |

**Note:**  
Some lengths, styles and options are non-standard, non-returnable.